


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS		SINGLEMODE MAXIMUM LOSS
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm		.40 dB/KM @ 1310nm .30 dB/KM @ 1500nm
BEND RADIUS		
INSTALLATION		LONG TERM
21.8cm [8.6in]		10.9cm [4.3in]
TENSILE LOAD		
INSTALLATION		LONG TERM
2700 N (600 lbf)		890 N (200 lbf)
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-10°C TO +60°C 4°F TO +140°F	-30°C TO +70°C -22°F TO +158°F	-40°C TO +70°C -40°F TO +158°F

							TITLE	2,4,6 & 8 FIBER OUTSIDE PLANT UNARMORED STRANDED CABLE									
							ITEM REVISION NAME	CUSTOMER DRAWING									
							M02055JW/00	<div>PANDUIT</div>									
							DATASET FILE NAME						M02055JW_DC/00A				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]										
							.X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±										
							<div><div><div></div></div><div><div></div></div></div> THIRD ANGLE PROJECTION					PART NO. SEE TABLE					
00	02-13-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JW-DC	DRAWING NUMBER: M02055JW-DC					SIZE A					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2						
							SAT	02-13-14	WMA	NONE							

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	FIBER TYPE	FIBER COUNT	FIBER PER TUBE	NO. FILLER TUBES
FLTN602	MULTIMODE 62.5/125	2	1 TUBE WITH 2 FIBERS	5
FLTN604		4	1 TUBE WITH 4 FIBERS	
FLTN606		6	BLUE TUBE WITH 4 FIBERS ORANGE TUBE WITH 2 FIBERS	4
FLTN608		8	2 TUBES WITH 4 TUBES	
FLTN502	MULTIMODE 50/125 OM2	2	1 TUBE WITH 2 FIBERS	5
FLTN504		4	1 TUBE WITH 4 FIBERS	
FLTN506		6	BLUE TUBE WITH 4 FIBERS ORANGE TUBE WITH 2 FIBERS	4
FLTN508		8	2 TUBES WITH 4 TUBES	
FLTNX02	MULTIMODE 50/125 OM3	2	1 TUBE WITH 2 FIBERS	5
FLTNX04		4	1 TUBE WITH 4 FIBERS	
FLTNX06		6	BLUE TUBE WITH 4 FIBERS ORANGE TUBE WITH 2 FIBERS	4
FLTNX08		8	2 TUBES WITH 4 TUBES	
FLTNZ02	MULTIMODE 50/125 OM4	2	1 TUBE WITH 2 FIBERS	5
FLTNZ04		4	1 TUBE WITH 4 FIBERS	
FLTNZ06		6	BLUE TUBE WITH 4 FIBERS ORANGE TUBE WITH 2 FIBERS	4
FLTNZ08		8	2 TUBES WITH 4 TUBES	
FLTN902	SINGLEMODE 9/125	2	1 TUBE WITH 2 FIBERS	5
FLTN904		4	1 TUBE WITH 4 FIBERS	
FLTN906		6	BLUE TUBE WITH 4 FIBERS ORANGE TUBE WITH 2 FIBERS	4
FLTN908		8	2 TUBES WITH 4 TUBES	

						TITLE		2,4,6 & 8 FIBER OUTSIDE PLANT UNARMORED STRANDED CABLE	
						CUSTOMER DRAWING			
						ITEM REVISION NAME		M02055JW/00	
						DATASET FILE NAME		M02055JW_DC/00A	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT PART NO. SEE TABLE DRAWING NUMBER: M02055JW-DC	
						.X ± .XX ± .03 [0.8] .XXX ± .010 [0.3] ANGLES ±			
						 THIRD ANGLE PROJECTION			
00	02-13-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JW-DC			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK
							SAT	02-13-14	WMA
							SCALE	SIZE	
							NONE	A	
							SHT 2 OF 2		