



3933 US ROUTE 11, CORTLAND, NEW YORK 13045
 Phone Number: 1-800-345-3851 Fax Number: 607-758-3648

REPORT OF TEST

Panduit Corporation
 10500 167th Street
 Orland Park, IL 60467


The products described in this Report were tested and examined by Intertek for compliance to the standards listed below. The products listed below are not part of an Intertek Verification Program. The results are provided to the client as a one time performance test and shall not be utilized to imply compliance to the standard as part of an on-going program.

Reference Intertek Report No.: 100394839CRT-001b

Date: April 28, 2011

Test:

Electrical performance testing of a cabling configuration to the requirements of ANSI/TIA-568-C.2 for Category 6 channel and ISO/IEC 11801 for Class E channel.



Component Id	Manufacturer	Description	Part number
1	Panduit	Outlet Patch Cord	UTPSP5M
2	Panduit	Outlet Hardware	CJ688TG
3	Panduit	Zone Cord	UJLBBU5MBLY
4	Panduit	Horizontal Cable	PUL6004
5	Panduit	Equipment Cord	UTPSP2M
6	Panduit	Equipment Cord	UTPSP3M

Standards and sections used:


ANSI/TIA-568-C.2-2009: Balanced Twisted-Pair Telecommunications Cabling and Components Standards, dated August 2009 (Sections 6.2.1 to 6.2.26)

ISO/IEC 11801 Information Technology - Generic cabling for customer premises, Second edition dated September 2002 including amendments up to Amendment 2, dated April 2010 (Sections 6.4.2 to 6.4.8 and 6.4.12 to 6.4.14.3)

Conclusion:

The channel cabling configuration, as described above, was tested in accordance with the ANSI/TIA-568-C.2-2009 and ISO/IEC 11801 standards, and did comply with the indicated applicable transmission requirements. The testing was performed at Intertek located in Cortland, New York.

Reviewed and approved by:


 John Cash
 Technician
 Global Cabling Products Testing


 Antoine Pelletier
 Engineer
 Global Cabling Products Testing

This report is for the exclusive use of Intertek's Client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this report. Only the Client is authorized to copy or distribute this report and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test results in this report are relevant only to the sample tested. This report by itself does not imply that the material, product, or service is or has ever been under an Intertek certification program.