






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| | |
|-------------|-----------------------------------|
| PANDUIT P/N | WEIGHT |
| PXM1ARGRBL | .30 LB/10 PCS (134.8 g/10 PCS) |

NOTES:

1. ALL PURCHASED ITEMS MUST CONFORM TO C2-0834 PANDUIT SPECIFICATION FOR CHEMICAL SUBSTANCES TO BE CONTROLLED IN PRODUCT AND PACKAGING.
2. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
3. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
4. DIMENSIONS IN [] ARE IN METRIC.
5. PART INCLUDES:
 - 1- BLACK MODULE BASE
 - 1- GREEN MALE EUROSTYLE CONNECTOR (ASSEMBLED TO MODULE BASE)
 - 1- GREEN FEMALE EUROSTYLE CONNECTOR
6. WIRE GAGE RANGE: 26-12



| | | | |
|---|-----------------|--------------------|------|
| PART NUMBER | | PXM1ARGRBL | |
| TITLE | | | |
| MINI-COM POWER CONNECTOR MODULE ASSEMBLY | | | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | | 01959NZY/02 | |
| DATASET FILE NAME | | 01959NZY_DC/02B | |
| UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: IN [MM] | | | |
| .X +/- | | .XXX +/- .010 [.3] | |
| .XX +/- .03 [.8] | | ANGLES +/- | |
| DRAWING NUMBER: | | 01959NZY - DC | |
| THIRD ANGLE PROJECTION | DRAWING NUMBER: | | |
| DRAWN BY | | DATE | CHK |
| TWW | | 2-23-21 | REFR |
| SCALE | 1:1 | | SIZE |
| SHT 1 OF 1 | | A | |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|-----------|-----|-----|------|-------------------------------------|-------------|
| 02B | 9-01-2023 | TA | SWL | MIBR | A. UPDATED PART NAME IN TITLE BLOCK | 01959NZY-DC |
| 02A | 9-23-21 | BJN | TA | MIBR | RELEASED TO PRODUCTION | 01959NZY-DC |

N\GLOBAL-ASIZE