



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



**FLEXFUSION™ CABINET
WITH BEZELS AND COVERS**

**FLEXFUSION™ CABINET
WITH BRUSHES**

700mm CABINET SHOWN

NOTES:


1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. FACTORY SETTINGS:
SERVER CONFIGURATION - ALL WIDTHS AND DEPTHS:
FRONT FACE OF FRONT E-RAILS ARE: 64.0mm ±2.0mm / [2.52in ±0.08in] FROM FRONT FACE OF FRAME.
FRONT FACE OF REAR E-RAILS ARE: 742mm ±2.0mm / [29.2in ±0.08in] FROM FRONT FACE OF FRONT E-RAILS.
NETWORK CONFIGURATION - ALL DEPTHS:
600mm WIDE:
FRONT FACE OF FRONT E-RAILS ARE: 234.0mm ±2.0mm / [9.2in ±0.08in] FROM FRONT FACE OF FRAME.
FRONT FACE OF REAR E-RAILS ARE: 572mm ±2.0mm / [22.5in ±0.08in] FROM FRONT FACE OF FRONT E-RAILS.
700mm & 800mm WIDE:
FRONT FACE OF FRONT E-RAILS ARE: 177.0mm ±2.0mm / [7.0in ±0.08in] FROM FRONT FACE OF FRAME.
FRONT FACE OF REAR E-RAILS ARE: 629mm ±2.0mm / [24.8in ±0.08in] FROM FRONT FACE OF FRONT E-RAILS.
3. FOR REAR E-RAIL ADJUSTMENTS
SEE TABLE ON SHEET 8
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS
15.88mm, 15.88mm, 12.70mm, 15.88mm, 15.88mm, 12.7mm...ETC.
6. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS
7. FRONT TO BACK BEAMS ARE NUMBERED AND INDEXED FOR E-RAIL LOCATIONS
8. PARTS SUPPLIED:
-FRAME
-E-RAILS
-TOP CAP
-LEVELING LEGS
9. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS
10. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM, BOTH FRONT AND BACK OF CABINET
11. STATIC LOAD RATING: 1588 Kg (3500 lbs)
12. ROLLING LOAD RATING: 1134 Kg (2500 lbs)
13. PRIMARY DIMENSIONS ARE IN MILLIMETERS

TITLE		FLEXFUSION™ CABINET FAMILY		
ITEM REVISION NAME		CUSTOMER DRAWING		
00460NXB/04		PANDUIT		
DATASET FILE NAME				
00460NXB_DC/04A		MATERIAL:		
		N/A		
		DRAWING NUMBER:		
		00460NXB-DC		
		THIRD ANGLE PROJECTION		
DRAWN BY	DATE	CHK	SCALE	
LEE	1/5/2021	SSP	NONE	
REV		DATE		BY
00A		1/5/2021		LEE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	1/30/23	HBO	FWI	FWI	PDU BRACKET UPDATED. UPDATED ALL WIDTHS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	UPDATED ALL WIDTHS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	REPLACED 51RU VALUES W/ 52RU, UPDATED NOTE #2	V09002FD/04
01B	9/13/21	MES	BRAP	ELE	UPDATED DIMENSIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	ADDED WEIGHTS	V09002FD/02
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00

D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




* HEIGHT WITHOUT CASTERS IS 24mm [0.94] LESS
 ** CASTERS ARE NOT AVAILABLE ON 52RU CABINETS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00

TITLE						FLEXFUSION™ CABINET FAMILY			
ITEM REVISION NAME						CUSTOMER DRAWING			
00460NXB/04						PANDUIT			
DATASET FILE NAME									
00460NXB_DC/04A						MATERIAL:			
						N/A			
						DRAWING NUMBER:			
						00460NXB-DC			
DRAWN BY		DATE		CHK		SCALE		SIZE	
LEE		1/5/2021		SSP		NONE		A	


D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



VIEW BN
600mm E-RAIL ARRANGEMENT
NO PASS THRU OPENINGS


PASS THRU COVERS



700mm E-RAIL ARRANGEMENT



PASS THRU OPENINGS FOR
42RU - 12 PASS THRU OPENINGS
45RU - 12 PASS THRU OPENINGS
48RU - 16 PASS THRU OPENINGS
52RU - 16 PASS THRU OPENINGS
122mm X 34mm
(4.8) X (1.3)VIEW BL


PASS THRU COVERS



VIEW BM
800mm E-RAIL ARRANGEMENT
4 PASS THRU OPENINGS
FOR ALL RU SIZED CABINETS
19" X 1RU

NOTE:
*OPENINGS WILL FIT
CVPTB1X4 - SOLD SEPARATELY
*PASS THRU OPENING PARTIALLY
BLOCKED WHEN E-RAILS ARE
IN COMPLETELY FORWARD
POSITION



TITLE		FLEXFUSION™ CABINET FAMILY		
		CUSTOMER DRAWING		
ITEM REVISION NAME		00460NXB/04		PANDUIT
DATASET FILE NAME		00460NXB_DC/04A		
		MATERIAL:		N/A
		DRAWING NUMBER:		00460NXB-DC
 THIRD ANGLE PROJECTION		DRAWN BY	DATE	CHK
REV	DATE	BY	CHK	SCALE
LEE	1/5/2021	SSP	NONE	SHT 3 OF 12
DESCRIPTION		ECN	SIZE	A

04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

D110100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

**FRONT DOOR, REAR DOOR,
AND SIDE PANELS NOT SHOWN**

600mm 118 [4.6]
700mm 168 [6.6]
800mm 218 [8.6]

2X 180
[7.1]

TOP CAP HATCH
DOOR FOR CABLES
SEE SHEET 8 FOR
OPENING SIZE

1070 993 [39]
1200 1143 [45]

SEE SHEET 9 FOR
BEZELS AND COVERS
COMPATABILITY TABLE



(6) LOCATIONS FOR 1070mm
(6) LOCATIONS FOR 1200mm
TAPPED FOR M10 THREADED ROD

RACK UNITS ARE
NUMBERED AND
INDEXED FOR
IDENTIFICATION

VERTICAL CABLE
MANAGEMENT FINGERS
WITH BEND RADIUS
CONTROL CAN BE ASSEMBLED
TO FRONT OR REAR E-RAILS
BY CUSTOMER

(2) ADJUSTABLE REAR
EQUIPMENT RAILS
SEE SHEET 8 FOR
DEFAULT SETTINGS
AND ADJUSTABILITY
RANGE TABLE

(2) ADJUSTABLE FRONT
EQUIPMENT RAILS
SEE SHEET 8 FOR
DEFAULT SETTINGS
AND ADJUSTABILITY
RANGE TABLE



FRONT


REAR

REAR

FRONT

TOP VIEW


**TOP CAP WITH BEZEL & COVERS OPTION SHOWN
BRUSH OPTION ALSO AVAILABLE**

TITLE		FLEXFUSION™ CABINET FAMILY	
		CUSTOMER DRAWING	
ITEM REVISION NAME		00460NXB/04	
DATASET FILE NAME		00460NXB_DC/04A	
		MATERIAL: N/A	
		DRAWING NUMBER: 00460NXB-DC	
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
LEE	1/5/2021	SSP	NONE
REV		DESCRIPTION	
DATE		ECN	
BY		SIZE	
CHK		SHT 4 OF 12	
APR		A	

04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00

D10100DA/16


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT


(2) STANDARD PDU BRACKETS

CAN BE INSTALLED ON LEFT, RIGHT OR BOTH SIDES




RIGHT SIDE VIEW

SEE PDU BRACKET DETAIL



PDU BRACKET DETAIL

- 42RU - 185 [7.3]
- 45RU - 318 [12.5]
- 48RU - 452 [17.8]
- 52RU - 630 [24.8]



TOP VIEW

26 [1.0]


PDU MOUNTING SURFACE

REAR FACE OF E-RAIL

- 600mm 47 [1.9]
- 700mm 97 [3.8]
- 800mm 147 [5.8]




DETAIL

PDU BRACKETS

TITLE		FLEXFUSION™ CABINET FAMILY		
		CUSTOMER DRAWING		
ITEM REVISION NAME		00460NXB/04		PANDUIT
DATASET FILE NAME		00460NXB_DC/04A		
		MATERIAL:		N/A
		DRAWING NUMBER:		00460NXB-DC
		THIRD ANGLE PROJECTION		
DRAWN BY	DATE	CHK	SCALE	SIZE
LEE	1/5/2021	SSP	NONE	A
REV		DATE		BY
00A		1/5/2021		LEE
DESCRIPTION		ECN		
DRAWING RELEASE		V09002FD/00		
SEE SHEET ONE OF 12 FOR REVISIONS		V09002FD/02		
SEE SHEET ONE OF 12 FOR REVISIONS		V09002FD/03		
SEE SHEET 1 FOR REVISIONS		V09002FD/04		
SEE SHEET 1 FOR REVISIONS		V09002FD/05		
SEE SHEET 1 FOR REVISIONS		V09002FD/06		

D101000A/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DETAIL A
OPTIONAL-NOT INCLUDED
VERTICAL CABLE MANAGER PANEL OPTIONS


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00

TITLE FLEXFUSION™ CABINET FAMILY						
CUSTOMER DRAWING						
ITEM REVISION NAME 00460NXB/04					PANDUIT	
DATASET FILE NAME 00460NXB_DC/04A						
DRAWING NUMBER: 00460NXB-DC					MATERIAL: N/A	
DRAWN BY LEE			DATE 1/5/2021		THIRD ANGLE PROJECTION	
CHK SSP			SCALE NONE		DRAWING NUMBER: SHT 6 OF 12	
					SIZE A	

D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DESCRIPTION	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"
	LEVELING LEGS		FLOOR MOUNT		FLOOR OPENING	
FLEX FUSION™ 600mm WIDE X 1070mm DEEP	462 (18.2)	1010 (39.8)	390 (15.4)	744 (29.3)	792 (31.2)	553 (21.2)
FLEX FUSION™ 600mm WIDE X 1200mm DEEP	462 (18.2)	1160 (45.7)	390 (15.4)	894 (35.2)	942 (37.1)	553 (21.2)
FLEX FUSION™ 700mm WIDE X 1070mm DEEP	562 (22.1)	1010 (39.8)	490 (19.3)	744 (29.3)	792 (31.2)	653 (25.7)
FLEX FUSION™ 700mm WIDE X 1200mm DEEP	562 (22.1)	1160 (45.7)	490 (19.3)	894 (35.2)	942 (37.1)	653 (25.7)
FLEX FUSION™ 800mm WIDE X 1070mm DEEP	662 (26.1)	1010 (39.8)	590 (23.2)	744 (29.3)	792 (31.2)	753 (29.7)
FLEX FUSION™ 800mm WIDE X 1200mm DEEP	662 (26.1)	1160 (45.7)	590 (23.2)	894 (35.2)	942 (37.1)	753 (29.7)



FLOOR MOUNTING HOLE LOCATIONS - SOME PARTS REMOVED FOR CLARITY

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02
00A	1/5/21	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00

TITLE		FLEXFUSION™ CABINET FAMILY	
CUSTOMER DRAWING			
ITEM REVISION NAME	00460NXB/04	PANDUIT	
DATASET FILE NAME	00460NXB_DC/04A		
MATERIAL:		N/A	
DRAWING NUMBER:		00460NXB-DC	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
LEE	1/5/2021	SSP	NONE
SHT 7 OF 12		A	

D101000A/16


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FRONT AND REAR E-RAIL POSITION RANGE

WIDTH	DEPTH	FRONT OF FRAME TO FRONT RAIL	FRONT TO REAR RAIL SPAN
600	1070	64mm (2.5")	154mm TO 915mm / (6.1" TO 36.0")
600	1200	64mm (2.5")	154mm TO 1065mm / (6.1" TO 42.0")
700	1070	64mm (2.5")	166mm TO 915mm / (6.5" TO 36.0")
700	1200	64mm (2.5")	166mm TO 1065mm / (6.5" TO 42.0")
800	1070	64mm (2.5")	166mm TO 915mm / (6.5" TO 36.0")
800	1200	64mm (2.5")	166mm TO 1065mm / (6.5" TO 42.0")

NOTE: MAXIMUM E-RAIL SPAN ONLY POSSIBLE IF NO VERTICAL CABLE MANAGEMENT FINGERS OR PDU BRACKETS ARE INSTALLED

04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00

TITLE		FLEXFUSION™ CABINET FAMILY	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		00460NXB/04	PANDUIT
		00460NXB_DC/04A	
DRAWING NUMBER:		N/A	
DRAWING NUMBER:		00460NXB-DC	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
LEE	1/5/2021	SSP	NONE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TOP CAP BEZELS AND COVERS COMPATABILITY - 600, 700 & 800

DEPTH	# OF CABLE OPENINGS	SIZE OF CABLE OPENING	COMPATIBLE WITH COOL BOOT-SOLD SEPARATELY
1070	8	83mm [3.3] X 120mm [4.7]	CTGN3X5
1200	10	83mm [3.3] X 120mm [4.7]	CTGN3X5

TOP CAP BRUSH COMPATABILITY - 600, 700 & 800

DEPTH	# OF CABLE OPENINGS	SIZE OF CABLE OPENING	REPLACEMENT BRUSH KIT
1070	2	87mm [3.4] X 600mm [23.6]	XG-TCBS1B or XG-TCBS1W
1200	2	87mm [3.4] X 750mm [29.5]	XG-TCBS2B or XG-TCBS2W

TOP CAP HATCH BRUSH OPENING - 600, 700 & 800

DEPTH	# OF HATCH BRUSH OPENINGS	HATCH BRUSH OPENING
1070 OR 1200	3	(1) 170 [6.7] X 59 [2.3] (2) 169 [6.7] X 56 [2.2]

TOP CAP HATCH OPENING - 1070 & 1200 DEPTH

WIDTH	REAR SIDE HATCH OPENING
600	284mm X 548mm (11.2 X 23.0)
700	284mm X 648mm (11.2 X 25.5)
800	284mm X 748mm (11.2 X 29.5)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00

TITLE		FLEXFUSION™ CABINET FAMILY	
		CUSTOMER DRAWING	
ITEM REVISION NAME		00460NXB/04	
DATASET FILE NAME		00460NXB_DC/04A	
		PANDUIT	
		MATERIAL:	
		N/A	
		DRAWING NUMBER:	
		00460NXB-DC	
DRAWN BY		DATE	
LEE		1/5/2021	
CHK		SCALE	
SSP		NONE	
SHT 9 OF 12		A	

D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
XG64212*	FLEXFUSION™ CABINET 600mm X 42RU X 1070mm DEEP W/SIDE PANELS	125 Kg/EACH 276 LBS/EACH	145 Kg/EACH 320 LBS/EACH
XG64219*	FLEXFUSION™ CABINET 600mm X 42RU X 1070mm DEEP W/O SIDE PANELS	89 Kg/EACH 196 LBS/EACH	109 Kg/EACH 240 LBS/EACH
XG64512*	FLEXFUSION™ CABINET 600mm X 45RU X 1070mm DEEP W/SIDE PANELS	132 Kg/EACH 292 LBS/EACH	152 Kg/EACH 336 LBS/EACH
XG64519*	FLEXFUSION™ CABINET 600mm X 45RU X 1070mm DEEP W/O SIDE PANELS	93 Kg/EACH 206 LBS/EACH	113 Kg/EACH 250 LBS/EACH
XG64812*	FLEXFUSION™ CABINET 600mm X 48RU X 1070mm DEEP W/SIDE PANELS	138 Kg/EACH 304 LBS/EACH	158 Kg/EACH 348 LBS/EACH
XG64819*	FLEXFUSION™ CABINET 600mm X 48RU X 1070mm DEEP W/O SIDE PANELS	96 Kg/EACH 213 LBS/EACH	116 Kg/EACH 257 LBS/EACH
XG65212*	FLEXFUSION™ CABINET 600mm X 52RU X 1070mm DEEP W/SIDE PANELS	147 Kg/EACH 323 LBS/EACH	167 Kg/EACH 368 LBS/EACH
XG65219*	FLEXFUSION™ CABINET 600mm X 52RU X 1070mm DEEP W/O SIDE PANELS	102 Kg/EACH 224 LBS/EACH	122 Kg/EACH 269 LBS/EACH
XG64222*	FLEXFUSION™ CABINET 600mm X 42RU X 1200mm DEEP W/SIDE PANELS	133 Kg/EACH 292 LBS/EACH	153 Kg/EACH 337 LBS/EACH
XG64229*	FLEXFUSION™ CABINET 600mm X 42RU X 1200mm DEEP W/O SIDE PANELS	91 Kg/EACH 201 LBS/EACH	112 Kg/EACH 246 LBS/EACH
XG64522*	FLEXFUSION™ CABINET 600mm X 45RU X 1200mm DEEP W/SIDE PANELS	142 Kg/EACH 313 LBS/EACH	162 Kg/EACH 358 LBS/EACH
XG64529*	FLEXFUSION™ CABINET 600mm X 45RU X 1200mm DEEP W/O SIDE PANELS	98 Kg/EACH 216 LBS/EACH	118 Kg/EACH 261 LBS/EACH
XG64822*	FLEXFUSION™ CABINET 600mm X 48RU X 1200mm DEEP W/SIDE PANELS	148 Kg/EACH 326 LBS/EACH	168 Kg/EACH 371 LBS/EACH
XG64829*	FLEXFUSION™ CABINET 600mm X 48RU X 1200mm DEEP W/O SIDE PANELS	101 Kg/EACH 223 LBS/EACH	122 Kg/EACH 268 LBS/EACH
XG65222*	FLEXFUSION™ CABINET 600mm X 52RU X 1200mm DEEP W/SIDE PANELS	157 Kg/EACH 346 LBS/EACH	177 Kg/EACH 391 LBS/EACH
XG65229*	FLEXFUSION™ CABINET 600mm X 52RU X 1200mm DEEP W/O SIDE PANELS	106 Kg/EACH 235 LBS/EACH	127 Kg/EACH 280 LBS/EACH

* DENOTES COLOR
 "B" = BLACK
 "W" = WHITE

ABOVE WEIGHTS ARE CABINET THAT INCLUDES SINGLE HINGED FRONT DOOR, SPLIT HINGED REAR DOOR, 1 SET OF PDU BRACKETS AND CASTERS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER	SIZE
04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06	LEE	1/5/2021	SSP	NONE	SHT 10 OF 12	A
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05						
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04						
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03						
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02						
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00						

TITLE
FLEXFUSION™ CABINET FAMILY
 CUSTOMER DRAWING


ITEM REVISION NAME
00460NXB/04

DATASET FILE NAME
00460NXB_DC/04A

MATERIAL:
N/A

DRAWING NUMBER:
00460NXB-DC

THIRD ANGLE PROJECTION



D10100DA/20

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
XG74212*	FLEXFUSION™ CABINET 700mm X 42RU X 1070mm DEEP W/SIDE PANELS	143 Kg/EACH 315 LBS/EACH	166 Kg/EACH 367 LBS/EACH
XG74219*	FLEXFUSION™ CABINET 700mm X 42RU X 1070mm DEEP W/O SIDE PANELS	106 Kg/EACH 234 LBS/EACH	130 Kg/EACH 286 LBS/EACH
XG74512*	FLEXFUSION™ CABINET 700mm X 45RU X 1070mm DEEP W/SIDE PANELS	151 Kg/EACH 332 LBS/EACH	174 Kg/EACH 384 LBS/EACH
XG74519*	FLEXFUSION™ CABINET 700mm X 45RU X 1070mm DEEP W/O SIDE PANELS	112 Kg/EACH 246 LBS/EACH	135 Kg/EACH 298 LBS/EACH
XG74812*	FLEXFUSION™ CABINET 700mm X 48RU X 1070mm DEEP W/SIDE PANELS	157 Kg/EACH 346 LBS/EACH	181 Kg/EACH 398 LBS/EACH
XG74819*	FLEXFUSION™ CABINET 700mm X 48RU X 1070mm DEEP W/O SIDE PANELS	116 Kg/EACH 255 LBS/EACH	139 Kg/EACH 307 LBS/EACH
XG75212*	FLEXFUSION™ CABINET 700mm X 52RU X 1070mm DEEP W/SIDE PANELS	167 Kg/EACH 368 LBS/EACH	192 Kg/EACH 421 LBS/EACH
XG75219*	FLEXFUSION™ CABINET 700mm X 52RU X 1070mm DEEP W/O SIDE PANELS	122 Kg/EACH 270 LBS/EACH	147 Kg/EACH 323 LBS/EACH
XG74222*	FLEXFUSION™ CABINET 700mm X 42RU X 1200mm DEEP W/SIDE PANELS	153 Kg/EACH 338 LBS/EACH	181 Kg/EACH 399 LBS/EACH
XG74229*	FLEXFUSION™ CABINET 700mm X 42RU X 1200mm DEEP W/O SIDE PANELS	112 Kg/EACH 248 LBS/EACH	140 Kg/EACH 309 LBS/EACH
XG74522*	FLEXFUSION™ CABINET 700mm X 45RU X 1200mm DEEP W/SIDE PANELS	161 Kg/EACH 354 LBS/EACH	188 Kg/EACH 415 LBS/EACH
XG74529*	FLEXFUSION™ CABINET 700mm X 45RU X 1200mm DEEP W/O SIDE PANELS	117 Kg/EACH 257 LBS/EACH	144 Kg/EACH 318 LBS/EACH
XG74822*	FLEXFUSION™ CABINET 700mm X 48RU X 1200mm DEEP W/SIDE PANELS	167 Kg/EACH 369 LBS/EACH	195 Kg/EACH 430 LBS/EACH
XG74829*	FLEXFUSION™ CABINET 700mm X 48RU X 1200mm DEEP W/O SIDE PANELS	121 Kg/EACH 266 LBS/EACH	148 Kg/EACH 327 LBS/EACH
XG75222*	FLEXFUSION™ CABINET 700mm X 52RU X 1200mm DEEP W/SIDE PANELS	177 Kg/EACH 392 LBS/EACH	206 Kg/EACH 453 LBS/EACH
XG75229*	FLEXFUSION™ CABINET 700mm X 52RU X 1200mm DEEP W/O SIDE PANELS	127 Kg/EACH 280 LBS/EACH	156 Kg/EACH 343 LBS/EACH

* DENOTES COLOR
 "B" = BLACK
 "W" = WHITE

ABOVE WEIGHTS ARE CABINET THAT INCLUDES SINGLE HINGED FRONT DOOR, SPLIT HINGED REAR DOOR, 1 SET OF PDU BRACKETS AND CASTERS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER	SIZE
04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06	LEE	1/5/2021	SSP	NONE	SHT 11 OF 12	A
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05						
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04						
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03						
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02						
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00						

TITLE
FLEXFUSION™ CABINET FAMILY
 CUSTOMER DRAWING


ITEM REVISION NAME
00460NXB/04

DATASET FILE NAME
00460NXB_DC/04A

MATERIAL:
N/A

DRAWING NUMBER:
00460NXB-DC

THIRD ANGLE PROJECTION




D10100DA/20

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
XG84212*	FLEXFUSION™ CABINET 800mm X 42RU X 1070mm DEEP W/SIDE PANELS	153 Kg/EACH 338 LBS/EACH	177 Kg/EACH 390 LBS/EACH
XG84219*	FLEXFUSION™ CABINET 800mm X 42RU X 1070mm DEEP W/O SIDE PANELS	117 Kg/EACH 257 LBS/EACH	140 Kg/EACH 309 LBS/EACH
XG84512*	FLEXFUSION™ CABINET 800mm X 45RU X 1070mm DEEP W/SIDE PANELS	160 Kg/EACH 353 LBS/EACH	184 Kg/EACH 405 LBS/EACH
XG84519*	FLEXFUSION™ CABINET 800mm X 45RU X 1070mm DEEP W/O SIDE PANELS	121 Kg/EACH 267 LBS/EACH	145 Kg/EACH 319 LBS/EACH
XG84812*	FLEXFUSION™ CABINET 800mm X 48RU X 1070mm DEEP W/SIDE PANELS	167 Kg/EACH 369 LBS/EACH	191 Kg/EACH 421 LBS/EACH
XG84819*	FLEXFUSION™ CABINET 800mm X 48RU X 1070mm DEEP W/O SIDE PANELS	126 Kg/EACH 278 LBS/EACH	150 Kg/EACH 330 LBS/EACH
XG85212*	FLEXFUSION™ CABINET 800mm X 52RU X 1070mm DEEP W/SIDE PANELS	178 Kg/EACH 393 LBS/EACH	202 Kg/EACH 446 LBS/EACH
XG85219*	FLEXFUSION™ CABINET 800mm X 52RU X 1070mm DEEP W/O SIDE PANELS	134 Kg/EACH 294 LBS/EACH	157 Kg/EACH 347 LBS/EACH
XG84222*	FLEXFUSION™ CABINET 800mm X 42RU X 1200mm DEEP W/SIDE PANELS	163 Kg/EACH 359 LBS/EACH	190 Kg/EACH 420 LBS/EACH
XG84229*	FLEXFUSION™ CABINET 800mm X 42RU X 1200mm DEEP W/O SIDE PANELS	122 Kg/EACH 268 LBS/EACH	149 Kg/EACH 329 LBS/EACH
XG84522*	FLEXFUSION™ CABINET 800mm X 45RU X 1200mm DEEP W/SIDE PANELS	170 Kg/EACH 375 LBS/EACH	198 Kg/EACH 436 LBS/EACH
XG84529*	FLEXFUSION™ CABINET 800mm X 45RU X 1200mm DEEP W/O SIDE PANELS	126 Kg/EACH 278 LBS/EACH	154 Kg/EACH 339 LBS/EACH
XG84822*	FLEXFUSION™ CABINET 800mm X 48RU X 1200mm DEEP W/SIDE PANELS	178 Kg/EACH 392 LBS/EACH	205 Kg/EACH 453 LBS/EACH
XG84829*	FLEXFUSION™ CABINET 800mm X 48RU X 1200mm DEEP W/O SIDE PANELS	131 Kg/EACH 289 LBS/EACH	159 Kg/EACH 350 LBS/EACH
XG85222*	FLEXFUSION™ CABINET 800mm X 52RU X 1200mm DEEP W/SIDE PANELS	189 Kg/EACH 416 LBS/EACH	217 Kg/EACH 478 LBS/EACH
XG85229*	FLEXFUSION™ CABINET 800mm X 52RU X 1200mm DEEP W/O SIDE PANELS	139 Kg/EACH 305 LBS/EACH	166 Kg/EACH 367 LBS/EACH

* DENOTES COLOR
 "B" = BLACK
 "W" = WHITE

ABOVE WEIGHTS ARE CABINET THAT INCLUDES SINGLE HINGED FRONT DOOR, SPLIT HINGED REAR DOOR, 1 SET OF PDU BRACKETS AND CASTERS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	MATERIAL	DRAWING NUMBER
							FLEXFUSION™ CABINET FAMILY				
							CUSTOMER DRAWING				
04A	1/30/23	HBO	FWI	FWI	SEE SHEET 1 FOR REVISIONS	V09002FD/06		00460NXB/04		PANDUIT	
03A	11/15/22	MEX-JAGC	MCIS	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/05		00460NXB_DC/04A			
02A	8/4/22	MEX-JAGC	BRAP	ELE	SEE SHEET 1 FOR REVISIONS	V09002FD/04				N/A	
01B	9/13/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/03					
01A	7/27/2021	MES	BRAP	ELE	SEE SHEET ONE OF 12 FOR REVISIONS	V09002FD/02					
00A	1/5/2021	LEE	SSP	ELE	DRAWING RELEASE	V09002FD/00					00460NXB-DC
											
							THIRD ANGLE PROJECTION				
							DRAWN BY	DATE	CHK	SCALE	
							LEE	1/5/2021	SSP	NONE	
											SHT 12 OF 12
											A

D10100DA/20