


# High Temperature Polyetheretherketone (PEEK) Cable Ties and Mounts

PEEK Cable Ties and mount are ideal for use in high temperature and harsh chemical environments. PEEK is a dimensionally stable material that offers an excellent tensile rating with an operating temperature up to 464°F (240°C). It is halogen free, generating low smoke and toxicity upon burn, contributing to improved workplace safety. It has excellent chemical resistance to almost all organic and inorganic chemicals and is extremely resistant to high levels of gamma radiation for a long-term bundling solution. PEEK cable ties and mount can be used in a broad range of applications and environments including Oil and Gas, Automotive and Aerospace.



## KEY FEATURES AND BENEFITS

<b>High Temperature Polyetheretherketone (PEEK) material:</b>	Operating temperature range up to 464°F (240°C); maintains good tensile strength in high temperature environments
<b>Chemical resistant material:</b>	Withstands attack from most organic and inorganic chemicals; able to be used in harsh chemical environments, providing a long-term bundling solution
<b>Gamma radiation resistant material:</b>	Maintains mechanical properties when exposed to high levels of gamma radiation; maintains tensile properties, providing longer useful life
<b>Good electrical isolation properties:</b>	Non-metallic material provides an alternative to conductive fasteners; safe to use where a non-conductive material is specified and/or required
<b>Low water absorption:</b>	Non-hygroscopic material provides excellent moisture resistance; won't absorb water in humid/steam environments; maintains dimensional stability and tensile strength

## CABLE TIE

<b>Cable tie design:</b>	Threads easily and installs quickly compared to lacing cord, which requires time consuming, hand-tied knots that can lead to repetitive strain injuries
<b>Curved tip – applicable sizes:</b>	Easy to pick up from flat surfaces; allows faster threading

## TECHNICAL INFORMATION

<b>Oxygen index:</b>	35
<b>Radiation resistance:</b>	1 x 10 <sup>9</sup> Rads
<b>Continuous use temperature:</b>	-76° – 464°F (-60° – 240°C)
<b>Halogen free:</b>	Yes
<b>RoHS compliant:</b>	Yes
<b>Military specification:</b>	Yes, MS3367-1-16 and MS3367-4-16

## MOUNT

<b>Low profile design:</b>	Keeps bundle close to mounting surface where overhead space is limited
<b>Mount cradle design:</b>	Provides maximum stability for the cable bundle

## APPLICATIONS

Applications for PEEK product include, but are not limited to, the following:


- Drilling down-hole electronics
- Nuclear power plants
- Vacuum ovens for optics
- Commercial cooking equipment
- High temperature lighting
- Industrial ovens
- Transformers and transducers
- Wire harnesses for harsh environments
- Chemical manufacturing
- Transportation

# High Temperature Polyetheretherketone (PEEK) Cable Ties and Mounts

## CABLE TIES ORDERING INFORMATION

Part Number	Length In.(mm)	Width In.(mm)	Thickness In.(mm)	Head Height In.(mm)	Head Width In.(mm)	Max. Bundle Diameter In.(mm)	Min. Loop Tensile Strength Lbs.(N)	Recommended Tools	Std. Pkg. Qty.	Std. Ctn. Qty.
<b>Miniature Cross Section</b>										
<b>PLT1M-C71</b>	4.0 (101.6)	0.101 (2.6)	0.048 (1.2)	0.130 (3.3)	0.190 (4.8)	0.87 (22)	35 (156)	<b>GTS-E, GS2B-E, PTS</b>	100	1000
<b>PLT1.5M-C71</b>	5.90 (149.9)	0.101 (2.6)		0.130 (3.3)	0.190 (4.8)	1.38 (35)			100	1000
<b>Standard Cross Section (Straight Tip)</b>										
<b>PLT2S-C71</b>	7.4 (188)	0.190 (4.8)	0.055 (1.4)	0.240 (6.1)	0.320 (8.1)	1.88 (48)	150 (668)	<b>GTS-E, GTH-E, GS2B-E, GS4H-E, PTS, PTH</b>	100	1000

## CABLE TIE MOUNTS ORDERING INFORMATION



Part Number	Used With Cable Ties	A Width In.(mm)	B Width In.(mm)	C Height In.(mm)	Counterbore Diameter In.(mm)	Mounting Method	Std. Pkg. Qty.*	Std. Ctn. Qty.*
<b>TM2S8-C71</b>	Min., Std.	0.636 (16.2)	0.427 (10.8)	0.278 (7.1)	0.335 (8.5)	#8 (M4) screw	100	500

## RELATED PRODUCTS



Part Numbers	Used with PEEK Cable Ties	Description	Std. Pkg. Qty.
<b>Tool Controlled Tension and Cut-Off Tools</b>			
<b>GTS-E, GS2B-E</b>	Miniature, Standard	Tool controlled tension tools consistently provide flush tie cut-offs to speed installation.	1
<b>GTH-E, GS4H-E</b>	Standard		1

\*Order number of pieces required, in multiples of standard package quantity.

### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)  
Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT**<sup>®</sup>

© 2024 Panduit Corp.  
ALL RIGHTS RESERVED.  
FRCB34-WW-ENG  
3/2024