

REV DATE BY CHK APR

DESCRIPTION

CAP REW PORT) QTY.	CAP (WIREPORT) QTY.	А	L	Ν	TIG HTEN IN G TO R Q U E
2	4	2.72	2.469	2	
3	6	4.00	3.750	3	
4	8	5.28	5.031	4	375 in/1b
5	10	6.56	6.312	5	
6	12	7.84	7.593	6	
8	16	10.41	10.155	8	
10	2 0	12.97	12.717	10	
12	2 4	15.53	15.279	12	
14	2 8	18.0 9	17.841	14	

1. UL486A-UL486B LISTED, DUAL RATED CU9AL FOR ALUMINUM OR COPPER CONDUCTORS. MEETS OR EXCEEDS ANSI C119.4

2. SEE TABLE FOR WIRE RANGE.

3. STRIP LENGTH: 1.06 +.06/-0

4. FOR TIGHTENING TORQUE SEE TABLE

5. VOLTAGE RATING: 600 V. MAX. BUILDING WIRE, 1000 V. MAX. IN SIGNS & FIXTURES.

6. TEMPERATURE RATING: 90°C (CU9AL).

7. CONNECTOR BLOCK BODY ARE MADE FROM ALUMINUM. CONDUCTOR PORTS IN CONNECTOR BLOCK ARE PREFILLED WITH AN OXIDE-INHIBITING COMPOUND.

8. CONNECTOR TO INCLUDE TIN PLATED ALUMINUM CLAMPING SCREWS FOR EACH CONDUCTOR PORT.

9. INSULATION MATERIAL IS CLEAR PVC.

10. CLAMPING SCREW ACCESS PORTS AND ALL WIRE ENTRY PORTS ARE PROVIDED WITH REMOVABLE PLASTIC CLOSURE PLUGS.

11. ALL DIMENSIONS SHOWN ARE NOMINAL.

12. ONLY ONE CONDUCTOR PER PORT ALLOWED.

13. PACKAGE QTY: -12 = 12 PCS. -6 = 6 PCS.-4 = 4 PCS.

ECN

14. THIS PART IS ROHS COMPLIANT.

MULTI-TAP INSULATED CONNECTORS PCSB600 SERIES CUSTOMER DRAWING										
ITEM REVISION NAME	N41530BB-C4	30BB-C41531/07								
DATASET FILE NAME	C41530/07.S	LDDRW	I 7 AN	DUIT						
UNLESS OTH DIMENSIONAL TOL .X ±	material SEE NOTES									
.XX ± .02	ANGLES : THIRD	<u>+</u> ANGLE	DRAWING NUMBER	0.41500	07					
DRAWN BY DATE		CTION	C41530_07							
	B/99 RLS	NONE	SHEET	1 OF 1	B					