


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
PEV12	54.7 LBS/EACH (24.9 kg/EACH)

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) 12" DUAL-SIDE VERTICAL MANAGER
(1) HARDWARE KIT
(2) FINGER KITS
(4) DOOR BRACKET BASES
- CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK.
- 3 ROWS OF 6RU 19" CEA OPENINGS (18 TOTAL RU, 6 RU'S WITH LIMITED DEPTH)
- 12" DOOR SOLD SEPARATELY (P/N: PED12B1)
- DIMENSIONS IN PARENTHESIS ARE METRIC.
- ALL DIMENSIONS ARE REFERENCE ONLY.

TITLE PATCHRUNNER HIGH CAPACITY VERTICAL MANAGER 12" WIDE, DUAL-SIDED (PEV12) CONTROL DRAWING		PANDUIT
ITEM REVISION NAME 09V054AG/10	MATERIAL: BACKBONE- STEEL FINGERS- ABS	
DATASET FILE NAME 09V054AG_DC/10A		DRAWING NUMBER: 09V054AG-DC
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		
THIRD ANGLE PROJECTION	DRAWING NUMBER: 09V054AG-DC	
DRAWN BY BAME	DATE 1/6/09	CHK NAGL
SCALE NONE	SHT 1 OF 1	
SIZE A		

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
10A	3-1-17	TWW	KZU	JEFK	REPLACED P/N PED12 WITH PED12B1 IN NOTE #5	09V054AG-DC
09A	7/21/16	AMF	KZU	KRKE	REMOVED DOOR BRACKETS	09054AG-DC

D10100DA/15