Push Mounts and Assemblies



specifications

Fasteners for automotive wire harnesses shall provide fifty pounds of pull-out force with no more than 45° maximum rotation of the installed bundle. When installed in the panel, the fastening method shall firmly retain a minimum wire gauge of 12 AWG within \pm 10mm (.394") of the initial installation point. The mounts shall require no more than 14 pounds of insertion force. Mounts with wider cable tie slot capability may have a proportionately higher insertion and pull-out capability. Mounts shall be self-tensioning to prevent rattles and degradation of the mount over the life of the vehicle. The material for the mounts and the cable ties shall be heat stabilized Nylon 6.6, black. Application temperature range shall be -60°C to 115°C (-76°F to 239°F).



technical information

Material:	Heat Stabilized Nylon 6.6							
Flammability:	Meets UL94 V-2, passes FMVSS 302							
Color:	Black							
Application temperature range:	-60°C to 115°C (-76°F to 239°F) continuous							
Chemical resistance at 21°C (70 °F):	Excellent resistance to common transportation fluids including: ethylene glycol, gasoline, jet fuel, hydraulic fluid, transmission fluids and 10% sodium chloride solution							
Insertion force:	14 pounds maximum*							
Environmental compliance:	Meets 2000/53/EC ELV and 2002/95/EC RoHS standards and all industry standards for hazardous material content							

^{*}Insertion force for PUM-925 is 30 pounds at nominal hole size.

key features and benefits

Unique alternating barb design:	Provides increased retention and lower insertion force, reducing operator fatigue and improving productivity						
Umbrella fir tree design:	Locks securely into position and can be rotated 360 degrees, giving you a wider application range than fixed barb designs; also seals against dust and moisture						
Exclusive contoured anvil head:	Firmly retains a minimum wire gauge of 12 AWG (2mm \emptyset) within \pm 10mm (.394") of the initial installation point, providing a low profile design						
Assemblies with PLT cable ties:	Provide routing and anchoring for wire harnesses, significantly reducing harness assembly time						
Production Parts Approval Process (PPAP), 3-D, and International Materials Data Sheet (IMDS) capability:	Meets the needs of Verband der Automobilindustrie (VDA) and Automotive Industry Action Group (AIAG) compliant documentation, allowing parts to be listed to IMDS site ID						

applications

PANDUIT push mounts with umbrellas and push mount assemblies are a reliable and cost effective solution for securing wire harnesses in the automotive, marine, white goods, heavy equipment and mass transit-rail markets. Designed for 4.6mm to 10.0mm through holes and variable panel thicknesses, the push mounts insert easily and exceed

manufacturers' requirements for primary anchors of wire harnesses. The PANDUIT push mounts with umbrellas are compatible with all standard PANDUIT Cable Ties up to the standard 50 pound loop tensile ties. The PUM-925-M30 mount has expanded slot capability which allows the use of the 120 pound loop tensile Light-Heavy cable ties.

Push Mounts with Umbrella

4.6mm – 4.9mm (.18" – .19") panel hole

PUM-049-M30

6.3mm – 7.1mm (.25" – .28") panel hole diameter range:

diameter range:

nge: PUM-071-M30

9.0mm - 10.0mm (.35" - .40") panel hole

diameter range: PUM-100-M30

8.8mm - 9.3mm (.34" - .36") panel hole diameter range:

PUM-925-M30

Push Mount Assemblies with Panduit® Cable Ties

4.6mm – 4.9mm (.18" – .19") panel hole

diameter range: PUM-049-2S-D30

6.3mm - 7.1mm (.25" - .28") panel hole diameter range: 9.0mm - 10.0mm

PUM-071-2S-D30

(.35" – .40") panel hole diameter range

diameter range: PUM-100-2S-D30

8.8mm – 9.3mm (.34" – .36") panel hole

diameter range: PUM-925-3H-T30

Push Mount Assembly with DOME-TOP® Barb Ty Cable Tie


6.3mm – 7.1mm (.25" – .28") panel hole


diameter range: PUM-071-B2S-D30


Push Mounts and Assemblies

Push Mounts with Umbrella

	Used With		Panel to Top of Mount B		Overall Height C		Hole Size Range		Panel Thickness Range		Std. Pkg	Bulk Pkg
Part Number	Cable Ties	In. (mm)	ln.	mm	ln.	mm	ln.	mm	ln.	mm	Qty.	Qty.
PUM-049-M30	Miniature	.67 (17)	.26	6.6	.54	13.8	.18 – .19	4.6 – 4.9	.03 – .19	.7 – 3.0	1000	5000
PUM-071-M30	Intermediate,	.67 (17)	.26	6.5	.67	16.9	.25 – .28	6.3 – 7.1	.03 – .28	.8 – 7.0	1000	5000
PUM-100-M30	Standard	.64 (16)	.26	6.6	.67	16.9	.35 – .40	9.0 – 10.0	.03 – .28	.8 – 7.0	1000	5000
PUM-925-M30	Miniature Intermediate, Standard, Light-Heavy	.77 (20)	.30	7.6	1.05	26.7	.34 – .36	8.8 – 9.3	.04 – .62	1.0 – 16.0	1000	5000








Push Mount Assemblies

	Footprint	Max. Bundle Diameter		Panel to Top of Mount		Overall Height		Hole Size Range		Panel Thickness Range		Std. Pkg	Bulk Pkg
Part Number	ln. (mm)	ln.	mm	ln.	mm	ln.	mm	ln.	mm	ln.	mm	Qty.	Qty.
PUM-049-2S-D30*	.67 (17)	1.88	48	.26	6.6	.54	13.8	.18 – .19	4.6 – 4.9	.03 – .19	.7 – 3.0	500	5000
PUM-071-2S-D30*	.67 (17)	1.88	48	.26	6.5	.67	16.9	.25 – .28	6.3 – 7.1	.03 – .28	.8 – 7.0	500	5000
PUM-100-2S-D30*	.64 (16)	1.88	48	.26	6.6	.67	16.9	.35 – .40	9.0 – 10.0	.03 – .28	.8 – 7.0	500	5000
PUM-925-3H-T30**	.77 (20)	3.00	76	.30	7.6	1.05	26.7	.34 – .36	8.8 – 9.3	.04 – .62	1.0 – 16.0	200	1000
PUM-071-B2S-D30***	.67 (17)	2.00	51	.26	6.6	.67	16.9	.25 – .28	6.3 – 7.1	.03 – .28	.8 – 7.0	500	5000

^{*}PLT2S cable tie included in assembly. This cable tie is manufactured with heat stabilized, black Nylon 6.6 and is approved for continuous use from -60°C to 115°C

^{(-76°}F to 239°F).

***BT2S cable tie included in assembly. This cable tie is manufactured with heat stabilized, black Nylon 6.6 and is approved for continuous use from -60°C to 115°C (-76°F to 239°F).



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300

PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 and reference WASP04

© 2020 Panduit Corp. ALL RIGHTS RESERVED. WW-WASP04 11/2020



^{(-76°}F to 239°F).
**PLT3H cable tie included in assembly. This cable tie is manufactured with heat stabilized, black Nylon 6.6 and is approved for continuous use from -60°C to 115°C