## **Short Circuit Warning Signs**

· Aids in compliance with UL 508A requirement



PPS0305W2201Y PPS0507W2201Y

### **Material Chart**

Material	Print Method	Temperature Range	Features
Polyester (PPS)	Pre-Printed	-40°F to 275°F (-40°C to 135°C)	Indoor/outdoor rated; laminated label material protects legend from abrasion and chemicals; resistant to resistant to UV light, chemical atmosphere, and abrasion; excellent life and adhesion properties.

### Size Reference Chart

Part	Width		Height		Signs Per	
Number	ln.	mm	ln.	mm	Card	
*0305*	5.00	127.00	3.00	76.20	5	
*0507*	7.00	177.80	5.00	127.00	5	
*0710*	10.00	254.00	7.00	177.80	1	
*1014*	14.00	355.60	10.00	254.00	1	
*1209*	9.00	228.60	12.00	304.80	1	

<sup>\*</sup>Denotes the part numbers' prefix and suffix.

### **Photoluminescent Safety Signs**

- Used to mark egress routes, fire alarms, and fire equipment that is clearly visible for up to ten hours after power is lost
- · Absorbs energy from ambient light and releases this energy in the form of a glow when power is lost
- Panduit Photoluminescent Signs meet or exceed the following safety standard specification for photoluminescent safety markings including: ASTM E 2072-00, ASTM E 2073-00, ASTM É 2030-99, DIN67510-1, IMO Resolution A.752.18, ISO/CD 15370, DIN 67510, UL 924, ASTM 162, ASTM 648, ASTM 662, MIL-L-3891 B, NFPA 101 Life Safety Code, OSHA 1910.37











PPS1209G012

# Electrical Symbols on Cards

#### **Material Chart**

Material	Print Method	Temperature Range	Features
Vinyl Cloth	Pre-Printed	-50°F to 170°F (-46°C to 77°C)	Indoor/outdoor rated; conformable material with repositionable adhesive allows label to be removed and reused or used in temporary applications; provides durability, high temperature resistance, and dimensional stability for rough or textured surfaces.

			Marker Size		Markers Per	Std. Pkg.	Std. Ctn.
Part Number	Symbol	Description	ln.	mm	Card	_	Card(s)
PESC-H-AT	4	WARNING OF DANGEROUS	0.51 x 0.51	13.00 x 13.00	68	10	100
PESC-J-AT		ELECTRICAL VOLTAGE	0.75 x 0.75	19.00 x 19.00	36	10	100
PESC-H-E	4	EARTH (GROUND)	0.51 x 0.51	13.00 x 13.00	68	10	200
PESC-J-E			0.75 x 0.75	19.00 x 19.00	36	10	100
PESC-H-EC		SAFETY FUNCTION	0.51 x 0.51	13.00 x 13.00	68	10	200
PESC-J-EC			0.75 x 0.75	19.00 x 19.00	36	10	100
PESC-H-HT		STATIC SENSITIVE DEVICE	0.51 x 0.51	13.00 x 13.00	68	10	100
PESC-J-HT		– HANDLING PRECAUTIONS REQUIRED	0.75 x 0.75	19.00 x 19.00	36	10	100
PESC-H-PE	PE	PROTECTIVE CONDUCTOR	0.51 x 0.51	13.00 x 13.00	68	10	100
PESC-J-PE			0.75 x 0.75	19.00 x 19.00	36	10	100

System Overview

B1. **Cable Ties** 

B2. Cable Accessories

**C1**. Wiring Duct

C2. Surface Raceway

СЗ. Abrasion Protection

C4. Cable Management

> D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

Labeling Systems E2. Labels **Pre-Printed** & Write-On Markers

F4. Permanent Identification Lockout/

F. Index