

18900 Panduit Drive Tinley Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMY4-HT 31AUG20

High Tack Thermal Transfer Printable Polyester Film

This specification is intended to outline the physical and chemical properties of PANDUIT's pressure sensitive high tack thermal transfer printable polyester material and include the following printable material identifiers:

| Printable Material Suffixes | | | | | |
|-----------------------------|-------|-------|------------------|--|--|
| YPT | YQT-P | YUT-P | Y9T-P | | |
| YPT-P | YRT-P | YVT-P | Y*1 | | |
| Y0T | YST-P | YWT-P | AJC (Flag Label) | | |
| Y0T-P | YTT-P | Y8T-P | AJT (Flag Label) | | |
| YPC | A*1 | | | | |

PRODUCT SPECIFICATIONS:

Description: Material is RoHS compliant (European Union directive

2002/95/EC). Material is a top coated polyester film with a

pressure sensitive adhesive.

Print Methods: This material is recommended for thermal transfer printing. Adhesive: Rubber based, pressure sensitive high tack permanent adhesive

Standard Colors: Various colors

Thickness: 3.9 + -0.3 mils (substrate and adhesive)

-40°F to 302°F (-40°C to 150°C) Service Temperature Range:

Minimum Application Temperature: 50°F (10°C)

Storage Conditions: Store at 70°F (21°C) and 50% Relative Humidity.

PROPERTIES: PERFORMANCE:

100 oz/in width minimum (PSTC-101, 15 min. dwell) Peel Adhesion to Stainless Steel: 24 hours minimum (PSTC-107, modified Procedure A) Shear Adhesion:

Tensile Strength: MD 36 +/- 3.6 lbs./inch width (PSTC-131) TD 41 +/- 4.1 lbs./inch width (PSTC-131)

MD 80% +/- 15% (PSTC-131) Elongation: TD 75% +/- 15% (PSTC-131)

UV Resistance: *3000 hours no visual change observed for both white and colored labels

(ASTM G154).

5000 hours no visual change observed for white but significant fade observed for colored labels but print still legible (ASTM G154). 10,000 hours slight yellowing observed for white, complete fade for

colored labels but print still legible (ASTM G154)

After 8 hours at 150°F (65.5°C) there was no deterioration of the substrate Elevated Temperature Exposure:

*3000 hours equates to 5 years of assimilated outdoor UV exposure.

Page 1 of 4

© 2020PANDUIT Corp TDS: GMY4-HT **Technical Data Sheet**

18900 Panduit Drive Tinley Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMY4-HT 31AUG20 11

PROPERTIES FOR SOLAR **PERFORMANCE:**

APPLICATION:

Short term low temperature exposure: 30 days at -51C, no visible change observed 30 days at 93C, no visible change observed Short term high temperature exposure:

Relative Lightfastness and weatherability: 1000 hours, no change observed (ASTM D3424, Method 4)

Tensile Strength: MD: 10114 PSI (ASTM D3759)

Elongation: MD: 90% (ASTM D3759) Tack: 12.6 N (ASTM D2979)

Flammability: 16 seconds (ASTM D1000) Adhesion: 154.0 oz/in (ASTM D3330)

CHEMICAL/SOLVENT RESISTANCE:

The testing was conducted at room temperature. Samples were orange/red (flexo) preprinted and thermal transfer printed with Panduit RMR*BL/RMER*BL ribbon on the Panduit TDP43MY/TDP43ME printer. Separate sets were conditioned for 24 hours before being immersed in the following solvents for a period of 1 hour and 24 hours. After the samples were removed from the immersed solvents, they were rubbed 10 times with a lint free gauze. Visual observations were noted for any smear or loss of legibility.

1 Hour Immersion

| Chemical/Solvent | Visual Observation | | |
|------------------------|--------------------------|------------------------|--|
| | Ribbon only | Colored Flexo Ink | |
| Jet Fuel | No change | No change | |
| Gasoline | Loss in print density | No change | |
| Methyl Ethyl Ketone | Loss in print density | Orange/red ink removed | |
| 1:1:1 TCE | Loss in print density | Orange ink removed | |
| Trichloroethylene | Loss in print legibility | Orange/red ink removed | |
| 409 Cleaner | No change | No change | |
| Alpha Flux 200L | No change | No change | |

Page 2 of 4 © 2020PANDUIT Corp

TDS: GMY4-HT

18900 Panduit Drive Tinley Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMY4-HT 31AUG20 11

24 Hours Immersion

| Chemical/Solvent | Visual Observation | | |
|-------------------|--------------------------|--------------------|--|
| | Ribbon only | Colored Flexo Ink | |
| Isopropyl Alcohol | No change | Orange ink removed | |
| Water 150°F | No change | No change | |
| Salt Water | No change | No change | |
| SAE 30 Motor Oil | No change | No change | |
| Hydraulic Fluid | No change | No change | |
| Skydrol | Loss in print legibility | Orange ink removed | |
| Methanol/Water | No change | No change | |
| Ethylene Glycol | No change | No change | |
| ASTM #3 Oil | No change | No change | |

Reference

American Society for Testing and Materials (U.S.A.) **ASTM:**

Pressure Sensitive Tape Council **PSTC**:

APPROVALS

UL Recognized: UL969 File number: MH 14979 CUL Recognized: C22.2 No 0.15-01 File number: MH 14979

Page 3 of 4 © 2020*PANDUIT* Corp

TDS: GMY4-HT



Technical Data Sheet

18900 Panduit Drive Tinley Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMY4-HT 31AUG20

PROPERTIES FOR HARSH WASHDOWN ENVIRONMENT (with overlaminate film)

Meets the requirements of Ingress protection rating standard DIN 40050-9, IP69K for labels used in harsh wash-down and high pressure spray applications, common to the food and beverage industries.

CHEMICAL RESISTANCE TEST:

Samples were printed with RMER4BL ribbon on Panduit TDP43ME printer and overlaminated with a clear film (T225X000YK1 or T425X000YK1). These samples were adhered to stainless steel panels and immersed in the following solvents. Testing consisted of 10 cycles of 10 minutes immersion followed by a 20 minute recovery period. After final immersion, visual observations were noted for any smear or loss of legibility.

| CHEMICAL/SOLVENT | TEMPERATURE | Print | Adhesive |
|-----------------------|-------------|-----------|-----------|
| Enforce LP | 50°C | No change | No change |
| HD PL-10 Plus | RT | No change | No change |
| Heavy Duty Acid LC-30 | 70°C | No change | No change |
| Soil Off II | 50°C | No change | No change |
| Madisan 75 | RT | No change | No change |
| Vortexx | 50°C | No change | No change |
| XY-12 | RT | No change | No change |

LIMITED WARRANTY

All PANDUIT Identification Solution Products (except for Software programs) are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to replacement of the product proved to be defective within 6 months from the date of sale, or in the case of printers, within 90 days from the date of sale. This warranty is void if the products or printers are modified, altered or misused in any way. Use of PANDUIT printers with any product other than the specified PANDUIT products for which the printer was designed constitutes misuse. Before using, the user shall determine the suitability of the product for its intended use and user assumes all risk and liability whatsoever in connection therewith. The foregoing may not be altered except by an agreement signed by officers or seller and manufacturer.

NEITHER PANDUIT OR SELLER SHALL BE LIABLE FOR ANY OTHER INJURY, LOSS OR DAMAGE, WHETHER DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OF, OR THE INABILITY TO USE THE PRODUCT OR THE PRINTER.

THIS WARRANTY IS MADE IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS OF PARTICULAR USE ARE SPECIFICALLY EXCLUDED.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide or use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. This publication is not to be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.

Page 4 of 4 © 2020PANDUIT Corp

TDS: GMY4-HT