Category 6A UTP Modular Plug for Vari-Matrix LSZH 23 AWG Solid Cable

SPECIFICATIONS

Category 6A/Class E_A , 8-position, 8-wire, UTP modular plug shall terminate Panduit PUL6AHD04*-G LSZH 4-pair, 23 AWG, 100 ohm, solid unshielded twisted pair cable with conductor insulation diameter range of 0.043 in. (1.09mm) to 0.047 in. (1.19mm) and jacket diameter range of 0.240 in. (6.10mm) to 0.260 in. (6.60mm).





Category 6A UTP LSZH 23 AWG100/pack:SP6X88LHD-CTools and AccessoriesTermination Tool:CSPTCrimp Tool:MPT5-8ASRJ45 Plug Lock-In
Device (Standard):PSL-DCPLE*RJ45 Plug Lock-In
Device (Recessed):PSL-DCPLRE*

*Colors other than Red: -BL (Black), -IW (Off White), -YL (Yellow), -OR (Orange)

TECHNICAL INFORMATION

Category 6A/Class E _A component performance:	Exceeds ANSI/TIA-568.2-D Category 6A and ISO 11801 Class E_A performance requirements when properly terminated to Panduit Category 6A UTP copper cable
Cable jacket diameter range:	0.240 in. (6.10mm) - 0.260 in. (6.60mm)
Conductor insulation diameter range:	0.043 in. (1.09mm) - 0.047 in. (1.19mm)
IEC compliance:	IEC-60603-7
PoE compliance:	Supports IEEE 802.3bt PoE, PoE+, and proposed Type 3 and 4 PoE++ applications for up to 100 W
RoHS compliance:	Compliant
Conductor termination:	Compatible with TX6A [™] Cat 6A Vari-MaTriX, 23 AWG, LSZH, UTP Copper Cable
Plug Housing:	UL94V-0 rated clear Polycarbonate
Contacts:	Gold plated phosphor bronze
Operating temperature:	14°F to 140°F (-10°C to 60°C)
Storage temperature:	-40°F to 158°F (-40°C to 70°C)

KEY FEATURES AND BENEFITS

Patented tangle-free latch:	Prevents snags and provides easy release, saving time and providing reliability on frequent moves, adds, and changes
Robust construction:	Rated to 2500 mating cycles


APPLICATIONS

Category 6A plugs allow customers to meet performance requirements in ISO 11801 Class E_A , IEEE 802.3an-2006 and ANSI/TIA-568.2-D Category 6A standards to support transmission at speeds up to and including 10GBASE-T. These plugs can be used in applications with data centers and connections to high end workstations such as stacking switches and switch-to-switch links, storage area networks, aggregation of Gigabit Ethernet channels, real-time intensive financial transactions, streaming video, animation, scientific modeling, and medical imaging.



All Part Numbers Compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to the United States.

ENGINEERING DRAWINGS



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2024 Panduit Corp. ALL RIGHTS RESERVED. COSP579-WW-ENG 01/2024