

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE WWW.PANDUIT.COM TO INDICATE PACKAGE QUANTITY.
2. SEE WWW.PANDUIT.COM FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. PRODUCT DESCRIPTION:
 - A. 1 LANE, 25 Gbps/LANE
 - B. STANDARD SFP CONNECTOR
 - C. CL2 RATED JACKET
 - D. JACKET COLOR: BLACK (BL), BLUE (BU), RED (RD), WHITE (WH)
4. MATES WITH SFP SFF-8432 INTERFACE
5. CABLE LABEL CONTAINS PRODUCT DESCRIPTION, PART NUMBER, LENGTH AND WIRE GAUGE, AND MANUFACTURING SERIAL NUMBER.




TABLE 1
CABLE ASSEMBLY

| PANDUIT P/N | P/N CODE FOR LENGTH | LENGTH IN FEET | CABLE AWG |
|---------------|---------------------|----------------|-----------|
| PSF2PZA1M** | 1M | 3.3 ft | 30 |
| PSF2PZA1.5M** | 1.5M | 4.9 ft | 30 |
| PSF2PZA2M** | 2M | 6.6 ft | 30 |
| PSF2PZA2.5M** | 2.5M | 8.2 ft | 30 |
| PSF2PZA3M** | 3M | 9.8 ft | 30 |
| PSF2PZC3.5M** | 3.5M | 11.5 ft | 26 |
| PSF2PZC4M** | 4M | 13.1 ft | 26 |
| PSF2PZC5M** | 5M | 16.4 ft | 26 |

**=SEE NOTE 3.D

| | | | |
|--|-----------------|--------------------------------|---------------|
| PART NUMBER SEE TABLE 1 | | PRODUCT SPEC/PKG SPEC N/A | |
| I.I. NUMBER N/A | | WORK INSTRUCTION N/A | |
| TITLE SFP28 PASSIVE CABLE ASSEMBLY CUSTOMER DRAWING | | | |
| ITEM REVISION NAME 00275EBA/02 | | PANDUIT | |
| DATASET FILE NAME 00275EBA_DC/02A | | | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] | | MATERIAL: | |
| .x ± .1 [2.54] .xxx ± .005 [0.127] | | DRAWING NUMBER: 00275EBA-DC | |
| .xx ± .01 [0.25] ANGLES ± 5° | | | |
| THIRD ANGLE PROJECTION | | | |
| DRAWN BY BJN | DATE 6-17-20 | CHK MATO | SCALE NONE |
| SHT 1 OF 2 | | SIZE A | |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|---------|-----|------|------|--|-------------|
| 02A | 4-12-23 | BJN | MATO | KYLM | PATCH CORD NOW HAS STRAIGHT SPRING LATCHES | M09000SX |
| 01A | 6-17-20 | BJN | MATO | DDH | RELEASED TO PRODUCTION REVISED & REDRAWN PREVIOUS HISTORY REMVD FOR CLARITY | 00275EBA-DC |

D101000DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




TABLE 2
PINOUT DIAGRAM

| BOTTOM SIDE | | TOP SIDE | |
|-------------|--------------|----------|--------|
| POS # | SIGNAL | POS # | SIGNAL |
| 1 | VEET* | 11 | VEER* |
| 2 | TX_FAULT** | 12 | RD- |
| 3 | TX_DISABLE** | 13 | RD+ |
| 4 | SDA | 14 | VEER* |
| 5 | SCL | 15 | VCCR |
| 6 | MOD_ABS | 16 | VCCT |
| 7 | RS0 | 17 | VEET* |
| 8 | RX_LOS** | 18 | TD+ |
| 9 | RS1 | 19 | TD- |
| 10 | VEER* | 20 | VEET* |

- * VEE PINS CONNECT FIRST UPON PLUGGING IN.
- ** TX_FAULT, TX_DISABLE, AND RX_LOS ARE DEFINED IN SFF-8431, BUT ARE NOT USED IN PASSIVE DIRECT ATTACH COPPER CABLES.

| | | | |
|--|-----------------|----------------------------------|---------------|
| PART NUMBER SEE TABLE 1 | | PRODUCT SPEC/PKG SPEC N/A | |
| I.I. NUMBER N/A | | WORK INSTRUCTION N/A | |
| TITLE SFP28 PASSIVE CABLE ASSEMBLY | | | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME 00275EBA/02 | | PANDUIT | |
| DATASET FILE NAME 00275EBA_DC/02A | | | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) | | MATERIAL: | |
| .x ± .1 [2.54] .xxx ± .005 [.127] | | DRAWING NUMBER: 00275EBA - DC | |
| .xx ± .01 [.25] ANGLES ± 5 ° | | | |
| THIRD ANGLE PROJECTION | | | |
| DRAWN BY BJN | DATE 6-17-20 | CHK MATO | SCALE NONE |
| SHT 2 OF 2 | | SIZE A | |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|---------|-----|------|------|----------------------------------|-------------|
| 01A | 4-12-23 | BJN | MATO | KYLM | SEE SHEET 1 FOR REVISION HISTORY | M09000SX |
| 00A | 6-17-20 | BJN | MATO | DDH | SEE SHEET 1 FOR REVISION HISTORY | 00275EBA-DC |

D101000DA/14