
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT PART NUMBER	DESCRIPTION	
FMTPMFCT	MPO/MTP MALE REEL CLEANING TOOL	

## APPROXIMATE PRODUCT DIMENSIONS

3.2 X 5.0 X 1.4 inches [81 X 127 X 36 mm]

## NOTES:

- 1. THIS PRODUCT CLEANS SINGLEMODE AND MULTIMODE FERRULE ENDFACES OF MPO/MTP CONNECTORS WITH GUIDE PINS (NOT INSTALLED IN A MPO/MTP ADAPTER).
- 2. THE PRODUCT HOUSING INCORPORATES AN ANTI-STATIC AGENT.
- 3. THE PRODUCT DESIGN ALLOWS FOR ONE-HANDED USE.
  - A. DEPRESSING A LEVER ON THE CLEANING TOOL OPENS THE PROTECTIVE SHUTTER, ADVANCES, AND EXPOSES A FRESH PORTION OF CLEANING CLOTH. RELEASING THE LEVER CLOSES THE SHUTTER.
  - B. WIPING THE FERRULE ENDFACE ON THE EXPOSED CLEANING CLOTH IN A SPECIFIED DIRECTION CLEANS THE CONNECTOR FERRULE ENDFACE.
- 4. THE CLEANING CLOTH:

01893-55

ECN

- A. IS AN ULTRA CLEAN MICRO-FIBER CLOTH THAT CAPTURES DEBRIS AND OTHER CONTAMINATION, DOES NOT FRAY, AND DOES NOT LEAVE ANY FIBROUS MATERIALS ON THE FERRULE ENDFACES BEING CLEANED.
- B. PROVIDES APPROXIMATELY 400 CLEANINGS.
- C. DOES NOT REQUIRE THE USE OF ADDITIONAL WET CLEANING AGENTS.
- D. ALLOWS FOR USER REPLACEMENT OF CLEANING REEL.
- 5. OPERATING TEMPERATURE: 0 TO 40 °C
- 6. STORAGE TEMPERATURE: -20 TO 60 °C

PART NUMBER

DRAWN BY DATE

12-11-06

MC

TITLE			
MPT/MTP MALE REEL CLEANING TOOL			
CUSTOMER DRAWING			
ITEM REVISION NAME		<u> </u>	
M01893ZM/00			
DATASET FILE NAME	PANDUIT		
M01893ZM_DC/0			
LINE CCC OTHERWICE CRECIFIED		MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			
.xxx	±		
.XX ± ANGLES	±		
	HIRD ANGLE	DRAWING NUMBER:	
	PROJECTION	01893-55	

NONE

SHT 1 0F 1

**EMTPMECT** 

Α

REV

6/11/15

DATE

JSP

WJM

CHK

APR

JGSW A. REVISED DRAWING TITLE BLOCK.

DESCRIPTION

MMW

SCALE