





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT
GPB484R4WJY	4.61 LB/ea (2097 g/ea)

- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.
 - STAMPING ASSEMBLY IS DESIGNED FOR RACK MOUNT APPLICATIONS.
 - GP6 PLUS BASES AND TROUGHS ARE ASSEMBLED TO BRACKETS WITH 8 SUPPLIED SCREWS. (4) #12 MOUNTING SCREWS AND (4) METRIC M6x1x15MM SCREWS ARE ALSO PROVIDED.
 - A GP6 PLUS BLOCK KIT IS ALSO INCLUDED WITH EACH ASSEMBLY (SEE CHART).
 - DIMENSIONS IN [] IN METRIC.



PART NUMBER		GPB484R4WJY	
TITLE			
STANDARD DENSITY GP6 PLUS WITH JUMPER TROUGH,		4 RACK UNIT	
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479KA/AA	
DATASET FILE NAME		M02479KA_DC262/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xx ± .03 [.8]		PC	
.xxx ± .010 [.3]		DRAWING NUMBER:	
ANGLES ±		02479-262	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
NER	3-20-06	WJC	NONE
REV	DATE	BY	CHK
1	6/13/14	JSP	REFR
R	3-20-06	NER	WJC
APR	DESCRIPTION		ECN
MMR	A. REVISED DRAWING TITLE BLOCK.		02479-262
RMD	RELEASED TO PRODUCTION		02479-262

D10100DA/14