




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. EQUIPMENT RAILS (E-RAILS) ARE SET TO 738mm [29.1"] FROM THE FACTORY. E-RAILS ARE INFINITELY ADJUSTABLE, FROM A MINIMUM OF 128mm APART, TO A MAXIMUM FOUND IN THE CHART ON SHEET 2. FRONT E-RAIL CAN BE ADJUSTED BACK UP TO 299mm.
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS
6. PARTS SUPPLIED:
 - BASE CABINET
 - FRONT CURVED PERFORATED SINGLE HINGE DOOR, 69% OPEN AREA, OPENS UP TO 165° WHEN GANGED
 - REAR PERFORATED SPLIT DOOR, 69% OPEN AREA, OPENS UP TO 150° WHEN GANGED
 - EQUIPMENT RAILS FRONT & REAR (E-RAILS) (SEE CHART ON SHEET 2)
 - (2) PAIRS SPLIT SIDE PANELS
 - PDU MOUNTING / CABLE MANAGEMENT BRACKETS (CMB)
 - FRONT VERTICAL BLANKING PANELS
 - SWIVEL CASTERS
 - HARDWARE KIT CONTAINING:
 - (40) M6 CAGE NUTS
 - (40) M6 PHILIPS HEAD SCREWS
 - (4) GANGING BRACKETS
 - (8) M5 TORX (T25) THREAD CUTTING SCREWS
 - (4) RINGS OF CABINET LOCK KEYS WITH (2) KEYS PER RING.
 - LEVELING LEGS
 - INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE PRINTED ON EQUIPMENT MOUNTING RAILS, NUMBERS UP TO 8.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING 1500 Kg (3300 LBS)
10. ROLLING LOAD RATING 500 Kg (1102 LBS)


01A	7/13/20	MEX-JAGC	PATR	PATR	PART NOS. WITHOUT SIDE PANELS REMOVED	V09002DP/03
00A	12-4-19	MES	PATR	SJP	RELEASED TO PRODUCTION	V09002DP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					
NET-VERSE D-TYPE ENHANCED CABINET 800 WIDE X 42, 45 & 48RU X 1000mm/1200mm DEEP (DNE8**2*) CUSTOMER DRAWING					
ITEM REVISION NAME					
00568EAB/01					
DATASET FILE NAME				MATERIAL: N/A	
00568EAB_DC/01A					
 THIRD ANGLE PROJECTION				DRAWING NUMBER:	
				00568EAB - DC	
DRAWN BY	DATE	CHK	SCALE	SIZE	
MES	12-4-19	PATR	NONE	SHT 1 OF 7 A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	FRAME HEIGHT	FRAME DEPTH	E-RAIL MAXIMUM SPACING	CABINET UNPACKAGED WEIGHT	CABINET SHIPPING WEIGHT
DNE8212*	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1000mm DEEP	1998.0 [78.6]	1000.0 (39.37)	738 [29.1] WITH CMB 871 [34.3] WITHOUT CMB	146 Kg/EACH 321 LBS/EACH	177 Kg/EACH 390 LBS/EACH
DNE8222*	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1200mm DEEP	1998.0 [78.6]	1200.0 (47.24)	938 [36.9] WITH CMB 1071 [42.2] WITHOUT CMB	157 Kg/EACH 346 LBS/EACH	192 Kg/EACH 423 LBS/EACH
DNE8512*	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1000mm DEEP	2131.4 (84.04)	1000.0 (39.37)	738 [29.1] WITH CMB 871 [34.3] WITHOUT CMB	150 Kg/EACH 331 LBS/EACH	183 Kg/EACH 403 LBS/EACH
DNE8522*	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1200mm DEEP	2131.4 (84.04)	1200.0 (47.24)	938 [36.9] WITH CMB 1071 [42.2] WITHOUT CMB	162 Kg/EACH 355 LBS/EACH	199 Kg/EACH 439 LBS/EACH
DNE8812*	NET-VERSE D-TYPE CABINET 800mm WIDE X 48RU X 1000mm DEEP	2264.7 [89.16]	1000.0 (39.37)	738 [29.1] WITH CMB 871 [34.3] WITHOUT CMB	153 Kg/EACH 337 LBS/EACH	184 Kg/EACH 406 LBS/EACH
DNE8822*	NET-VERSE D-TYPE CABINET 800mm WIDE X 48RU X 1200mm DEEP	2264.7 [89.16]	1200.0 (47.24)	938 [36.9] WITH CMB 1071 [42.2] WITHOUT CMB	165 Kg/EACH 364 LBS/EACH	200 Kg/EACH 440 LBS/EACH


NOTE: *DENOTES COLOR - ADD SUFFIX "B" FOR BLACK AND "W" FOR WHITE.



						TITLE		NET-VERSE D-TYPE ENHANCED CABINET 800 WIDE X 42, 45 & 48RU X 1000mm/1200mm DEEP (DNE8**2*) CUSTOMER DRAWING	
						ITEM REVISION NAME		00568EAB/01	
						DATASET FILE NAME		00568EAB_DC/01A	
								MATERIAL:	
								N/A	
01A	7/13/20	MEX-JAGC	PATR	PATR	SEE SHEET 1 FOR REVISIONS	V09002DP/03		 THIRD ANGLE PROJECTION	
00A	12-4-19	MES	PATR	SJP	SEE SHEET ONE FOR REVISIONS	V09002DP			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK
							MES	12-4-19	PATR
							SCALE	NONE	
							SHT 2 OF 7		SIZE
							A		

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




							TITLE NET-VERSE D-TYPE ENHANCED CABINET 800 WIDE X 42, 45 & 48RU X 1000mm/1200mm DEEP (DNE8**2*) CUSTOMER DRAWING					
							ITEM REVISION NAME 00568EAB/01					
							DATASET FILE NAME 00568EAB_DC/01A					
							 THIRD ANGLE PROJECTION					
01A	7/13/20	MEX-JAGC	PATR	PATR	SEE SHEET 1 FOR REVISIONS	V09002DP/03	MATERIAL: N/A					
00A	12-4-19	MES	PATR	SJP	SEE SHEET ONE FOR REVISIONS	V09002DP						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MES	DATE 12-4-19	CHK PATR	SCALE NONE	DRAWING NUMBER: 00568EAB-DC	SIZE A

2


1



D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT DOOR, REAR DOOR,
AND SIDE PANELS NOT SHOWN




							TITLE NET-VERSE D-TYPE ENHANCED CABINET 800 WIDE X 42, 45 & 48RU X 1000mm/1200mm DEEP (DNE8**2*) CUSTOMER DRAWING					
							ITEM REVISION NAME 00568EAB/01					
							DATASET FILE NAME 00568EAB_DC/01A					
											MATERIAL: N/A	
01A	7/13/20	MEX-JAGC	PATR	PATR	SEE SHEET 1 FOR REVISIONS	V09002DP/03	 THIRD ANGLE PROJECTION				DRAWING NUMBER: 00568EAB-DC	
00A	12-4-19	MES	PATR	SJP	SEE SHEET ONE FOR REVISIONS	V09002DP						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY MES	DATE 12-4-19	CHK PATR	SCALE NONE	SHT 4 OF 7	SIZE A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


B



REAR OF CABINET
BOTTOM VIEW

64 [2.5]
FROM FRONT
OF FRAME TO
FACE OF RAIL

738 [29.1]
FROM FRONT FACE
OF FRONT RAIL
TO REAR FACE
OF REAR RAIL



REAR OF CABINET
TOP VIEW

SOME PARTS REMOVED FOR CLARITY

A

01A	7/13/20	MEX-JAGC	PATR	PATR	SEE SHEET 1 FOR REVISIONS	V09002DP/03
00A	12-4-19	MES	PATR	SJP	SEE SHEET ONE FOR REVISIONS	V09002DP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		NET-VERSE D-TYPE ENHANCED CABINET 800 WIDE X 42, 45 & 48RU X 1000mm/1200mm DEEP (DNE8**2*) CUSTOMER DRAWING	
ITEM REVISION NAME		00568EAB/01	PANDUIT
DATASET FILE NAME		00568EAB_DC/01A	
			MATERIAL:
			N/A
			DRAWING NUMBER:
			00568EAB-DC
DRAWN BY	DATE	CHK	SCALE
MES	12-4-19	MCIS	NONE
		THIRD ANGLE PROJECTION	
		SHT 5 OF 7	SIZE
			A

A

2

1

D101000A/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TOP CAP OPENING CABLE CAPACITY								
	AREA		CABLE CAPACTIY* (CABLE DIA)					
	CM ²	IN ²	CAT 6A (8.99mm)	CAT 6A (7.87mm)	CAT 6A (7.54mm)	CAT 6 (6.35mm)	CAT 5e (4.75mm)	FIBER (3mm)
84mm × 476mm FRONT AND REAR OPENINGS (EACH)	399.6	61.9	251	328	358	504	902	2261
39.8mm × 476mm SIDE OPENINGS (EACH)	189.2	29.3	119	155	169	239	427	1070

* CAPACITY CALCULATION ASSUMES 40% FILL FACTOR

							<div>TITLE</div> <div>NET-VERSE D-TYPE ENHANCED CABINET 800 WIDE X 42, 45 & 48RU X 1000mm/1200mm DEEP (DNE8**2*) CUSTOMER DRAWING</div> <div>ITEM REVISION NAME</div> <div>00568EAB/01</div> <div>DATASET FILE NAME</div> <div>00568EAB_DC/01A</div> <div><div><div></div><div></div></div><div>THIRD ANGLE PROJECTION</div></div> <div>MATERIAL:</div> <div>N/A</div> <div>DRAWING NUMBER:</div> <div>00568EAB-DC</div> <div>SIZE</div> <div>A</div>						
01A	7/13/20	MEX-JAGC	PATR	PATR	SEE SHEET 1 FOR REVISIONS	V09002DP/03							
00A	12-4-19	MES	PATR	SJP	SEE SHEET ONE FOR REVISIONS	V09002DP							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY		DATE	CHK	SCALE	SHT 6 OF 7	SIZE
							MES		12-4-19	PATR	NONE		A

SI/10100DA/16

