

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	THREAD	THICKNESS	WRENCH SIZE
SSN1420-C	1/4-20	.22 [5.6]	7/16
SSNUT31-C	5/16-18	.27 [6.7]	1/2
SSN3816-C	3/8-16	.31 [7.9]	9/16
SSNUT50-C	1/2-13	.44 [11.1]	3/4
SSNUT62-C	5/8-11	.55 [13.9]	15/16

NOTES:

- 1. MATERIAL: 18-8 STAINLESS STEEL
- 2. DIMENSIONS IN BRACKETS ARE MILLIMETERS
- 3. PKG. QTY: C = 100





							STAINLESS STEEL HEX NUT (SSNUT SERIES) CUSTOMER DRAWING
							TEM REVISION NAME 15J350BG/00 DATASET FILE NAME 15J350BG-DC/00.SLDDRW
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] SEE XX ± .XXX ± NOTES XXX ± .02 [0.5] ANGLES ±
00	4/17	JHNU	JHNU	RGB	DRAWING RELEASED	15J350BG-DC	THIRD ANGLE PROJECTION DRAWING NUMBER 15J350BG-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE JHNU 4/17 RGB N/A SHEET 1 OF 1 SIZE A