

TDS: Effective Date: Revision:

Preprinted Laminated Vinyl Film

This specification is intended to outline the physical and chemical properties of *PANDUIT*'s pressure sensitive preprinted RoHS compliant laminated vinyl material and include the following part numbers and printable material identifiers:

Part Number Prefixes
PESW*Y
PESG
PESF
PESH
PESV
WL36Y
WL35Y

PRODUCT SPECIFICATIONS:

Description:	Material is RoHS compliant (European Union directive 2002/95/EC). GMV1OL consist of a 1.5 mil overlaminant laminated to a 4.0 mil vinyl film.
Print Methods:	This material is preprinted.
Adhesive:	Acrylic based, pressure sensitive permanent adhesive.
Standard Colors:	White, Yellow, Orange, Red, Blue and Green
Thickness:	5.5 +/- 0.5 mils (total laminated construction)
Service Temperature Range:	-40°F to 176°F (-40°C to 80°C)
Minimum Application Temperature:	50°F (10°C)
Storage Conditions:	Store at 70°F (21°C) and 50% Relative Humidity.

PROPERTIES: PERFORMANCE:

Peel Adhesion to Stainless Steel:	40 oz/in width minimum (PSTC-101, 15 min. dwell)
Steel.	40.02 m widdi minimum (1.51C-101, 15 mm. dwch)
Shear Adhesion:	24+ hours (PSTC-107, Procedure A)
Tensile Strength:	MD 48 +/- 4.8 lbs./inch width (PSTC-131) TD 37 +/- 3.7 lbs./inch width (PSTC-131)
Elongation:	MD 90% +/- 10% (PSTC-131) TD 145% +/- 10% (PSTC-131)
Elevated Temperature Exposure:	After 8 hours at 150°F (65.5°C) there was no deterioration of the substrate
Tack:	425 g/cm ² (ASTM D-2979-71, 1 sec dwell)
UV Resistance:	*3000 hours no change observed (ASTM G154)
*20001	

*3000 hours equates to 5 years of assimilated outdoor UV exposure.



TDS: Effective Date: Revision:

CHEMICAL/SOLVENT RESISTANCE:

Preprinted samples were applied to stainless steel panels and conditioned for 24 hours at room temperature before testing. The samples were then immersed in the specified reagents for five immersions using the following cycle: a 10 minute immersion time followed by a 30 minute recovery time. After the fifth immersion, the samples were rubbed 10 times with a lint free cotton gauze.

	Visual Observation		
Chemical Reagent	Substrate / Adhesive	Pre-Printed Printed Legend	
Distilled Water	No effect	No effect	
Mineral Spirits	No effect	No effect	
Toluene	Delamination of film	Loss of print legibility	
Isopropyl Alcohol	No effect	No effect	
Methanol	No effect	No effect	
Acetone	Delamination of film	Loss of print density	
Methyl Ethyl Ketone	Delamination of film	Loss of print density	
1,1,1 Trichloroethane	Delamination of film	Loss of print density	
Freon TF	No effect	No effect	
Super Agitene	No effect	No effect	
Jet-A Fuel	No effect	No effect	
Arco TruSlide 68	No effect	No effect	
SAE 30 Motor Oil	No effect	No effect	

APPROVALS:

UL Recognized: UL969 CUL Recognized: C22.2 No. 0.15-01 File Number: MH 14576 (only PESW*Y, WL35Y, WL36Y) File Number: MH 14576 (only PESW*Y, WL35Y, WL36Y)

LIMITED WARRANTY

All *PANDUIT* Identification Solution Products (except for Software programs) are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to replacement of the product proved to be defective within 6 months from the date of sale, or in the case of printers, within 90 days from the date of sale. This warranty is void if the products or printers are modified, altered or misused in any way. Use of *PANDUIT* printers with any product other than the specified *PANDUIT* products for which the printer was designed constitutes misuse. Before using, the user shall determine the suitability of the product for its intended use and user assumes all risk and liability whatsoever in connection therewith. The foregoing may not be altered except by an agreement signed by officers or seller and manufacturer.

NEITHER *PANDUIT* OR SELLER SHALL BE LIABLE FOR ANY OTHER INJURY, LOSS OR DAMAGE, WHETHER DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OF, OR THE INABILITY TO USE THE PRODUCT OR THE PRINTER.

THIS WARRANTY IS MADE IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS OF PARTICULAR USE ARE SPECIFICALLY EXCLUDED.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide or use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. This publication is not to be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.