

technical information

This pure sine wave Double Conversion 1–3 KVA UPS delivers highly efficient and reliable power protection and backup for your computer IT equipment. The UPS features a maintenance-free VRLA battery and is a 1–3kVA single-phase 120/230 volt unit. The pure Online Double Conversion system provides constant excellent electrical performance and comes standard with enhanced intelligent monitoring and network functions. The unit complies with ENERGY STAR® 2.0, EMC, and safety standards to meet the continually growing power demands of Data Center, Enterprise, and Edge IT Infrastructure.







key features and benefits

Key Icaluics	and benefits
Rack/Tower convertible:	Supports rack/tower installation with rotatable colorful LCD display
Online Double Conversion with fully digital control:	Provides stable and clean power with less ripple by filtering noise, automatic voltage regulation (AVR) and surge protectionn
Wide input voltage range:	110–300 VAC for EU units and 55–150 VAC for North America units, covering extended voltage range, applicable for severe situation such as large power grid fluctuation
High efficiency:	Up to 96.5%, reducing the energy waste and the cost of electricity
Energy savings:	High Efficiency on Smart ECO mode for Online Double Conversion models
Green design:	RoHS and Reach, CE/UL/ENERGY STAR® 2.0 compliant for North America units
Output unity power factor:	Means more active power for IT equipment load
Input power factor:	Power factor correction topology on the input side dramatically reducing the total harmonic distortion (THD)
Expandable battery packs:	Allows to connect maximum four external battery packs, extending the UPS backup running time
Intelligent Battery Management:	The most optimal curve and temperature-compensated with advanced algorithms prolonging the battery life
EPO function (Emergency Power Off):	Allows to quickly and easy shut down the UPS when emergency event occurs
Generator compatible:	Wide input frequency and voltage, supports connecting to generators, ensuring the uninterruptible operation
Hot-Swappable battery design:	Can perform the replacement of battery cartridge without powering down the UPS
Cold start function:	Allows to boot up the UPS without mains input but with batteries
Intelligent fan speed regulation:	Automatically adjustment of fan speed due to the ambient temperature and load percentage
Programmable outlet group with Smart Load Shedding:	Loads connected to the programmable group can lose power first, saving more energy and extending the runtime for critical load. Smart Load Shed allows logical group shutdown with time or load.
Segment colorful LCD:	Colorful LCD with four buttons and LED indicators, providing intuitive display
Multiple communication interface:	RS232/USB/intelligent slot, realizing communication and monitoring function
Comprehensive protection function:	Short-circuit, overload, overheat, battery overcharge and over discharge, output low voltage, fan fault alarm and RJ45 surge protection
Intelligent Network Management Card (included with N Models*):	Provides harden security remote access via Ethernet Secure SNMPv3 protocol to monitor and manage the UPS, micro-USB for firmware upgrade and RS-485 for connecting environmental and security sensors. Built-in WiFi and Bluetooth hardware support with future optional firmware upgrade.
Cloud Ready (included with N Models*):	Support for technology allowing to easily, securely and quickly connect to DCIM with management, monitoring, control and alerting of Power Chain, Environmental, Cooling, Security, Asset and Connectivity Infrastructure Assets.
mPower Management Software:	Configure, monitor, and manage the UPS (includes graceful equipment shutdown) remotely via RS-232 or USB or Ethernet. Software is available for free download from www.panduit.com/ups

^{*} N Model UPS has an N in the 4th digit of the part number, e.g. U01N12V

product specifications — 1-3k 230 v vrla

MODEL		U01S12V/U01N12V				
Output power capa	city	1000 VA	2000 VA	3000 VA		
Max Configurable P	ower (Watts)	1000 W	2000 W	3000 W		
Nominal output voltage		230 VAC (220/240 VAC selectable)				
Output Voltage	Linear load		<3%			
Distortion	Non linear load		<5%			
Output frequency	Online mode		50/60 ± 4 Hz			
Output frequency	Battery mode		50/60 ± 0.1 Hz			
Output power facto	r		1.0			
Load crest factor		3:1				
Topology		Double Conversion Online				
Waveform		Pure Sine Wave				
Overload	Online mode	105%-125%: 1 min; 125%-130%: 30 s; > 130%: 200 ms, transfer to bypass				
capability	Battery mode	105%-125%: 1 min; 125%-130%: 10 s; > 130%: 200 ms, shut down				
Transfer time	Online mode <-> Battery mode	0 ms				
(typical)	Inverter <-> Bypass	4 ms				
Efficiency	Online mode 90.0% 92.0%		92.0%			
Emclency	ECO mode	95.0%	96.0%	96.5%		
Output	Programmable	(4) IEC C13		(4) IEC C13		
connection	Non-programmable	(4) IEC C13		(1) IEC C19; (4) IEC C13		
Bypass			Internal			

INPUT

• .				
Nominal input voltage		230 VAC (220 VAC/240 VAC selectable)		
Full load		176–264 VAC		
Input voltage range	Half load	110-300 VAC		
Input frequency range		40-70 Hz (auto sensing)		
Input connection	Input connection C14 socket (2 cords included) C20 socket (2 cords		C20 socket (2 cords included)	
Input power factor		>0.98 (full load)		
Cord Length		1.8m (6 ft.)		
Number of Power Co	ords	Schuko CEE 7/EU1-16P and BS1363A		

BATTERY

DALIENT					
Battery type		VRLA			
Typical recharge time 4–6 hours					
Battery voltage		36 VDC 48 VDC 72 VDC			
Battery quantity	× capacity	3 × 12 V/9 Ah 4 × 12 V/9 Ah 6 × 12 V/9 Ah			
Charging current (max.)		2 A			
Backup time	Full load	13 min.	8 min.	8 min.	
	Half load	26 min.	17 min.	17 min.	
Expected Battery	y Life (years)		3–5 yrs.		
Internal Replace	ment Cartridge	UVC036	UVC048	UVC072	
Maximum External Battery Pack (EBP) quantity			4 units		

product specifications — 1-3k 230 v vrla (continued)

COMMUNICATION & MANAGEMENT					
Communication ports		USB, RS232, intelligent slot			
Pre-Installed iNMC Card	N model only				
Local Display/Control Panel	Segment colorful screen				
Audible Alarm	Yes				
Emergency Power Off (EPO)	Yes				
ENVIRONMENTAL					
Operating temperature	32°F-104°F (0°C-40°C) (no derating)				
Storage temperature		-25°C-55°C (without batteries)			
Relative humidity		0-95% (non-condensing)			
Operating elevation		Up to 3000 m (derated 10%)			
Online thermal dissipation	400 BTU/hour	593 BTU/hour	890 BTU/hour		
Protection Class		IP20			
Noise level		<55dB at 1m			
CONFORMANCE					
Safety	CB: IEC62040-1:2013, CE-LVD: EN62040-1:2008+A1:2013, RCM UKCA: BS62040-1-2013				
EMC	IEC 62040-2-2016, EN 62040-2-2018, BS62040-2-2018				
Transportation	ISTA Procedure 2A				
Surge protection	ANSI C62.41 Category A (380 J)				
CUSTOMER SERVICE					
Warranty	3 years for UPS and EBP, 2 years for internal battery cartridges				
SUSTAINABLE OFFER STATUS					
RoHS 2.0		Compliant			
Proposition 65 Warning		See Safety Sheet (IM053)			
PHYSICAL					
Maximum Height		86.5mm			
Maximum Width		440mm			
Maximum Depth	460)mm	600mm		
Rack Height		2 RU			
Net Weight	16.1 kg	21.3 kg	24.4 kg		
Shipping Weight	22.3 kg	27.6 kg	30.9 kg		
Shipping Height		202mm (7.95")			
Shipping Width		555mm (21.8")			
Shipping Depth	590mm (23.2")	590mm (23.2")	730mm (28.7")		
Color	Black				

product specifications — 1-3k 120 v vrla

MODEL		U01S13V/ U01S11V/ U02S11V/ U03S- U01N13V U01N11V U02N11V U03N				
Output power capacity		1000 VA		2000 VA	3000 VA	
Max Configurable	Power (Watts)	1000) W	2000 W	3000 W	
Nominal output voltage			120 VAC (100/110/11	5/125 VAC selectable)		
Output voltage	Linear load		<	3%		
distortion	Non Linear load		<	5%		
Output	Online mode		50/60	± 4 Hz		
frequency	Battery mode		50/60	± 0.1 Hz		
Output power fact	or		1	1.0		
Load crest factor			3	3:1		
Topology		Double Conversion Online				
Waveform		Pure Sine Wave				
Overload Online mode		105%-125%: 1 min.; 125%-130%: 30 s; > 130%: 200 ms, transfer to bypass				
capability	Battery mode	105%-125%: 1 min.; 125%-130%: 10 s; > 130%: 200 ms, shut down				
Transfer time	Online mode <-> Battery mode	0 ms				
(typical)	Inverter <-> Bypass	4 ms				
Efficiency	Online mode	90.0)%	92.0%	92.0%	
Efficiency	ECO mode	95.0)%	96.0%	96.5%	
0	Programmable	(2) NEMA	\ 5–15R	(2) NEMA 5-20R	(2) NEMA 5-20R	
Output connection	Non-programmable	(4) NEMA	A 5–15R	(4) NEMA 5-20R	(1) NEMA L5-30R; (2) NEMA 5-20R	
Bypass		Internal				
INPUT						
Nominal input volt	age	100-125 VAC				

Nominal input voltage	100-125 VAC			
Input voltage range	55–150 VAC			
Input frequency range	40-70 Hz (auto sensing)			
Input connection	NEMA 5–15P NEMA 5–20P NEMA L5–30P			
Input power factor	>0.98 (full load)			
Cord Length	3m (10 ft.)			
Number of Power Cords	(1) fixed			

BATTERY

Battery type			VF	RLA			
Typical recharge	time		4–6	hrs.			
Battery voltage		24 VDC	24 VDC 36 VDC 48 VDC 72 VDC				
Battery quantity	× capacity	2 × 12 V/9 Ah	2 × 12 V/9 Ah 3 × 12 V/9 Ah 4 × 12 V/9 Ah 6 × 12 V/9				
Charging current (max.)			2A				
Backup time	Full load	8 min.	13 min.	8 min.	8 min.		
	Half load	17 min.	26 min.	17 min.	17 min.		
Expected Battery	Life (years)		3-5	yrs.			
Internal Replacement Cartridge		UVC024	UVC036	UVC048	UVC072		
Maximum External Battery Pack (EBP) quantity			4 u	nits			

product specifications — 1-3k 120 v vrla (continued)

COMMUNICATION & MANAGEMENT					
Communication ports	USB, RS232, intelligent slot				
Pre-Installed iNMC Card	N model only				
Local Display/Control Panel	Segment colorful screen				
Audible Alarm		•	⁄es		
Emergency Power Off (EPO)			/es		
ENVIRONMENTAL					
Operating temperature	32°F-104°F (0°C-40°C) (no derating)				
Storage temperature		-25°C-55°C (v	vithout batteries)		
Relative humidity		0–95% (nor	n-condensing)		
Operating elevation		Up to 3000m	(derated 10%)		
Online thermal dissipation	400 BT	J/hour	534 BTU/hour	801 BTU/hour	
Protection Class		II	P20		
Noise level		<55d	B at 1m		
CONFORMANCE					
Energy Saving	ENERGY STAR® 2.0				
Safety	cUL: UL 1778 5th Edition, CSA C22.2 NO.107.3-14, NOM & RETIE				
EMC	FCC Part 15 Subpart B Class A, ANSI C63.4-2014				
Transportation	ISTA Procedure 2A				
Surge protection	ANSI C62.41 Category A (380 J)				
CUSTOMER SERVICE					
Warranty	3 years for UPS, 2 years for internal battery and EBP				
SUSTAINABLE OFFER STATUS					
RoHS 2.0		Con	npliant		
Proposition 65 Warning		See Safety	Sheet (IM053)		
PHYSICAL					
Maximum Height		86	5mm		
Maximum Width		44	0mm		
Maximum Depth	325r	nm	460mm	600mm	
Rack Height		2	RU		
Net Weight	12.4 kg	16.6 kg	20 kg	25.7 kg	
Shipping Weight	18.4 kg	22.7 kg	27.9 kg	31.7 kg	
Shipping Height		202m	m (7.95")		
Shipping Width		555m	m (21.8")		
Shipping Depth	545mm (21.4")	590m	m (23.2")	730mm (28.7")	
Color	Black				

Transportation

product specifications —ebp

· · · · · · · · · · · · · · · · · · ·				
EBP MODEL	UVP024	UVP036	UVP048	UVP072
MATCHED UPS	U01S13V/U01N13V	U01S11V/ U01N11V U01S12V/ U01N12V	U02S11V/U02N11V U02S12V/U02N12V	U03S11V/U03N11V U03S12V/U03N12V
BATTERY SYSTEM				
Battery type		VRLA (lead acid main	tenance free battery)	
Typical battery life	3 - 5 yea	rs, depend on dischargin	g cycle and ambient tem	perature
System voltage	24 VDC	36 VDC	48 VDC	72 VDC
Battery quantity	2 × 2 pcs.	2 × 3 pcs.	2 × 4 pcs.	2 × 6 pcs.
Battery capacity		12 V/	9 Ah	
Replacement Cartridge Set	UVD024	UVD036	UVD048	UVD072
PHYSICAL				
Maximum Height	86.5mm (3.42")			
Maximum Width		440mm	n (17.3")	
Maximum Depth	430mm	า (16.9")	550mm (21.6")	710mm (27.9")
Rack Height		2 F	RU	
Net Weight	17.8 kg	23.3 kg	30 kg	43 kg
ENVIRONMENTAL				
Operating temperature		0°C-	40°C	
Relative humidity	0-95% (non-condensing)			
Noise level	<40dB at 1m			
CONFORMANCE				
Safety		CE-LVD: EN62040-1:200 5th Edition, CSA C22.2 N		

ISTA Procedure 2A

ups accessories

Part Number	Description
URC005	Relay card (MiniAS400) (12 V) (for 1 to 10kVA single phase UPS units)
UNCP01	Panduit® Intelligent Network Management Card (iNMC) See iNMC specs for more details
UTOWFT	Tower stabilizer brackets
URMKIT2	Rack mount rail kit for 1-3kVA & 5-20kVA UPS and EBP
U2PTRMT	2-post mounting bracket
EXTWLAUPS1	1-3kVA LEAD ACID UPS 1 YR Extended Warranty, for up to 3 years. The extended warranty includes repair or replacement of UPS and covers your battery
EXTWLABPS1	1-3kVA LEAD ACID Battery Pack 1 YR Extended Warranty, for up to 3 years. The extended warranty includes repair or replacement and covers your battery

ups models

U01N11V (Rear)



U01N12V (Rear)



U02N11V (Rear)



U02N12V (Rear)



U03N11V (Rear)



U03N12V (Rear)



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

