

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

- 1. SEE CHART FOR PRODUCT OPTIONS.
- 2. PATCH CORDS ARE HELD TOGETHER USING HLS TAK-TY STRAPS AT 12"(305mm) SPACING.
- 3. EACH PATCH CORD IS SEQUENTIALLY NUMBERED AT BOTH ENDS WITH PORT ID LABELS.
- 4. PATCH CORD ID LABELS CONTAIN PATCH CORD PERFORMANCE, PART#, LENGTH(L), AND QC#.
- 5. ONE SET OF PLUG PACK ID LABELS AND ONE PLFIMA-C MARKER TIE ARE INCLUDED FOR CUSTOMER APPLIED SWITCH AND PORT IDENTIFICATION. FOR PRINTABLE LABEL OPTIONS. REFER TO PANDUIT C125X030FJJ, C125X030YPT AND C125X030FJC.
- 6. REFER TO 03073-06 FOR PLUG PACK CUSTOMER DRAWING.

QUICKNET PLUG PACK ASSEMBLY MATRIX									
QPP	A	C				03			
QUICKNET PLUG PACK	PERFORMANCE LEVEL	FLAME/SMOKE RATING (see notes below)	CABLE COLOR	PLUG PACK CONFIGURATION	PLUG PACK COLOR	PATCH CORD ASSEMBLY LENGTH ***			
QPP	A - CAT 6A (10Gig) UTP	C - CM	B - BLUE	R - RECESSED 6 PACK	S - SILVER				
	E - CAT 6A (10Gig)/ CAT 6 STP	L - LOW SMOKE ZERO HALOGEN (LSZH)	W - WHITE*			05 = 5 FEET			
	C - CAT 6 UTP	D - DUAL RATING	G - GRAY CABLE BLACK BOOT **			07 = 7 FEET			
		(MEETS BOTH CM AND LSZH RATING)				10 = 10 FEET			
						14 = 14 FEET			
						1M = 1 METER			
						2M = 2 METERS			
						3M = 3 METERS			
						5M = 5 METERS			



NOTES (FLAME RATING ABOVE):

- 1) ALL UTP ASSEMBLIES AVAILABLE IN CM OR LSZH ONLY (NO DUAL RATED OPTION AVAILABLE). 2) ALL STP ASSEMBLIES AVAILABLE ONLY AS DUAL RATED-D (MEET BOTH CM + LSZH REQUIREMENTS).
- * NOT AVAILABLE IN CAT6A/CAT6 STP
 ** ONLY AVAILABLE IN CAT6A/CAT6 STP
 *** LENGTH TOLERANCE: +2/0" (+5|mm/Omm) FOR LENGTHS UP TO (& INCLUDING) 20 FEET (6.1m)

+3/-0(+76mm/-0mm) FOR LENGTHS GREATER THAN 20 FEET (6.1m)

OPP * * * RS * *

TITLE

PART NUMBER

ITEM REVISION NAME

QUICKNET RECESSED 6 POSITION PLUG PACK ASSEMBLY

CUSTOMER DRAWING

								DATACET E		3AB/00		PANDUI	
ſ								DATASET FILE NAME M03073AB_DC05/00C					
f	2	12-11-18	BJN	SGO		REMOVE LENGTH TOLERANCE FROM DRAWING DIMENSIONS ADDED AS THREE ASTERISK NOTE	03073-05	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:		
	1	5/23/14	JSP	REFR		A. REVISED DRAWING TITLE BLOCK. B. REDUCED DOWN TO ONE SHEET.	03073-05	.× ±	.03[.8]	.XXX ±	.010 [.3]		
4. [R	11-3-08	MDJr	WFMI	JPMC	RELEASED TO PRODUCTION	03073-05				RD ANGLE OJECTION	DRAWING NUMBER: 03073-05	
50101	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	MDJr	11-03-08	WFMI	SCALE NONE	SHT 1 0F 1	SIZE