



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




TEMPERATURE	
PLENUM	
OPERATION/STORAGE	INSTALLATION
-40° F TO 176° F [-40° C TO 80° C]	32° F TO 140° F [0° C TO 60° C]
RISER	
OPERATION/STORAGE	INSTALLATION
-40° F TO 176° F [-40° C TO 80° C]	14° F TO 140° F [-10° C TO 60° C]

						TITLE	
						144 FIBER ARMORED INDOOR/OUTDOOR CABLE WITH 900µm BUFFERED FIBERS	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	PANDUIT
						M02055JR/00	
						DATASET FILE NAME	
						M02055JR_DC/00A	PART NO. SEE TABLE
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
						.X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±	
						 THIRD ANGLE PROJECTION	DRAWING NUMBER: M02055JR-DC
00	02-05-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JR-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT
							DATE 02-05-14
							CHK WMA
							SCALE NONE
							SHT 1 OF 2
							SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DESCRIPTION	FIBER COUNT	FLAME RATING	BEND RADIUS (INSTALLATION)	BEND RADIUS (LONG TERM)	TENSILE LOAD (INSTALLATION)	TENSILE LOAD (LONG TERM)	ATTENUATION
FSKR51A	MULTIMODE 50/125 OM2 INDOOR/OUTDOOR ARMORED CABLE	144	OFCR	27.0" [68.6cm]	13.5" [34.3cm]	600lbs [2670 N]	180lbs [800 N]	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSKR61A	MULTIMODE 62.5/125 OM1 INDOOR/OUTDOOR ARMORED CABLE		OFCR					3.5dB/km @ 850nm 1.0dB/km @ 1300nm
FOKRX1A	MULTIMODE 50/125 OM3 INDOOR/OUTDOOR ARMORED CABLE		OFCR					3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOKRZ1A	MULTIMODE 50/125 OM4 INDOOR/OUTDOOR ARMORED CABLE		OFCR					3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSKR91A	SINGLEMODE 9/125 INDOOR/OUTDOOR ARMORED CABLE		OFCR					0.7dB/km @ 1310nm 0.7dB/km @ 1550nm

							TITLE 144 FIBER ARMORED INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS CUSTOMER DRAWING					
							ITEM REVISION NAME M02055JR/00		PANDUIT			
							DATASET FILE NAME M02055JR_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±					
							THIRD ANGLE PROJECTION 		PART NO. SEE TABLE			
							DRAWING NUMBER: M02055JR-DC					
00	02-05-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JR-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 02-05-14	CHK WMA	SCALE NONE	SHT 2 OF 2	SIZE A