



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES :

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. PLENUM-RATED CABLES MEET THE REQUIREMENTS OF NFPA 262.
RISER-RATED CABLES MEET THE REQUIREMENTS OF UL 1666.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL
RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE
RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE
RoHS TECHNICAL ADAPTATION COMMITTEE.



PLENUM			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
600 lbs (2670 N)	180 lbs (800 N)	13 in (33.1 cm)	6.5 in (16.6 cm)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	STORAGE/OPERATION		INSTALLATION
.65" [16.6 mm]	-40°F TO +176°F [-40°C TO +80°C]		32°F TO +140°F [0°C TO +60°C]
RISER RATED			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
600 lbs (2670 N)	180 lbs (800 N)	16 in (40.7 cm)	8.0 in (20.4 cm)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	STORAGE/OPERATION		INSTALLATION
0.80" [20.3 mm]	-40°F TO +176°F [-40°C TO +80°C]		14°F TO +140°F [-10°C TO +60°C]

							TITLE 72 FIBER INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS CUSTOMER DRAWING					
							ITEM REVISION NAME M02055JA/00				PANDUIT	
							DATASET FILE NAME M02055JA_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±					
							 THIRD ANGLE PROJECTION					
00	02-04-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JA-DC					PART NO. SEE TABLE	
											DRAWING NUMBER: M02055JA - DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE	
							SAT	02-04-14	WMA	NONE	A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	FLAME RATING	CABLE ATTENUATION
FSLP572	MULTIMODE 50/125 OM2 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSLR572		OFNR	
FSLP672	MULTIMODE 62.5/125 OM1 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSLR672		OFNR	
FOLPX72	MULTIMODE 50/125 OM3 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRX72		OFNR	
FOLPZ72	MULTIMODE 50/125 OM4 INDOOR/OUTDOOR CABLE	OFNP	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRZ72		OFNR	
FSLP972	SINGLEMODE 9/125 INDOOR/OUTDOOR CABLE	OFNP	0.7dB/km @ 1310nm 0.7dB/km @ 1550nm
FSLR972		OFNR	

							TITLE					
							72 FIBER INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS					
							CUSTOMER DRAWING					
							ITEM REVISION NAME			<div>PANDUIT</div>		
							M02055JA/00					
							DATASET FILE NAME					
							M02055JA_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			PART NO.		
							.X ± .xxx ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±			SEE TABLE		
							<div><div></div><div></div></div> THIRD ANGLE PROJECTION			DRAWING NUMBER:		
00	02-04-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JA-DC				M02055JA-DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2	A
							SAT	02-04-14	WMA	NONE		