

# **Thermal Transfer Printable Polyimide Film**

This specification is intended to outline the physical and chemical properties of *PANDUIT*'s pressure sensitive polyimide material and include the following part numbers and printable material identifiers:

Part Number Prefixes				
TTC*KW				
TTC*K				

Printable Material Suffixes				
KBT				
КСТ				

### **PRODUCT SPECIFICATIONS:**

Description:	Material is a top coated polyimide film with a pressure sensitive adhesive. This product is halogen free and RoHS compliant (European Union directive 2002/95/EC).
Use:	Designed for barcode or alphanumeric identification of printed circuit boards, or related electronic components. It is the ideal label to withstand surface mount board processes, on either the top or bottom side of the board.
Properties:	The topcoat, in combination with Panduit thermal transfer resin ribbon, passes the requirements of MIL-STD-202G, Notice 12, Method 215K. The print resists smearing, even when the board and label are directly removed from a reflow or wave solder environment. Preheating the labeled product can further enhance print permanence in the case of extreme solvent and/or abrasion exposure, although this is not typically required for board processing applications.
Print Methods:	This material is recommended for thermal transfer printing.
Recommended Ribbons:	RMER4BL-C (for opaque white film), RMEH4BL (for opaque tan film)
Adhesive:	Acrylic based, pressure sensitive adhesive
Standard Colors:	Opaque white, Opaque tan
Thickness:	4.5 +/- 0.5 mils (coated substrate and adhesive)
Service Temperature Range:	-40°F to 350°F (-40°C to 177°C)
Minimum Application Temperature:	50°F (10°C)
Storage Conditions:	Store at 70°F (21°C) and 50% Relative Humidity.
PROPERTIES:	PERFORMANCE:
Peel Adhesion to Stainless Steel:	35 oz/in width minimum (PSTC-101, 20 min. dwell)
Shear Adhesion:	24 hours minimum(PSTC-107, procedure A)
Tensile Strength:	MD: 45 +/- 10% lbs./inch width (PSTC-131)
	TD: $40 + -10\%$ lbs./inch width (PSTC-131)
Elongation: Long Term High Service Temperature:	MD and 1D: $05\% \pm -15\%$ (PSTC-131) 1000 hours at $212^{\circ}$ E (100°C), no change observed
Low Service Temperature:	1000 hours at $-94^{\circ}$ F (-70°C), no change observed
Humidity Resistance:	1000 hours at 100°F(37°C), 95% R.H., no change observed
Abrasion Resistance:	Taber Abraser, CS-10 wheels, 250 g/arm, 30 cycles, no change observed
Maximum Intermittent Temperature:	Opaque white: 482°F (250°C)/> 30 min., 527°F (275°C)/> 20 min., 572°F (300°C)/> 10 min, 617°F (325°C)/5 min.
	Opaque tan: 482°F (250°C)/ 5 min., 527°F (275°C)/ 1 min., 572°F (300°C)/ 1 min,



TDS: Effective Date: Revision:

617°F (325°C)/ 1 min.

UV Resistance:

\*3000 hours in Xenon Arc Weatherometer, no change observed (ASTM G154)

\*3000 hrs. equates to 5 yrs. of assimilated outdoor UV exposure.

### I. 2 mil White Thermal Transfer Printable Polyimide

#### **Heat/Chemical Resistance**

Labels printed with 3:1 ratio barcodes with 6 mil (0.152mm) X dimension bars. Samples exposed to indicated environments.

Test Environment	RMER4BL		RMER4BL-C		RMEH4BL	
	Rating before	Rating after	Rating	Rating after	Rating	Rating after
	exposure <sup>1</sup>	exposure <sup>1</sup>	before	exposure <sup>1</sup>	before	exposure <sup>1</sup>
			exposure <sup>1</sup>		exposure <sup>1</sup>	
Control	В	В	А	А	А	А
260C heat, 5 minutes	В	В	А	А	А	А
170C heat, 2 hours	А	А	А	А	А	А
Kyzen Corp, Aquanox	В	В	А	А	А	А
SSA, 30% aqueous,						
40-45C, 10 minutes <sup>2</sup>						
RE-ENTRY.KNI 2000	В	С	А	С	А	NR
Terpene, 40-45C,						
10 minutes <sup>2</sup>						
Alpha Metals Inc. 2110	А	С	А	NR	А	В
Saponifier, 6% aqueous,						
65-70C, 10 minutes <sup>2</sup>						
Isopropanol 99%, 82C, 10	А	В	А	А	А	NR
minutes						
Deionized water, 100C,	А	А	А	А	А	А
10 minutes						
1,1,1 Trichloroethane,	А	А	А	А	А	NR
74C, 10 minutes						
BIOACT EC-7R Terpene	А	В	А	А	А	NR
Cleaner,						
40-45C, 10 minutes <sup>2</sup>						
Acetone, 30C,	A	F	A	NR	Α	NR
10 minutes						

1 Rating determined using PSC QuickCheck 850 Scanner.

2 Followed by 2 minute immersion in deionized water at 100C.

NR – NOT RATED



## **Technical Data Sheet**

#### **PROPERTIES** Chemical Resistance

**TEST METHOD** 

MIL-STD-202G, Notice 12, Method 215K

Labels printed with alphanumerics and 3:1 ratio barcodes with 6 mil (0.152mm) X dimension bars. Samples subjected to 3 cycles of three minute immersions immediately followed by a toothbrush rub after each immersion.

TEST FLUID	RMER4BL	RMER4BL-C	RMEH4BL
Solvent A	Loss of print legibility	Loss of print density	Loss of print legibility
1 part IPA, 3 parts Mineral			
Spirits			
Solvent B	Solvent deleted per	Solvent deleted per	Solvent deleted per
1,1,1 Trichloroethane	Notice 12	Notice 12	Notice 12
Solvent C	No visible effect	Loss of print legibility	No visible effect
Terpene Defluxer			
Solvent D	No visible effect	No visible effect	Loss of print density
Saponifier			

Aquanox SSA<sub>TM</sub> is a trademark of Kyzen Corporation. EC- $7R_{TM}$  is a trademark of Petroferm Inc. RE-ENTRY<sub>TM</sub> is a registered trademark of Environsolv Inc.

References: ASTM: American Society for Testing and Materials (U.S.A.) PSTC: Pressure Sensitive Tape Council (U.S.A.) S1: International Systems of Units.

## II. 2 mil Tan Thermal Transfer Printable Polyimide

#### **Heat/Chemical Resistance**

Labels printed with 3:1 ratio barcodes with 6 mil (0.152mm) X dimension bars. Samples exposed to indicated environments.

Test Environment	RMER4BL		RMER4BL-C		RMEH4BL	
	Rating before	Rating after	Rating	Rating after	Rating	Rating after
	exposure <sup>1</sup>	exposure <sup>1</sup>	before	exposure <sup>1</sup>	before	exposure <sup>1</sup>
			exposure <sup>1</sup>		exposure <sup>1</sup>	
Control	D	D	А	А	А	А
260C heat, 5 minutes	С	С	А	А	А	А
170C heat, 2 hours	D	D	А	А	А	А
Kyzen Corp, Aquanox	D	D	А	А	А	А
SSA, 30% aqueous,						
40-45C, 10 minutes <sup>2</sup>						
RE-ENTRY.KNI 2000	D	D	А	А	А	А
Terpene, 40-45C,						
10 minutes <sup>2</sup>						
Alpha Metals Inc. 2110	D	D	А	А	А	А
Saponifier, 6% aqueous,						
65-70C, 10 minutes <sup>2</sup>						
Isopropanol 99%, 82C, 10	C	C	А	А	А	А
minutes						
Deionized water, 100C,	С	C	А	А	А	А
10 minutes						
1,1,1 Trichloroethane,	C	C	А	А	А	А
74C, 10 minutes						



18900 Panduit Drive Tinley Park, IL 60487 Customer Service: 800-777-3300 TDS: Effective Date: Revision: GMK4 20APR2017 8

### **Technical Data Sheet**

Test Environment	RMER4BL		RMER4BL-C		RMEH4BL	
BIOACT EC-7R Terpene	С	С	А	А	А	А
Cleaner,						
40-45C, 10 minutes <sup>2</sup>						
Acetone, 30C,	D	D	А	А	А	А
10 minutes						

1 Rating determined using PSC QuickCheck 850 Scanner.

2 Followed by 2 minute immersion in deionized water at 100C.

#### PROPERTIES

Chemical Resistance

#### TEST METHOD

MIL-STD-202G, Notice 12, Method 215K

Labels printed with alphanumerics and 3:1 ratio barcodes with 6 mil (0.152mm) X dimension bars. Samples subjected to 3 cycles of three minute immersions immediately followed by a toothbrush rub after each immersion.

TEST FLUID	RMER4BL	RMER4BL-C	RMEH4BL
Solvent A	No visible effect	No visible effect	No visible effect
1 part IPA, 3 parts Mineral Spirits			
Solvent B	Solvent deleted per	Solvent deleted per	Solvent deleted per
1,1,1 Trichloroethane	Notice 12	Notice 12	Notice 12
Solvent C	No visible effect	Loss in print density	No visible effect
Terpene Defluxer			
Solvent D	No visible effect	No visible effect	No visible effect
Saponifier			

Aquanox SSA<sub>TM</sub> is a trademark of Kyzen Corporation. EC- $7R_{TM}$  is a trademark of Petroferm Inc. RE-ENTRY<sub>TM</sub> is a registered trademark of Environsolv Inc.

References: ASTM: American Society for Testing and Materials (U.S.A.) PSTC: Pressure Sensitive Tape Council (U.S.A.) S1: International Systems of Units.

#### **APPROVALS**

UL Recognized: UL 969 CUL Recognized: C22.2 No. 0.15-01 File Number: MH 14979 File Number: MH 14979

#### LIMITED WARRANTY

All *PANDUIT* Identification Solution Products (except for Software programs) are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to replacement of the product proved to be defective within 6 months from the date of sale, or in the case of printers, within 90 days from the date of sale. This warranty is void if the products or printers are modified, altered or misused in any way. Use of *PANDUIT* printers with any product other than the specified *PANDUIT* products for which the printer was designed constitutes misuse. Before using, the user shall determine the suitability of the product for its intended use and user assumes all risk and liability whatsoever in connection therewith. The foregoing may not be altered except by an agreement signed by officers of seller and manufacturer.

NEITHER *PANDUIT* NOR SELLER SHALL BE LIABLE FOR ANY OTHER INJURY, LOSS OR DAMAGE, WHETHER DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OF, OR THE INABILITY TO USE THE PRODUCT OR THE PRINTER.

THIS WARRANTY IS MADE IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS OF PARTICULAR USE ARE SPECIFICALLY EXCLUDED.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide or use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. This publication is not be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.