







PANDUIT P/N	WEIGHT
JASSPTP**	.23 LB/10 PCS (106.2 g/10 PCS)

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [ ] ARE IN METRIC.
4. PARTS INCLUDED IN KIT:
  - (1) -ADAPTER WITH CLEAR DOOR AND LAN/CAT 6 PRINT
  - (1) -MINI-COM TX6 PLUS JACK MODULE



VIEW SHOWN WITH A MINI-COM TX6 PLUS JACK MODULE INSTALLED.



PART NUMBER		JASSPTP***			
TITLE					
MINI-COM 1 POSITION JIS SPRING SHUTTERED ADAPTER KIT					
CUSTOMER DRAWING					
ITEM REVISION NAME		M02079AU/00			
DATASET FILE NAME		M02079AU_DC/00C			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]  .X ± .XXX ± .010 [ .3 ] .XX ± .03 [ .8 ] 				MATERIAL :  ADAPTER: ABS DOOR: PC SPRING: SPRING STEEL	
THIRD ANGLE PROJECTION				DRAWING NUMBER: 02079-07	
DRAWN BY	DATE	CHK	SCALE	SIZE	
JSP	8-1-05	JCO	NONE	SHT 1 OF 1	
				A	

D10100DA/14