


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SYSTEM INCLUDES:

- (2) ROCKWELL 91.2W 24 VOLT DC POWER SUPPLIES (1606-XLSDNET4)
- (2) STAHL 10 AMP LOCKOUT CONTACT BLOCKS (8082/1-1-01)
- (2) WEIDMULLER RED AND WHITE TERMINAL BLOCKS FOR INCOMING POWER (100-240 VAC 50-60HZ)
- (1) PANDUIT 6-PORT GROUND BAR


2. POWER CIRCUIT DESIGNED FOR ONE OR TWO 24 VOLT DC INDUSTRIAL ETHERNET SWITCHES NOT TO EXCEED 42 WATTS PER SWITCH

3. ALL ACTIVE COMPONENTS RATED FOR USE CLASS 1, DIVISION 2 ENVIRONMENTS

4. ALL ZONE SYSTEMS COMPLY WITH UL 508A STANDARDS

5. ALL ZONE SYSTEMS REQUIRE A 100-240 VOLT AC SINGLE-PHASE FEED

6. INTERNAL WIRING NOT SHOWN, SEE DRAWING (15V510RB) FOR COMPLETE SCHEMATIC

							TITLE						
							NETWORK ZONE SYSTEM, 100-240VAC INPUT, REDUNDANT 91.2W 24VDC POWER SUPPLIES						
							CUSTOMER DRAWING						
							ITEM REVISION NAME		15V510JC/01				
							DATASET FILE NAME		15V510JC_DC/01A				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					MATERIAL:	
							.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					N/A	
											DRAWING NUMBER:	15V510JC	
							THIRD ANGLE PROJECTION						
01A	1/11/17	JBO	NWW	TIMH	UPDATED POWER SUPPLIES	15V510JC	DRAWN BY		DATE	CHK	SCALE	SHT 1 OF 1	SIZE
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	JBO		10/26/16	NWW	1:4		A