


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. TERMINATED WITH (8 POSITION) UTP MODULAR PLUGS ON BOTH ENDS PER T568B.
2. CONSTRUCTED WITH 4-PR/26AWG STRANDED U/UTP CAT6A PATCH CABLE
3. MATERIAL :  
 PLUG: POLYCARBONATE  
 BOOT: THERMOPLASTIC RESIN
4. FLAMMABILITY RATING: CM RATED



LENGTH	TOLERANCE
1 M	+50mm/-0mm
2 M	
3 M	+100mm/-0mm
4 M	
5 M	
7 M	
10 M	

XX = LENGTH

COLOR	DESIGNATOR
BLUE	BU
RED	RD
OFF-WHITE	--

\*\* = COLOR

T568B WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

PART NUMBER		NKU6APCXXM**	
TITLE			
NETKEY™		CATEGORY 6A UTP PATCH CORD	
CUSTOMER DRAWING			
ITEM REVISION NAME		00821EAA/00	
DATASET FILE NAME		00821EAA_DC/00A	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTE 3	
DRAWING NUMBER		00821EAA-DC	
REV	DATE	BY	CHK
00A	2-3-21	BJN	MATO
APR	DESCRIPTION	ECN	SCALE
	RELEASED TO PRODUCTION	008221EAA-DC	NONE
SHEET 1 OF 1		A	

A-SIZE CUSTOMER