
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	TAB SIZE	WIRE RANGE AWG (mm²)	COLOR	MAX. INSUL.	MIN. INSUL.	DIMENSIONS in.[mm]			TOOL CHART RECOMMENDED PRESSES: CP-861, CP-862, CP-871
						L ±.03 [0,76]	H ± .02 [0,51]	W ± .02 [0,51]	CA-800EZ/CA9 APPLICATOR DIE INSERTS
DPF18-250FIMB	.250 x .032 [6,3 x 0,8]	22-18 [0,5-1,0]	RED	.13 [3,3]	.06 [1,5]	.92 [23,4]	.34 [8,6]	.46 [11,7]	CD-800-10 CD9-10B
DPF14-250FIMB	.250 x .032 [6,3 x 0,8]	16-14 [1,5-2,5]	BLUE	.16 [4,1]	.09 [2,3]	.92 [23,4]	.34 [8,6]	.46 [11,7]	CD-800-11 CD9-11B

NOTES:

 B

- 1. USED FOR:
 - A. 600V MAX VOLTAGE RATING
 - B. TEMPERATURE RATING OF INSULATION: 221°F [105°C]
 - C. STRANDED COPPER WIRE ONLY
- 2. WIRE STRIP LENGTH: $9/32^{+1/32}_{-0}$ (7,1 +,8)
- 3. MATERIAL:
 - A. STAMPING: NICKLE PLATED BRASS
 - B. HOUSING: PREMIUM GRADE NYLON FOR SUPERIOR STRAIN RELIEF INSULATION CRIMPING
- 4. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT







ECTS, ≠22-14	
22 11	
PANDUIT	
SEE NOTES	
S	A
	UMBER: A 4 1 5 1 3