



2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
NKDS2S**	.61 LB/10 PCS (277.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE IN METRIC.
4. PART INCLUDES:
 - 1- ADAPTER
 - 1- 2 POSITION NETKEY SLOPED SHUTTERED 1/2 INSERT
 - 1- BEZEL
 - 2- SCREW
 - 2- CLAMP
 - 1- LABEL
 - 1- LABEL COVER



PART NUMBER		NKDS2S**	
TITLE			
NETKEY 2 POSITION DENMARK SLOPED SHUTTERED FACEPLATE KIT			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02463AF/00	
DATASET FILE NAME		M02463AF_DC07/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT	
.X ± .XX ± .03 [.8]		MATERIAL: ADAPTER/INSERT- ABS CLAMP- C.R.S. SCREW- STEEL	
.XXX ± .010 [.3] ANGLES ±		DRAWING NUMBER: 02463-07	
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
JSP	6-17-06	EB	NONE
SHT 1 OF 1			SIZE A

2

1

D10100DA/14