


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SP688-*	.047 lb/10 PCS (21.4 g/10 PCS)

NOTES:

1. MATERIAL: HOUSING, LOAD BAR, DIVIDER, STRAIN RELIEF COLLAR - THERMOPLASTIC UL94V-0 RATED; STRAIN RELIEF BOOT - CLEAR PVC; CONTACT TERMINAL - PHOSPHOR BRONZE ELECTRO-POLISHED AND PLATED WITH .000050" MIN. GOLD IN MATING AREA, GOLD FLASH OVER REMAINDER, .000100" MIN. NICKEL UNDERPLATE.
2. PLUG ACCEPTS 4 PAIR CABLE .225-.250" DIA. WITH 23-24 AWG CONDUCTORS WITH A MAXIMUM INSULATOR DIAMETER OF .040".
3. MEETS DIMENSIONAL REQUIREMENTS OF FCC PART 68 AND IEC 60603-7. ALL DIMENSIONS MAXIMUM UNLESS OTHERWISE SPECIFIED.
4. TERMINATED CONTACT HEIGHT DIMENSION: .237±.005".
5. SEE WWW.PANDUIT.COM FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.



STRAIN RELIEF BOOT

STRAIN COLLAR

DIVIDER

LOAD BAR

PLUG HOUSING W/CONTACTS

PART NUMBER		SP688-*	
TITLE			
TX6 PLUS MODULAR PLUG FOR CATEGORY 6 PATCH CORDS		CUSTOMER DRAWING	
ITEM REVISION NAME		M01185CC/08	
DATASET FILE NAME		M01185CC_DC15/08B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xxx ± .010 [.3]		SEE NOTE 1	
.xx ± .03 [.8] ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		01185-15	
DRAWN BY	DATE	CHK	SCALE
MDJr	9-30-02	NGM	NONE
DESCRIPTION		SHT 1 OF 1	
ECN		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
08B	7-11-23	BJN	REFR	SKH	UPDATED	M09000TP
08A	6-16-21	BJN	SGO	TMBA	UPDATED	01185-15
7	6-10-16	BJN	SIP	SASK	UPDATED	01185-15
6	5-14-14	BJN	EJH	EJH	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	01185-15

D10100DA/14