


PANDUIT PART NO.	BUNDL MIN. (mm)	MAX. (mm)	A in (mm)	B in (mm)	in (mm)	MIN. LOOP* TENSILE lbs.	ROLL DESCRIPTION	
HLS1.5S	.25 (6.4)	1.5 (38.1)	.100 (2.5)	6.0 (152)	.750 (19.1)	50 (222)		
HLS3S	.25 (6.4)	3.2 (81.3)	.100 (2.5)	12.0 (305)	.750 (19.1)	50 (222)	PERFORATED STRIPS QTY: 10	
HLS5S	.25 (6.4)	5.0 (127)	.100 (2.5)	18.0 (457)	.750 (19.1)	50 (222)	PIECES/ROLL	
HLS-15R	.25 (6.4)	VARIOUS	.100 (2.5)	180 (4572)	.750 (19.1)	50 (222)	15 FT 1 SPLICE MAX.	
HLS-75R	.25 (6.4)	VARIOUS	.100 (2.5)	900 (22860)	.750 (19.1)	50 (222)	75 FT 2 SPLICE MAX.	



NOTES:

- 1) ALL LENGTHS PACKED IN ROLL FORM (SEE ILLUSTRATION 'A')
- * 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
 - 3) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR OPTIONAL COLORS.

									1
A								TAK-TY HOOK & LOOP CABLE TIES HLS SERIES CUSTOMER DRAWING	A
								SS-27184/AC DATASET FILE NAME SS_27184_06/A	
	06	01–14–19	SAT	DWW	ML	B. UPDATED MATERIAL. A. REMOVED APPROXIMATE WEIGHT COLUMN.	27184	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] BACK-TO-BACK HOOK & LOOP HOOKS: POLYETHYLENE OR NYLON.	
	5	8/27/14	RVU	DJW	KLN	ADDED 1 SPLICE MAX FOR HLS-15R. ADDED 2 SPLICE MAX FOR HLS-75R.	GAECN02271	.x ± .xxx ± L00PS: NYL0N	4
	4	6/5/06	FAB			ADDED PART WEIGHT TO DRAWING.	27184	THIRD ANGLE PROJECTION SS-27184	
	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	CHK SCALE NONE SHT 1 OF 1 SIZE CHK STALE SHT 1 OF 1 CHK SIZE CHK STALE CHK SIZE CHK SIZE	