Net-Access[™] N-Type Cabinets

specifications

Net-Access[™] N-Type cabinets are ideal for network applications as these cabinets come standard with tapped, front non-adjustable and rear adjustable equipment rails to accommodate switch applications. The top of cabinet includes molded edge protection and snap-in covers, and pre-installed in cable entry openings to prevent air leakage. N-Type Cabinets are manufactured with a welded and assembled steel frame and are available in multiple widths, depths and RU heights.

Standard N-Type Features:

- Front dual or single hinge doors with 69% open perforation
- · Dual hinge front door allows door to open to the left or right
- · Rear perforated split doors with 69% opening
- · Inset frame for improved cable management
- · Fully electrically bonded equipment rails, door, and side panels
- · Single point bonding at top and bottom of cabinet
- Two sets of 6" Cable Management Fingers included
- · Static Load Rating 3000 lbs. & Rolling Load Rating 2500 lbs.

technical information

Available Cabinet Sizes:	RU	Width	Depth	
	42		1070mm (42.12")	
	45	800mm (31.5")	1200mm (47.21")	
	48			
Material:	Steel with durable black or white polyester epoxy powder coat finish			
Compliance:	EIA-310-E, TIA/EIA-942, UL2416			
Packaging:	Cabinet ships assembled, one per pallet			
Application:	Indoor 19" rack mount equipment enclosure. Complete range of sizes and integration with Net-Contain VED and all Aisle Containment Systems optimize thermal efficiency.			

key features and benefits

Versatility	Wide range of cabinet designs available for specific thermal applications, resulting in improved thermal efficiencies and reductions in energy expenditures
Total air sealing	Panduit cabinets, thermal ducting, Cool Boot [®] product, integral blanking panels, blanking foam strips, and blanking shade provide a complete thermal and sealing solution by reducing bypass air and mixing of cold air and exhaust air within the cabinet for improved thermal efficiency. (thermal parts sold separately)
Compatibility	N-Type and S-Type Cabinets can be ganged together for complete streamlined appearance improving data center aesthetics
Rapid deployment	Cable management ready rails included help speed deployment; easily adjustable rear rails can be quickly repositioned; heavy duty leveling legs can be accessed from top or bottom for faster deployment
Bonding	Cabinets and accessories are single-point bonded, providing a safe and reliable network while reducing installation costs
Cable Management Fingers	Provides bend radius control for each rack unit and can be positioned where required on cabinet posts for cable protection for increased network availability; provides design flexibility, scalability, and improved aesthetics for easier moves, adds, and changes
Expansive offering	Multiple cabinet configurations for hot aisle/cold aisle, cold aisle containment, or vertical exhaust ducting deployments





Net-Access[™] N-Type Accessories Doors Dual Hinge, 45 RU: N85DHD Split Door, 45 RU: SN85SD Side Panels N-Type Standard Side Panel 45 RU x 1070mm: N51SPS* Cable Management Vertical Cable Management Bracket: SN8VCM Front to Back Cable Management Bracket: SN8FBB 4" (100mm) 42-45 RU Finger Kit: SN15F 4" (100mm) 48 RU Finger Kit: SN18F 6" (150mm) 42-45 RU Finger Kit: SN25F 6" (150mm) 48 RU Finger Kit: SN28F Center Slack Spool: NACSS End of Row Slack Spool: NERSS Cool Boot® Seal Fitting 3.5 x 5": CTGN3X5 6.5 x 6.5": CTGN6X6 PDU Brackets Enhanced N-Type Brackets: NVPDUBE Casters Caster Kit, 2 Rear Swivel Casters, 2 Fixed Front Casters: NCSTR4 Vertical Blanking Panels Vertical Blanking Panel with pass-through holes for cabinets 42-48 RU: NVBP Equipment Rail Kits 45 RU Cage Nut Rail -2 front and 2 rear rails: N5RCFR 45 RU Tapped Rail -2 front and 2 rear rails: N5RTFR Combination Lock with Key Three Digit Combo Lock with Key: CCI 3

*Denotes Part Number Also Available in White Refer to Catalog for Complete List of Accessories



Series	Width	Height	Depth	Side Panels	Color	Standard Options (Select Only One)
N	8 = 800mm	2 = 42 RU	1 = 1070mm	2 = 2 Side	B = Black	C = Cage Nut Rails
		5 = 45 RU	2 = 1200mm	Panels	W = White	E = Single Hinge Front Door
		8 = 48 RU		9 = No Side		and Cage Nut Rails
				Panel		U = Vertical Blanking and Cage Nut Rails

2

В

1


Net-Access N-Type standard configured cabinets

2

N-Type cabinet dimensions

8

Ν



Dimension A	Dimension B	Dimension C	Dimension D
1070mm (42.0")	1115mm (43.9")	42 RU - 2000mm (78.8")	000mm (01 Ell)
1200mm (48.0")	1269mm (50.0")	45 RU - 2134mm (84.0") 48 RU - 2267mm (89.3")	800mm (31.5")

Rail Span Dimensions

N-Type Rail Span				
Width Depth		Front of Frame to Front Rail	Front to Rear Rail Span	
800	1070	6.9" (175mm)	5.1" - 12.9" (130mm - 327mm) / 16.2" - 23.6" (412mm - 599mm)	
800	1200	6.9" (175mm)	5.1" - 16.2" (130mm - 412mm) / 18.5" - 29.5" (469mm - 751mm)	

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA	PAN
Phone: 800.777.3300	Lon
	DI

NDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

© 2020 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. RKSP173--WW-ENG 5/2020