



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:


- STANDARD
 UNIT TYPE: MONITORED INPUT
 ORIENTATION: VERTICAL, 0U MID
 OUTLET QTY & TYPE: (18)C13, (3)C19
 INPUT VOLTAGE: 100-240VAC
 INPUT FREQUENCY: 50/60HZ
 INPUT CURRENT: 16A
 BREAKER QTY & TYPE: NONE
 INPUT PHASE: SINGLE-PHASE
 RATED POWER: 3.7 kVA
 INPUT PLUG: IEC 60309 2P+E 6H 16A
 INPUT POWER CORD: SEE SHEET 2 PART NUMBER TABLE
 REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL:
NONE
- ACCESSORIES:
DOCUMENTATION KIT
PRODUCT SAFETY WARNING SHEET

NOTES:


- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSIONS ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION:

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: E21D10M-XXYZ



PLUG / RECEPTACLE BLOCK




00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E21D10M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU E21D10M CONTROL DRAWING		
ITEM REVISION NAME:		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN] Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0		MATERIAL/COLOR: N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: E21D10M_DC
DRAWN BY LL	DATE 08/29/2023	CHK MIM
SCALE NONE	SHT 1 OF 2	
		SCALE B

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
E21D10M	MI PDU, 16A, (18)C13 (3)C19, IEC 60309 2P+E 6h IP44-3M, TOP-FED, BLACK	BLACK(RAL 9005)	3M(+254MM/-127MM)[10'(+10"/-5")]	4.5kg

00A	08/29/2023	LL	MIM	MJD	INITIAL RELEASE	E21D10M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU E21D10M CONTROL DRAWING		
ITEM REVISION NAME:		PANDUIT
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
 Tolerance (mm) 0 < L ≤ 50 ±0.5 50 < L ≤ 250 ±1.0 250 < L ≤ 500 ±1.5 500 < L ≤ 1000 ±2.5 1000 < L ≤ 2000 ±4.0 THIRD ANGLE PROJECTION		DRAWING NUMBER: E21D10M_DC
DRAWN BY	DATE	SCALE
LL	08/29/2023	NONE
CHK	MIM	SHT 2 OF 2
		SCALE B