

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



В

7	PANDUIT PART NO.	'A' MAX.	'B'	'C' MIN.	'D' HOLE SIZE	REC. FAST.				'H' WHEN USED DIATE STRAPS	WEIGHT Ibs (gs) / 100 pcs.
	FCBI1-S10	2.50 [83.5]	2.08 [52.8]	1.04 [26.4]	.200 [5.1]	#10 (MS) SCREW	.8 [20.3]	2.0 [50.8]	3.7 [94]	5.2 [132.1]	.30 [136.21]
	FCBI2-S10	3 50	3.10 [87.7]	2.04 [51.8]	.200 [5.1]	#10 (MS) SCREW		1.0 [25.4]	2.7 [68.6]	4.2 [106.7]	.43 [195.2]
	FCBI3-S10	4.52 [114.8]	4 12 [104 6]	3.04 [77.2]	.200 [5.1]	#10 (MS) SCREW			1.7 [43.2]	3.2 [81.3]	.48 [263.3]



2

3

FCBI(_) H (MAX.) /3

В

NOTES: * 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE. **2. CUSTOMER MUST FURNISH ADHESIVE. 3. PRODUCT CAN BE USED WITH PLATE

FCP(_), REFER TO <u>GB0239KV</u>.
BAG MAY CONTAIN EXTRA PIECES TO COMPENSATE FOR VARIANCE IN THE PACKAGING PROCESS. PANDUIT ASSURES MINIMUM PIECE COUNT AS STATED ON THE BAG.



	3	6/1/2021	RVU	JADE	RMHI	REBUILD MODEL AND UPDATE DRAWING. ADDED NOTE 4. REMOVED FCBI1-A, FCBI2-A AND FCBI3-A.	GAECN05612	2 UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] NYLON 6/6		
	2	5/16/18	RVU	DJW	JHAC	INCREASE TOLERANCE .XX FROM +/02 TO +/030.	GAECN04603	03 .xx ± .05 [1.3] .xxx ± 0.010 [0.25] COLOR: BLACK .xx ± .030 [.762] ANGLES ± 5 ° COLOR: BLACK		
DA/20	1	8/12/04	JAD			UPDATE NOTE 3, ADD * TO NOTE 1 & 2.	GB0239HY	THIRD ANGLE DRAWING NUMBER: PROJECTION GB0239HY		
D10100	REV	DATE	ΒY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE STZE JAD 8/12/04 JHAC NONE SHT 1 OF 1 A		

∕3∖

2