Net-Contain™ Vertical Exhaust Ducts (VEDs) for Net-Access™ N-Type and S-Type Cabinets



specifications

Vertical exhaust duct shall channel heat from server exhaust directly to the data center return plenum. The system shall increase CRAH unit cooling efficiency and lower operating expenses. The vertical exhaust duct shall leverage existing server fans to direct the flow of hot exhaust air, reducing energy costs and noise levels. The system shall be passive, containing no moving parts resulting in a more energy efficient solution than comparable forced-air options. The vertical exhaust duct shall address high heat loads per cabinet to enable dense server applications and eliminate data center hot spots. The vertical exhaust duct shall be modular, capable of being added without disrupting existing in-cabinet equipment and cabling to enable a migration path.



technical information

Dimensions: C2VED08I1626*1: 16.0" up to 26.0"H x 30.5" W x 17.9" D (406.4mm up to 660.4mm x 763.5mm x 454.5mm)

26.0" up to 38.0"H x 30.5" W x 17.9" D C2VED08I2638*1:

(660.4mm up to 965.2mm x 763.5mm x 454.5mm)

C2VED08I3866*1: 38.0" up to 66.0"H x 30.5" W x 17.9" D

(965.2mm up to 1676.4mm x 763.5mm x 454.5mm)

C2VED07I1626*1: 16.0" up to 26.0"H x 26.1 W x 17.9" D (406.4mm up to 660.4mm x 663.5mm x 454.5mm)

C2VED07I2638*1: 26.0" up to 38.0"H x 26.1 W x 17.9" D

(660.4mm up to 965.2mm x 663.5mm x 454.5mm)

C2VED07I3866*1: 38.0" up to 66.0"H x 26.1 W x 17.9" D

(965.2mm up to 1676.4mm x 663.5mm x 454.5mm)

C2VED06I1626*1: 16.0" up to 26.0"H x 22.2"W x 17.9"D (406.4mm up to 660.4mm x 563.5mm x 454.5mm)

C2VED06I2638*1: 26.0" up to 38.0"H x 22.2"W x 17.9"D

(660.4mm up to 965.2mm x 563.5mm x 454.5mm) C2VED06I3866*1:

38.0" up to 66.0"H x 22.2"W x 17.9"D

(965.2mm up to 1676.4mm x 563.5mm x 454.5mm)

key features and benefits

Transfers heat load directly Lowers energy costs up to 40% and capital construction expenditures for to return plenum to reduce increased network reliability and lowest cost of ownership the number of CRAH units Prevents hot spots and allows

installation of high-density server cabinets close together in new builds or existing data centers

Reduces the need for extra real estate and additional CRAH units for increased data center cooling

Works with leading server suppliers (HP, IBM, Dell, Sun) via uniform and proper air flow distribution within servers

Verified interoperability, minimizes risk of overheating for increased network reliability

Contains no moving parts to passively direct the heated air out of the data center

Eliminates acoustical noise and failure points for increased network reliability

Reduces the need for flow balancing in raised floor and return plenums

Minimizes local hot spots within the data center and improves CPU/network reliability

Infinitely adjustable within specified range of vertical exhaust system

Allows for variable ceiling heights and ease of installation

applications

Net-Contain™ Vertical Exhaust Ducts optimize data center airflow for a highly efficient passive thermal management solution by channeling heat from the cabinet directly to the overhead ceiling return plenum increasing cooling efficiency and significantly lowering operating expenses. This passive exhaust system removes heated air without additional moving parts

and enables increased server densities by preventing hot and cold air mixing and eliminating hot spots. The vertical exhaust system can be utilized during an initial installation or can be added when required as heat densities increase. Cabinets with VED solution must utilize a solid rear door to direct the hot air to the above plenum area.

Net-Contain™ Vertical Exhaust Ducts (VEDs

For 800mm W Net-Access™ Cabinet, 16" up to 26"H:

C2VFD08I1626*1

For 800mm W Net-Access™ Cabinet, 26" up to 38"H:

C2VED08I2638*1

For 800mm W Net-Access™ Cabinet, 38" up to 66"H: For 700mm W

C2VED08I3866*1

Net-Access™ Cabinet, 16" up to 26"H: For 700mm W

C2VED07I1626*1

Net-Access™ Cabinet, 26" up to 38"H:

C2VED07I2638*1

For 700mm W Net-Access™ Cabinet, 38" up to 66"H: For 600mm W

C2VED07I3866*1

Net-Access™ Cabinet, 16" up to 26"H: For 600mm W Net-Access™ Cabinet,

C2VED06I1626*1

26" up to 38"H: For 600mm W

C2VED06I2638*1

Net-Access™ Cabinet, 38" up to 66"H:

C2VED06I3866*1

Net-Access™ N-Type Cabinets 800mm x 45 RU x 1200mm

45 RU, front dual hinge door, rear solid split doors, cage nut rails, vertical blanking panels, cable management vertical

exhaust duct ready: N8529*Y

45 RU, front dual hinge door, rear solid split doors, (1) side panel, cage nut rails, vertical blanking panels, cable management vertical exhaust duct ready:

N8521*Y

45 RU, front dual hinge door, rear solid split doors, 12-24 tapped rails, vertical blanking panels, cable management vertical exhaust duct ready:

N8529*N

45 RU, front dual hinge door, rear solid split doors, (1) side panel, 12-24 tapped rails, vertical blanking panels, cable management vertical exhaust duct ready:

N8521*N

Net-Access™ S-Type Cabinets

600mm x 42 RU x 1200mm

42 RU, single hinge perforated front door, single solid rear door, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S6229*V

42 RU, single hinge perforated front door, single solid rear door, (2) side panels, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S6222*V

Net-Contain™ Vertical Exhaust Ducts (VEDs) for Net-Access™ N-Type and S-Type Cabinets

Ceiling Return Plenum Under Floor Plenum Hot Spots Develop Without VES


In a traditional raised floor with ceiling returns configuration (hot aisle/cold aisle) hot air can recirculate to the front of the enclosure, heating the top portion of the rack.

The Panduit VED optimizes thermal efficiency by moving hot air through vertical ducts directly to the return plenum.

Ceiling Return Plenun With VED Cold Aisle Under Floor Plenum

Without

VED



Part Number	Height	Width	Depth
C2VED08l3866*1 C2VED07l3866*1 C2VED06l3866*1	38.0" up to 66.0" (965.2mm up to 1676.4mm)	30.5" (763.5mm) 26.1" (663.5mm) 22.2" (563.5mm)	17.9" (454.5mm)
C2VED06I36606 1 C2VED08I2638*1 C2VED06I2638*1	26.0" up to 38.0" (660.4mm up to 965.2mm)	30.5" (763.5mm) 26.1" (663.5mm) 22.2" (563.5mm)	
C2VED06l2638 1 C2VED08l1626*1 C2VED07l1626*1 C2VED06l1626*1	16.0" up to 26.0" (406.4mm up to 660.4mm)	30.5" (763.5mm) 26.1" (663.5mm) 22.2" (563.5mm)	

Net-Access™ S-Type Cabinets

600mm x 45 RU x 1200mm

45 RU, single hinge perforated front door, single solid rear door, casters, pou brackets, cage nut rails, vertical exhaust S6529*V ready, front and rear floor seals: 45 RU, single hinge perforated front door, single solid rear door, (2) side panels, casters, pou brackets, cage nut rails, vertical exhaust ready, front and S6522*V rear floor seals:

700mm x 42 RU 1200mm

42 RU, single hinge perforated front door, single solid rear door, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S7229*V

42 RU, single hinge perforated front door, single solid rear door, (2) side panels, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S7222*V

700mm x 45 RU 1200mm

45 RU, single hinge perforated front door, single solid rear door, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S7529*V

45 RU, single hinge perforated front door, single solid rear door, (2) side panels, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S7522*V

800mm x 42 RU x 1200mm

42 RU, single hinge perforated front door, single solid rear door, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S8229*V

42 RU, single hinge perforated front door, single solid rear door, (2) side panels, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S8222*V

800mm x 45 RU x 1200mm

45 RU, single hinge perforated front door, single solid rear door, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S8529*V

45 RU, single hinge perforated front door, single solid rear door, (2) side panels, casters, pou brackets, cage nut rails, vertical exhaust ready, front and rear floor seals:

S8522*V

*Indicates optional colors. Replace * with B = Black, or W = White

Dimensions are in inches. (Dimensions in parenthesis are metric).

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information



Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300

