


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	COLOR	MARKER SIZE	LABELS PER SHEET	SHEET PER PKG.	STANDARD PKG. QTY.
C750X050Y1J	GM Y8	WHITE	7.50 [ 190.50 ] X 0.50 [ 12.70 ]	16	32	500



.50 [12.70]  
TYP. 16 PLCS.

NOTES:  
1. MILLIMETERS ARE IN [ ].

1. SELECT C750X050Y1J AS DESIGNATED PART IN PANDUIT LABELING SOFTWARE PROGRAM.
  2. INSERT DATA TO BE PRINTED INTO SOFTWARE PROGRAM.
  3. INSERT SHEET INTO MANUAL FEED TRAY OF INKJET OR LASER PRINTER.
  4. AFTER PRINTING, REMOVE STRIPS AND INSERT INTO ULTIMATE I.D. SYSTEM FACEPLATE.
- ADDITIONAL SIZES AVAILABLE FOR A WIDE VARIETY OF ULTIMATE I.D. SYSTEM COMPONENTS.  
FOR TECHNICAL ASSISTANCE CALL: 1-866-871-4571

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:
							<b>C750X050Y1J</b> <b>OPTIMUM LASER/INKJET COMPONENT LABEL</b> CONTROL DRAWING	<b>PANDUIT</b>
							ITEM REVISION NAME <b>I00673CF/01</b>	
							DATASET FILE NAME <b>I00673CF_DC_C10170/01B</b>	
1	8/17/15	RVU	SEWH	JHAC	UPDATE ON PANDUIT LOGO. CHANGE BORDER FROM B TO A. UPDATE TABLE, NOTES, AND T. TITLE. 2 PLCS. GMY8 WAS GM3SIGY2-925W. ADD 500. CHANGE PHONE NUMBERS.	GAECN03097	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] .x ± .12 [ 3.05 ] .xxx ± .025 [ 6.35 ] .xx ± .062 [ 1.57 ] ANGLES ±	<b>SEE TABLE</b>
0	8/5/04	JMHO			DRAWING RELEASE.	4949	THIRD ANGLE PROJECTION	DRAWING NUMBER: <b>C10170</b>
RVU	8/5/04	JHAC					SCALE <b>1/2</b>	SHT 1 OF 1
								SIZE <b>A</b>