



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SRBBRM-KIT	.74 LB/EACH PC (335.7 g/EACH PC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- STRAIN RELIEF BAR
 - 6- TAK-TY
 - 1- #12-24 SCREW KIT
 - 2- RATCHET FASTENER
 - 2- LATCH BRACKET
 - 2- TAB BRACKET (ASSEMBLED TO THE STRAIN RELIEF BAR)



PART NUMBER		SRBBRM-K I T	
TITLE			
STRAIN RELIEF BAR KIT WITH SRBM19BLY AND QUICK RELEASE BRACKETS			
CUSTOMER DRAWING			
ITEM REVISION NAME			
M02644AA/01			
DATASET FILE NAME		MATERIAL: STRAIN RELIEF BAR: C.R.S. QUICK RELEASE BRACKETS: C.R.S.	
M02644AA_DC01/01A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03[.8] ANGLES ±			
		THIRD ANGLE PROJECTION	
DRAWING NUMBER:		02644-01	
DRAWN BY	DATE	CHK	SCALE
JSP	9-19-06	MJD	NONE
SHT 1 OF 1		SIZE A	