


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

* PANDUIT PART #	A (REF) IN (mm)	B (REF) IN (mm)	F IN (mm)	APPROXIMATE WEIGHT LBS. (g)
PC14C13BL1.5	.33 (9.14)	2.475 (62.86)	18.0 (457 mm)	.19 (88.0)
PC14C13BL2			24.0 (610 mm)	.23 (106.0)
PC14C13BL3			36.0 (914 mm)	.31 (140.0)
PC14C13BL4			48.0 (1219 mm)	.38 (174.0)

NOTES:

- \*1) SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- 2) RATING: 10A/250V AC, 13A /125V AC.
- 3) CORD ASSEMBLY HAS THESE APPROVALS: VDE, CE, UL, CSA OR cUL.
- 4) PRODUCT IS RoHS COMPLIANT AND REACH COMPLIANT.



CAD FILENAME/LAYERS W10001DL\_DC\_SS-41986/01A

PANDUIT CORP. TINLEY PARK, ILLINOIS

C-13 TO C-14 POWER CORDS

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± 2.5" (.XXX) ±  
(.XX) ± .02" ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

01A	7-14-11	TMSA	DJW	ADDED PART NUMBER PC14C13BL4	SS-41986	01A	GLZ														
R	8/12/09	BWG	DWW	DRAWING RELEASED	SS-41986	00															
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP													

DRAWN BY BWG  
DATE 8/12/09  
CHK'D GLZ

MAT'L:  
SCALE NTS  
DRAWING NO. SS-41986  
DWG SIZE A