

BT2HT


MS STRAPPING TOOL OPERATION INSTRUCTIONS


© Panduit Corp. 2017


INTRODUCTION

The BT2HT Tool installs Panduit Pan-Steel coated and uncoated MS Series strap and buckles in widths of 3/8" X .015" thick (9.5mm), 1/2" X .015" thick (12.7mm); and 5/8" X .015" and .025" thick (15.9mm).

Note: This tool is not intended for other uses such as cutting or tensioning other types of fastening devices.







TOOL FEATURES

- A. Rear Handle
- B.* Tension Pawl Release Knob pointing towards the front of tool for pawl engagement and to rear of tool for disengagement.
- C.* Anti-Backup Pawl Release Lever up against tool for pawl engagement and pulled down to disengage pawl.
- D.* Detent Lock Pins For controlled tension, pull both pins forward; for manual tension, push both pins backward.
- E. Cutter Handle Cuts tie when strap is tensioned properly.
- F. Cutter Blade
- G. Tensioning Mandrel
- H.* Tension Indicator Window Located on the back of front handle.
- I.* Adjustment Knob Adjust tension of strap application.
- J. Tension Locking Set Screw
- K. Front Handle With ratchet controlled tensioning.

* See Page 2 for Feature Detail

TOOL OPERATION

See Steps 1 - 8 on Pages 3 and 4.

E-mail: techsupport@panduit.com





Technical Support: 1-800-777-3300

OPERATION INSTRUCTIONS

TOOL MAINTENANCE


TO INHIBIT CORROSION AND MAINTAIN PERFORMANCE OF THE TOOL, KEEP THE METAL SURFACES COATED WITH A LIGHT OIL (WD-40 $^{\mbox{\scriptsize B}}$ OR EQUIVALENT).





OPERATION INSTRUCTIONS

BT2HT



OPERATION INSTRUCTIONS

BT2HT

