DP6[™] PLUS Punchdown Patch Panels



specifications

Category 6/Class E, punchdown patch panels shall terminate 4-pair, 22 – 26 AWG, 100 ohm unshielded twisted pair cable with an industry standard single wire 110 punchdown tool. Patch panels shall include a universal label coded for T568A and T568B wiring schemes and mount to 19 inches and 23 inches racks. Patch panels shall be easy to identify with pre-printed numbers, write-on areas and optional label kits.



technical information

Category 6/Class E channel and component	Exceeds channel requirements of ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E standards at swept frequencies 1 to 250 MHz	
performance:	Exceeds component requirements of ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E standards at swept frequencies 1 to 250 MHz	
FCC and ANSI compliance:	Meets ANSI/TIA-1096-A; contacts plated with 50 microinches of gold for superior performance	
IEC compliance:	Meets IEC 60603-7 and IEC 60512-99-002	
PoE and PoH compliance:	Meets IEEE 802.3af/802.3at and 802.3bt type 3 and type 4. Supports Power over HDBaseT up to 100 watts	
c(UL)us Listed:	UL 1863 (Use as communications circuit accessory); CSA standard C22.2	
Conductor termination range:	Wire cap compatible with 22 – 26 AWG solid or stranded cable with conductor insulation diameters of 0.060" max and overall cable O.D. 0.200" to 0.330"	
Mounting option:	Mounts to standard EIA 19" or 23" racks (with optional extender bracket) 12-port version can be wall mounted with optional 89D bracket	
Packaging:	Includes #12-24 mounting screws and punchdown retention caps	


key features and benefits

100% performance tested	Confidence that each jack module will deliver the critical electrical performance requirements		
Individually serialized	Each port is marked with quality control number for future traceability		
RJ45 interface	Industry standard interface provides a quick and easy plug and play connection to RJ45 patch cords; backwards compatible with Category 5		
Identification	Can be clearly identified with optional labels and icons for port identification		
Universal wiring scheme	T568A and T568B wiring schemes clearly identified		
Industry standard termination tool	Single wire 110 punchdown tool (PDT110) ensures conductors are fully terminated		
Block out device (optional)	Provides a simple and secure method to control access to data ports while not in use		
Angled design (optional)	Facilitates proper bend radius control and minimizes the need for horizontal cable managers		
Replacement jack module (optional)	Ability to replace field damaged ports for complete panel utilizations		

applications

DP6 PLUS Punchdown Patch Panels are a component of the TX6™ PLUS UTP Copper Cabling System. This end-to-end system is interoperable and backwards compatible, providing design flexibility to protect network investments well into the future. With certified performance to the ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E standards, this system is ideal for today's high performance workstation applications. With certified performance to the ANSI/TIA-568.2-D Category 6 and ISO 11801 Class E standards, these systems will support the following applications:

- Ethernet 10BASE-T, 100BASE-T (Fast Ethernet), 1000BASE-T (Gigabit Ethernet)
- · Digital video and broadband/baseband analog video
- Voice over Internet Protocol (VoIP)



24-port, 1 RU: DPA24688TGY 48-port, 2 RU: DPA48688TGY

DP6 PLUS Flat Punchdown Patch Panels

 12-port:
 DP12688TGY

 24-port, 1 RU:
 DP24688TGY

 48-port, 2 RU:
 DP48688TGY

Tools and Accessories

Wire snipping tool: CWST
Wire stripping tool: CJAST
Punchdown tool: PDT110
24-port label kit: DPLK24
48-port label kit: DPLK48

Replacement

jack module: DRJ688TGBL Strain relief bar: SRBM19BLY

DRWCIW-24

Replacement retention cap:

Extender bracket: PEB1

Clear dust cap: MDC-C

Block out device: PSL-DCJB-^^^

Phone icons: CIPIW-C

Data icons: CIDWH-C±

^^^To designate color other than Red, add suffix BL (Black), BU (Blue), YL (Yellow), GR (Green), OR (Orange), IW (Off White) or IG (International Gray) at the end of the part number. 10/package.


‡To designate color other than WH (White), replace WH with BU (Blue), RD (Red), YL (Yellow), GR (Green), OR (Orange) in the part number. 100/package.

test results

Mechanical Test	Test Method	Measurement	Typical Test Results
Normal force	ANSI/TIA-1096-A	Load (grams)	>100
Vibration	IEC 512-6d	Circuit Resistance (mOhms)	<40
Shock	IEC 512-6c	Contact Disturbance (microseconds)	<5
Durability	IEC 512-9a	Circuit Resistance (mOhms)	<40
Mating/un-mating	IEC 512-13b	Mating Force (N)	<20
	IEC 512-130	Un-Mating Force (N)	<20
Termination cycles	IEC 352	Number of Cycles	>20
Mating cycles	IEC 60603-7	Number of Plug Insertions	>2500

Electrical Test	Test Method	Measurement	Typical Test Results
Low level circuit resistance	IEC 512-2a	Resistance (mOhms)	<20
Dielectric withstand voltage	IEC 512-4a	1000 VAC, 1 minute	Passed
Insulation resistance	IEC 512-3a	Resistance (MOhms)	>500

Environmental Test	Test Method	Measurement	Typical Test Results
Temperature life	IEC 512-9b	Circuit Resistance (mOhms)	<40
Humidity	IEC 512-11c	Circuit Resistance (mOhms)	<40
Thermal shock	IEC 512-11d	Circuit Resistance (mOhms)	<40
Climatic sequence	IEC 512-11a	Circuit Resistance (mOhms)	<40
Flowing mixed gas corrosion	IEC 512-11a	Circuit Resistance (mOhms)	<40



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

