



Part Number: FC-ICCP0.5M^^, FC-ICCP1M^^


INSTALLATION INSTRUCTIONS PN651B © Panduit Corp. 2021





NOTE:


Steps 1-5 show cable preparation method for TX6A Cable with MaTriX Technology, similar for other cables.
























For Technical Support: www.panduit.com/resources/install_maintain.asp








For Technical Support: www.panduit.com/resources/install_maintain.asp
















For Technical Support: www.panduit.com/resources/install_maintain.asp





- For specified performance, follow TIA/EIA 568.2-D installation guidelines.
 Splice module can terminate 22-26 AWG solid or stranded IWC data cable with 0.060" (1.52mm) maximum insulated conductor outside diameter.
- Splice module may be re-terminated up to 20 times.
- For technical and performance information, consult Panduit technical support.

As with all Wiring Accessories, the following statements apply:

- Never install communications wiring during a lightning storm.
- Never install communications wiring in wet locations unless the plug is specifically designed for use in wet locations.
- Never touch uninsulated communications wiring or terminals unless the communication line has been disconnected at the network interface.
- Use caution when installing or modifying communication wiring.



Intertek 5020430 **Conforms to UL** STD 1863. **Certified to CSA** STD C22.2#233

For Instructions in Local Languages and Technical Support:

www.panduit.com

E-mail: techsupport@panduit.com

Phone: 866-405-6654