



NOTES:

1. MATERIAL:  
BODY - ALUMINUM, TIN PLATED  
SCREW - ALUMINUM, TIN PLATED
2. cULus LISTED FOR USE UP TO 600V & TEMPERATURE RATED 90°C (AL9CU)
3. DUAL RATED FOR USE WITH COPPER OR ALUMINUM STRANDED CODE CONDUCTOR
4. PARTS ARE RoHS COMPLIANT
5. USE OF OXIDE INHIBITING JOINT COMPOUND LIKE PANDUIT CMP-100 RECOMMENDED FOR PAD TO PAD AND CONDUCTOR SURFACES
6. SEE INSTRUCTION SHEET T-PMPI-223-PC FOR TIGHTENING TORQUE INFORMATION
7. DIMENSIONS IN BRACKETS ARE MILLIMETERS



PART NUMBER	WIRE RANGE COPPER/ALUMINUM	WIRE STRIP LENGTH	STUD SIZE IN.	PACKAGING QUANTITY	DIMENSIONS - IN [ mm ] ±.02 [ .5 ]								HEX KEY
					A	B	C	D	E	F	G	H	
LAM2B350-12-8	6 AWG - 350 kcmil	1-1/8	1/2	8	.63 [ 16.0 ]	1.75 [ 44.5 ]	1.13 [ 28.7 ]	4.19 [ 106.4 ]	.28 [ 7.0 ]	1.28 [ 32.4 ]	1.91 [ 48.4 ]	.68 [ 17.3 ]	3/8

PART NUMBER		SEE TABLE	
TITLE			
LAM2B Aluminum Connector (Reditek Phase 2) Customer Drawing			
CUSTOMER DRAWING			
ITEM REVISION NAME		03468NBC/00	
DATASET FILE NAME		03468NBC-DC/00	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTES	
DRAWING NUMBER		03468NBC - DC	
DRAWN BY	DATE	CHK	SCALE
JHNU	10-13-23	JHNU	NONE
SHEET 1 OF 1			SIZE
			B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	10-13-23	JHNU	JHNU	MRWA	DRAWING RELEASED	135288

B-SIZE CUSTOMER