

18900 Panduit Drive Tinlev Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMT4-W 27JUL20

Technical Data Sheet

Thermal Transfer Printable Polyvinyl Fluoride Film

This specification is intended to outline the physical and chemical properties of PANDUIT's pressure sensitive thermal transfer printable polyvinyl fluoride material and include the following part numbers and printable material identifiers:

Part Number Prefixes			
TTC*T			

Printable Material Suffixes			
TJT			

PRODUCT SPECIFICATIONS:

Description: Material is RoHS compliant (European Union directive 2002/95/EC).

Material is a self-extinguishing, top coated polyvinyl fluoride film with

a pressure sensitive adhesive.

Print Methods: This material is recommended for thermal transfer printing.

Adhesive: Acrylic based, pressure sensitive permanent adhesive.

Standard Colors: White

Thickness: 2.5 +/- 0.3 mils (substrate and adhesive)

-40°F to 275°F (-40°C to 135°C). Service Temperature Range:

Minimum Application Temperature: 50°F (10°C)

Storage Conditions: Store at 70°F (21°C) and 50% Relative Humidity.

PROPERTIES: PERFORMANCE:

Peel Adhesion to Stainless Steel: 35 oz/in width (PSTC-101, 15 min. dwell) Shear Adhesion: 20 hours (PSTC-107, Procedure A)

Tensile Strength: MD 12 +/- 1.2 lbs./inch width (PSTC-131)

MD 250% +/- 20% (PSTC-131) Elongation:

After 24 hours at 160°F (70°C) there was no deterioration of the substrate Elevated Temperature Exposure:

Passes the Federal Motor Vehicle Safety Standard (FMVSS-302) Flammability:

Average burn time less than 10 seconds (ASTM D1000)

Tack: 320 g/cm² (ASTM D-2979-88)

UV Resistance: *3000 hours no change observed (ASTM G154)

Page 1 of 3 © 2005 PANDUIT Corp

TDS: GMT4-W

^{*3000} hours equates to 5 years of assimilated outdoor UV exposure.

18900 Panduit Drive Tinley Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMT4-W 27JUL20 4

Technical Data Sheet

CHEMICAL/SOLVENT RESISTANCE:

The testing was conducted at room temperature. Samples were thermal transfer printed with Panduit RMR*BL/RMER*BL ribbon on the Panduit TDP43MY/TDP43ME printer. Separate sets were conditioned for 24 hours before being immersed in the following solvents for period of 1 hour and 24 hours. After the samples were removed from the immersed solvents, they were rubbed 10 times with a lint free gauze. Visual observations were noted for any smear or loss of legibility.

1 Hour Immersion

1 Hour Hilliersion		
Chemical/Solvent	Visual Observation	
Jet Fuel	No change	
Gasoline	No change	
Methyl Ethyl Ketone	Loss of print legibility	
1:1:1 TCE	Loss of print density	
Trichloroethylene	Loss of print density	
409 Cleaner	No change	
Alpha Flux 200L	No change	

24 Hours Immersion

Chemical Reagent Visual Observation		
Chemical Reagent	visual Observation	
Isopropyl Alcohol	Loss of print density	
Water 150F	No change	
Salt Water	No change	
SAE 30 Motor Oil	No change	
Hydraulic Fluid	No change	
Skydrol	Loss of print density	
Methanol/Water	No change	
Ethylene Glycol	No change	
ASTM #3 Oil	No change	

© 2005 PANDUIT Corp Page 2 of 3



18900 Panduit Drive Tinley Park, IL 60487

Customer Service: 800-777-3300

TDS: Effective Date: Revision:

GMT4-W 27JUL20

Technical Data Sheet

Chemical/Solvent Resistance:

Test was performed according to PSTC-101, ASTM D-543-87 and ASTM D-896-90. The testing was conducted at room temperature and performed with reference to the above test methods. The samples were cut 1" wide and applied to stainless steel panels and conditioned for 24 hours. The samples were then immersed in the specified reagents for 5 immersions using the following cycle: a 10 min. Immersion time followed by a 30 min. recovery time. After the fifth immersion, the samples were conditioned for 24 hours before testing. Percent retention of performance was based on a 48 hour adhesion value of 42 oz/in.

Chemical/Solvent	Visual Observation	Percent Retention of Performance
Distilled water	No effect	103%
Mineral Spirits	No effect	88%
Toluene	No effect	88%
Isopropyl Alcohol	No effect	100%
Methanol	No effect	100%
Acetone	Slight adhesive bleed	76%
Methyl Ethyl Ketone	No effect	92%
1,1,1 TCE	No effect	100%
Freon TF	No effect	103%
Super Agitene	No effect	96%
Jet A Fuel	Slight adhesive bleed	65%
Arco Truslide 68	No effect	92%
SAE 30 Motor Oil	No effect	108%

APPROVAL

UL Recognized: UL969 File Number: MH 14576, MH 14979

LIMITED WARRANTY

All PANDUIT Identification Solution Products (except for Software programs) are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to replacement of the product proved to be defective within 6 months from the date of sale, or in the case of printers, within 90 days from the date of sale. This warranty is void if the products or printers are modified. altered or misused in any way. Use of PANDUIT printers with any product other than the specified PANDUIT products for which the printer was designed constitutes misuse. Before using, the user shall determine the suitability of the product for its intended use and user assumes all risk and liability whatsoever in connection therewith. The foregoing may not be altered except by an agreement signed by officers or seller and manufacturer.

NEITHER PANDUIT OR SELLER SHALL BE LIABLE FOR ANY OTHER INJURY, LOSS OR DAMAGE, WHETHER DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OF, OR THE INABILITY TO USE THE PRODUCT OR THE PRINTER.

THIS WARRANTY IS MADE IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS OF PARTICULAR USE ARE SPECIFICALLY EXCLUDED.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide or use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. This publication is not to be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.

© 2005 PANDUIT Corp Page 3 of 3

TDS: GMT4-W