


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:
VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.

SPECIFICATIONS:
PANDUIT TOOL NO: CT-100B

HAND-HELD SINGLE PIECE CRIMPING HAND TOOL FOR INSULATED AND NON-INSULATED TERMINALS RANGING FROM #22 AWG TO #10 AWG. THIS TOOL ALSO CUTS AND STRIPS WIRE IN THOSE SIZES AND CUTS UNHARDENED MACHINE SCREWS.

TOOL WEIGHT: 8.9 oz. (253 g)

THIS TOOL'S FEATURES INCLUDE:

- STRIPPING OF STRANDED AND SOLID WIRE WITH PVC INSULATION #22 AWG TO #10 AWG
- CUTTING UNHARDENED MACHINE SCREWS IN 4-40, 6-32, 8-32, 10-32 AND 10-24.
- CUTTING AND BENDING SOLID AND STRANDED WIRES #22 AWG TO #10 AWG.
- CRIMPING INSULATED AND NON-INSULATED SOLID AND STRANDED WIRES FROM #22 AWG TO #10 AWG.
- THIS IS NOT A CONTROLLED CYCLE TOOL.

TOOL IS FULLY RECYCLABLE.
TOOL IS RoHS COMPLIANT.

DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.
DIMENSIONS IN PARENTHESES ARE IN [mm].

THIS TOOL IS THE REPLACEMENT FOR THE CT-100A CRIMP TOOL.

PART NUMBER		CT-100B	
TITLE		TERMINAL AND CRIMP TOOL	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		R29562BB/01	
MATERIAL		AS NOTED	
DRAWING NUMBER		TP29562A01	
DRAWN BY		BVG	
DATE		10-01-19	
CHK		BJPU	
SCALE		NONE	
SHEET 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	02-21-24	JBN	MRWA	ASY	ADDED HEXAGON SOCKET SCREW AND RELOCATED YELLOW DOT	051752/01
00A	10-01-19	BVG	BJPU	JADE	INITIAL RELEASE	051752/00

A-SIZE CUSTOMER

A