




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. EQUIPMENT RAILS (E-RAILS) ARE SET TO 622.3mm FROM THE FACTORY. E-RAILS ARE INFINITELY ADJUSTABLE, FROM A MINIMUM OF 127.5mm APART, TO A MAXIMUM FOUND IN THE CHART ON SHEET 2.
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS  
15.88mm [ .625in ], 15.88mm [ .625in ],  
12.70mm [ .5in ], 15.88mm [ .625in ],  
15.88mm [ .625in ], 12.7mm [ .5in ]...ETC.
6. PARTS SUPPLIED:
  - BASE CABINET
  - FRONT CURVED PERFORATED SINGLE HINGE DOOR, 69% OPEN AREA
  - REAR PERFORATED SPLIT DOOR, 69% OPEN AREA
  - EQUIPMENT RAILS FRONT & REAR (E-RAILS) (SEE CHART ON SHEET 2)
  - CABLE MANAGEMENT BRACKETS (CMB)
  - FRONT FINGER BRACKET FOR MOUNTING OPTIONAL CABLE MANAGEMENT FINGERS
  - SWIVEL CASTERS
  - HARDWARE KIT CONTAINING:
    - (40) M6 CAGE NUTS
    - (40) M6 PHILIPS HEAD SCREWS
    - (4) GANGING BRACKETS
    - (8) M5 TORX (T25) THREAD CUTTING SCREWS
    - (4) RINGS OF CABINET LOCK KEYS WITH (2) KEYS PER RING.
  - LEVELING LEGS
  - FINGER KIT (ONLY DA8\*\*\*BF PART NUMBERS)
  - INSTRUCTION SHEET (NOT SHOWN)
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING 1500 Kg (3300 LBS)
10. ROLLING LOAD RATING 500 Kg (1102 LBS)
11. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
03F	9/3/18	MEX-JAGC	DWR	SJP	REMOVED 48RU SIZE	V09001RP/06
03E	6/7/18	MEX-JAGC	DWR	SJP	ADDED 48RU SIZE	V09001RP/00
03D	5/8/18	MEX-JAGC	DWR	SJP	STATIC LOAD RATING UPDATED ADDED HARDWARE KIT TO PARTS SUPPLIED	V09001RG/00
03B	10/3/17	MEX-JAGC	DWR	ELE	ADDED DA****BF PART NUMBERS	V09000QF/02
01B	4-14-16	LEE	MCIS		ADDED E-RAIL LOCATION VIEW, SHEET 5	V09000QF/01
01A	3-22-16	LEE	MCIS		RELEASED TO PRODUCTION	V09000QF/00

TITLE		NET-VERSE D-TYPE CABINET 800 WIDE X 42 & 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** & DA8****F) CUSTOMER DRAWING		
ITEM REVISION NAME		15V526ZG/03		
DATASET FILE NAME		15V526ZG_DC/03F		
		 THIRD ANGLE PROJECTION		
DRAWN BY		DATE	CHK	SCALE
LEE		3-22-16	MCIS	NONE
		SHT 1 OF 8		
		A		

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	FRAME HEIGHT	FRAME DEPTH	E-RAIL MAXIMUM SPACING	SIDE PANELS	FINGER KIT QTY	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
DA8219*	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1000mm DEEP	1998.0 [ 78.76 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	00	00	102 Kg/EACH 225 LBS/EACH	123 Kg/EACH 270 LBS/EACH
DA8212*	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1000mm DEEP	1998.0 [ 78.76 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	04	00	141 Kg/EACH 311 LBS/EACH	161 Kg/EACH 356 LBS/EACH
DA8229*	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1200mm DEEP	1998.0 [ 78.76 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	00	00	107 Kg/EACH 237 LBS/EACH	130 Kg/EACH 287 LBS/EACH
DA8222*	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1200mm DEEP	1998.0 [ 78.76 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	04	00	152 Kg/EACH 336 LBS/EACH	175 Kg/EACH 386 LBS/EACH
DA8519*	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1000mm DEEP	2131.4 [ 83.91 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	00	00	105 Kg/EACH 232 LBS/EACH	126 Kg/EACH 278 LBS/EACH
DA8512*	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1000mm DEEP	2131.4 [ 83.91 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	04	00	157 Kg/EACH 345 LBS/EACH	180 Kg/EACH 396 LBS/EACH
DA8529*	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1200mm DEEP	2131.4 [ 83.91 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	00	00	110 Kg/EACH 243 LBS/EACH	133 Kg/EACH 294 LBS/EACH
DA8522*	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1200mm DEEP	2131.4 [ 83.91 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	04	00	166 Kg/EACH 365 LBS/EACH	189 Kg/EACH 417 LBS/EACH

NOTE: \*DENOTES COLOR - ADD SUFFIX "B" FOR BLACK AND "W" FOR WHITE.

							<b>NET-VERSE D-TYPE CABINET 800 WIDE X 42 &amp; 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** &amp; DA8****F)</b> CUSTOMER DRAWING			
03F	9/3/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/06	ITEM REVISION NAME			
03E	6/7/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/00	15V526ZG/03			
03D	5/8/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00	DATASET FILE NAME			
03B	10/3/17	MEX-JAGC	DWR	ELE	SEE SHEET ONE FOR REVISIONS	V09000QF/02	15V526ZG_DC/03F			
01B	4-14-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/01	MATERIAL:			
01A	3-22-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/00	N/A			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	 THIRD ANGLE PROJECTION			
							DRAWN BY	DATE	CHK	SCALE
							LEE	3-22-16	MCIS	NONE
							SHT 2 OF 8			
							A			

B

A

A



A

A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	FRAME HEIGHT	FRAME DEPTH	E-RAIL MAXIMUM SPACING	SIDE PANELS	FINGER KIT QTY	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
DA8219*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1000mm DEEP WITH FINGER KIT	1998.0 [ 78.76 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	00	01	105 Kg/EACH 231 LBS/EACH	126 Kg/EACH 276 LBS/EACH
DA8212*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1000mm DEEP WITH FINGER KIT	1998.0 [ 78.76 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	04	01	144 Kg/EACH 317 LBS/EACH	164 Kg/EACH 362 LBS/EACH
DA8229*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1200mm DEEP WITH FINGER KIT	1998.0 [ 78.76 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	00	01	110 Kg/EACH 242 LBS/EACH	133 Kg/EACH 293 LBS/EACH
DA8222*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 42RU X 1200mm DEEP WITH FINGER KIT	1998.0 [ 78.76 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	04	01	155 Kg/EACH 342 LBS/EACH	178 Kg/EACH 392 LBS/EACH
DA8519*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1000mm DEEP WITH FINGER KIT	2131.4 [ 83.91 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	00	01	108 Kg/EACH 238 LBS/EACH	129 Kg/EACH 284 LBS/EACH
DA8512*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1000mm DEEP WITH FINGER KIT	2131.4 [ 83.91 ]	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	04	01	160 Kg/EACH 351 LBS/EACH	183 Kg/EACH 402 LBS/EACH
DA8529*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1200mm DEEP WITH FINGER KIT	2131.4 [ 83.91 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	00	01	113 Kg/EACH 249 LBS/EACH	136 Kg/EACH 300 LBS/EACH
DA8522*F	NET-VERSE D-TYPE CABINET 800mm WIDE X 45RU X 1200mm DEEP WITH FINGER KIT	2131.4 [ 83.91 ]	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	04	01	169 Kg/EACH 371 LBS/EACH	192 Kg/EACH 423 LBS/EACH


NOTE: \*DENOTES COLOR - ADD SUFFIX "B" FOR BLACK AND "W" FOR WHITE.

							TITLE NET-VERSE D-TYPE CABINET 800 WIDE X 42 & 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** & DA8****F) CUSTOMER DRAWING					
03F	9/3/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/06	ITEM REVISION NAME 15V526ZG/03					
03E	6/7/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/00	DATASET FILE NAME 15V526ZG_DC/03F					
03D	5/8/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00						
03B	10/3/17	MEX-JAGC	DWR	ELE	SEE SHEET ONE FOR REVISIONS	V09000QF/02						
01B	4-14-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/01					MATERIAL:  N/A	
01A	3-22-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/00	 THIRD ANGLE PROJECTION				DRAWING NUMBER: 15V526ZG-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY LEE	DATE 3-22-16	CHK MCIS	SCALE NONE	SHT 3 OF 8	SIZE A


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




LEFT VIEW



FRONT VIEW



RIGHT VIEW



REAR VIEW

REAR DOOR DEPTH 25 [1.0]

FRONT DOOR DEPTH 59 [2.3]

SWIVEL FRONT CASTERS


SWIVEL REAR CASTERS

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
03F	9/3/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/06
03E	6/7/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/00
03D	5/8/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00
03B	10/3/17	MEX-JAGC	DWR	ELE	SEE SHEET ONE FOR REVISIONS	V09000QF/02
01B	4-14-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/01
01A	3-22-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/00

TITLE		NET-VERSE D-TYPE CABINET 800 WIDE X 42 & 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** & DA8****F)	
ITEM REVISION NAME		15V526ZG/03	
DATASET FILE NAME		15V526ZG_DC/03F	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 15V526ZG-DC	
DRAWN BY	DATE	CHK	SCALE
LEE	3-22-16	MCIS	NONE
SHT 4 OF 8			SIZE A

**PANDUIT**

N/A



THIRD ANGLE PROJECTION

DRAWING NUMBER:

15V526ZG-DC

DRAWN BY

DATE

CHK

SCALE

LEE

3-22-16

MCIS

NONE

SHT 4 OF 8

SIZE

A

2

1

B


A

A


A

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT DOOR, REAR DOOR,  
AND SIDE PANELS NOT SHOWN



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
03F	9/3/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/06
03E	6/7/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/00
03D	5/8/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00
03B	10/3/17	MEX-JAGC	DWR	ELE	SEE SHEET ONE FOR REVISIONS	V09000QF/02
01B	4-14-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/01
01A	3-22-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/00


TITLE					
NET-VERSE D-TYPE CABINET 800 WIDE X 42 & 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** & DA8****F) CUSTOMER DRAWING					
ITEM REVISION NAME				<div>PANDUIT</div>	
15V526ZG/03					
DATASET FILE NAME					
15V526ZG_DC/03F				MATERIAL :	
<div></div> <div>THIRD ANGLE PROJECTION</div>				N/A	
				DRAWING NUMBER:	
				15V526ZG-DC	
DRAWN BY	DATE	CHK	SCALE	SHT 5 OF 8	SIZE
LEE	3-22-16	MCIS	NONE		A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


B



REAR OF CABINET  
BOTTOM VIEW

128 [5.0]  
FROM FRONT  
OF FRAME TO  
FACE OF RAIL

622 [24.5]  
FROM FRONT FACE  
OF FRONT RAIL  
TO REAR FACE  
OF REAR RAIL



REAR OF CABINET  
TOP VIEW

SOME PARTS REMOVED FOR CLARITY

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
03F	9/3/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/06
03E	6/7/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/00
03D	5/8/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00
03B	10/3/17	MEX-JAGC	DWR	ELE	SEE SHEET ONE FOR REVISIONS	V09000QF/02
01B	4-14-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/01
01A	3-22-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/00

TITLE		NET-VERSE D-TYPE CABINET 800 WIDE X 42 & 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** & DA8****F)		
ITEM REVISION NAME		15V526ZG/03		
DATASET FILE NAME		15V526ZG_DC/03F		
THIRD ANGLE PROJECTION		MATERIAL:		
DRAWN BY		N/A		
DATE		DRAWING NUMBER:		
LEE		15V526ZG-DC		
3-22-16		SHT 6 OF 8		
MCIS		A		
NONE				

B

A

2



1

D10100DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TOP CAP OPENING CABLE CAPACITY								
	AREA		CABLE CAPACITY* (CABLE DIA)					
	CM <sup>2</sup>	IN <sup>2</sup>	CAT 6A (8.99mm)	CAT 6A (7.87mm)	CAT 6A (7.54mm)	CAT 6 (6.35mm)	CAT 5e (4.75mm)	FIBER (3mm)
84mm × 476mm FRONT AND REAR OPENINGS (EACH)	399.6	61.9	251	328	358	504	902	2261
39.8mm × 476mm SIDE OPENINGS (EACH)	189.2	29.3	119	155	169	239	427	1070

\* CAPACITY CALCULATION ASSUMES 40% FILL FACTOR

							TITLE NET-VERSE D-TYPE CABINET 800 WIDE X 42 & 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** & DA8****F) CUSTOMER DRAWING					
							ITEM REVISION NAME 15V526ZG/03					
							DATASET FILE NAME 15V526ZG_DC/03F					
03F	9/3/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/06				MATERIAL:  N/A		
03E	6/7/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/00						
03D	5/8/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00						
03B	10/3/17	MEX-JAGC	DWR	ELE	SEE SHEET ONE FOR REVISIONS	V09000QF/02						
01B	4-14-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/01						
01A	3-22-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/00						
										THIRD ANGLE PROJECTION		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY LEE	DATE 3-22-16	CHK MCIS	SCALE NONE	DRAWING NUMBER: 15V526ZG-DC	
											SHT 7 OF 8	SIZE A



2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

42RU 46.3 [1.8]  
45RU 112.9 [4.4]  
FROM CENTER OF TOP  
MOUNTING BUTTON TO  
EIA MOUNTING BEAM

42RU 137.5 [5.4]  
45RU 204.1 [8.0]  
FROM CENTER OF TOP MOUNTING  
BUTTON TO TOP CAP



PDU FIT:  
MAXIMUM WIDTH OF 63mm FOR (2) PDU'S MOUNTED  
ON ONE BRACKET, OR (1) 130mm WIDE PDU.

PDU'S GREATER THAN 61.5mm (42RU & 45RU)  
DEEP WILL BE BLOCKED BY EIA RAIL MOUNTING  
BEAMS, AS SHOWN IN VIEWS ON LEFT.

PDU'S GREATER THAN 129.8mm (42RU & 45RU)  
DEEP WILL ENTER EIA AREA BEHIND REAR  
EQUIPMENT RAILS.

42RU 80.6 [3.17]  
45RU 58.4 [2.29]  
TO FRAME



SOME  
COMPONENTS  
REMOVED  
FOR CLARITY

REAR VIEW

RIGHT VIEW

03F	9/3/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/06
03E	6/7/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP/00
03D	5/8/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00
03B	10/3/17	MEX-JAGC	DWR	ELE	SEE SHEET ONE FOR REVISIONS	V09000QF/02
01B	4-14-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/01
01A	3-22-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09000QF/00

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
-----	------	----	-----	-----	-------------	-----

TITLE						NET-VERSE D-TYPE CABINET 800 WIDE X 42 & 45 X 1000mm/1200mm DEEP WITHOUT/WITH FINGER KIT (DA8**** & DA8****F) CUSTOMER DRAWING	
ITEM REVISION NAME				15V526ZG/03			
DATASET FILE NAME				15V526ZG_DC/03F			
				MATERIAL :			
				N/A			
				DRAWING NUMBER:			
				15V526ZG-DC			
DRAWN BY		DATE		CHK		SCALE	
LEE		3-22-16		MCIS		NONE	
				SHT 8 OF 8		SIZE A	

2

1

D10100DA/16