# CT-2980/STBT Tool Specification

I. SCOPE: This specification defines the requirements for a battery operated, hydraulic tool and related components for terminating compression connectors. The tool is a dieless tool using four "indenters" to crimp applicable product. This tool meant for intermittent use. This tool now includes Blue Tooth connectivity to a cellular phone app that monitors tool performance.

#### II. TOOL FUNCTION & FEATURES:

#### A. Mechanical Function:

- 1. Tool output to be 6.2 tons (55 kN).
- 2. Minimum diametrical diameter opening to be 1.52" (38.5 mm).
- **3.** Approximate cycle time to be 9 seconds without product.
- 4. Tool ram to retract when the tool has reached its maximum output load.
- **5.** Tool head to open for removal for contiguous wire terminations.
- **6.** Tool to have built in locking feature to secure battery in place.
- 7. Tool to operate on 18.0 VDC Li-Ion Batteries.

#### **B.** Operational Features:

- 1. Tool does not require any operator adjustments.
- 2. Tool or battery to have a "low Battery" indicator light.
- 3. Tool ram activated by depressing trigger. Tool ram while advancing holds position when trigger is released. Tool ram may have feature to "teach" the tool to a user set position.
- 4. Tool to have manual retract/release button. Tool ram while retracting holds position when button is activated.
- 5. Tool has flashing LED and audible signal to alert if full crimp pressure is not achieved.
- 6. Tool to have shoulder strap rings.
- 7. Crimp head to rotate at least 350 degrees fully.
- 8. No additional pinch points.
- MAKITA Battery voltage to be 18.0 VDC 4 A-Hr Lithium-Ion. Battery will recharge in about one hour or less.
- 10. Tool has digital screen on lower back edge of tool. Tool is connected by Blue Tooth to a cellular phone app. The app is to be available in Android, iOS and Windows PC platforms.

# III. DESCRIPTION OF USE:

- 1. The operator pre-wires the desired compression connector.
- The operator properly positions the tool over the compression connector and activates the crimp cycle multiple times to position and hold the connector by pressing the ram advance trigger.
- 3. Assemble wire into connector.
- 4. Press trigger to operate the tool ram. The tool ram continues to close as long as the operator holds the trigger, and stops as soon as maximum output force is reached
- 5. The tool crimps the compression connector until the maximum output force is reached. The operator may retract the tool ram by releasing the trigger and/or pushing retract button. After maximum output force is reached the tool ram returns automatically.
- 6. When the maximum output force is reached, the tool ram starts to retract to indicate the crimp cycle is complete.
- 7. The operator presses the ram retract trigger to open the dies. After maximum output force is reached the tool ram returns automatically. If maximum crimp force is not reached, the tool signals with flashing LED and audible signal.
- 8. The operator removes the compression connector from the tool.

### IV. TECHNICAL / PERFORMANCE SPECIFICATIONS:

- 1.  $\#4\ AWG-750\ MCM\ (kcmil)\ Copper\ lugs\ and\ splices$
- 2. #6 AWG 500 MCM (kcmil) Aluminum lugs and splices.

PAGE: 1 of 3

# **CT-2980/STBT Tool Specification**

# V. LIFETIME PERFORMANCE:

Lifetime Performance to be 50,000 cycles minimum of the tool. Performance is based on standard usage and making sure all preventative maintenance requirements have been met on time.

#### VI. PHYSICAL CHARACTERISTICS:

## A. Approximate Overall Dimensions (with battery):

1. Length: 15.2" (387 mm) 2. Width: 3" (76 mm) 3. Height: 13.8" (351 mm)

**B. Weight:** 10.8 lbs. (4.9 kg)

#### C. Color and Texture:

1. Tool housing to be black.

# **D.** Environmental Requirements:

- 1. 50° to 104°F (Battery Charging Temp.)
- 2. -4° to 104°F (Tool Operating Temp, w/o battery warmer)
- 3. 10% to 95% Relative Humidity
- 4. Must work in an indoor and outdoor environment.

#### E. Minimum Rate of Operation

1. Minimum of 4 crimps per minute with 3 trigger pulls per crimp.

#### VII. PACKAGING

- A. Tool to be packaged in a hard plastic case.
- **B.** Tool case must hold tool, test cylinders and gage, two batteries and charger.
- C. Batteries are to conform to regulatory specification for packaging.

#### VIII. REGULATORY COMPLIANCE

- **A. Tool:** UL/CSA power connector/terminal compliance. Tool is CE tool compliant. Tool to be UL/CSA listed under UL 60745-1. Tool shall conform to IEC/EN 62841-1, ENV 61000, and ISO 12100. Tool is to be registered with Bluetooth SIG.
- **B.** Charger: UL/CSA and CE power compliant.
- C. Battery: CE compliance required.

#### IX. OPERATION INSTRUCTIONS

- **A.** Existing operating instructions with modifications are to be used.
- **B.** Alternate source Manufacturer's Battery and Charger manual to be used.

# X. WARRANTY

Tool warranty is 5 years. Battery is 1 year and Charger warranty is 2 years.

#### XI. ACCESSORIES (PROVIDED WITH TOOL):

- A. 2- Li-Ion 18.0 VDC rechargeable batteries.
- **B.** Manufacturer's battery charger and manual.

PAGE: 2 of 3

# **CT-2980/STBT Tool Specification**

- C. Tool Case with storage for batteries, charger, test cylinders and gage, and tool.
- **D.** Operating Instructions (see section IX).
- E. Tool Safety Booklet
- F. Shoulder Strap
- **G.** Test Cylinders and gage.

# XII. ACCESSORIES (SOLD SEPARATELY):

- **A.** Li-Ion 18.0 VDC rechargeable batteries (4.0Ah).
- **B.** Charger available in 115 VAC (US).

PAGE: 3 of 3