



NOTES:

- 1) DIMENSIONS IN [] ARE MILLIMETERS
- 2) 5 PIN CYLINDER
- 3) AVAILABLE WITH CUSTOM KEYING
- 4) SHORT SHACKLE IS STANDARD ADD "-LS" FOR LONG SHACKLE
- 5) REFERENCE TABLE FOR BODY STYLE

	BODY	DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"
PSL-14BYL	1	1.94 [49.3]	1.40 [35.4]	0.80 [20.3]	0.98 [24.9]	0.32 [8.1]	1.08 [27.5]
PSL-14BYL-LS	1	1.94 [49.3]	1.40 [35.4]	0.80 [20.3]	2.49 [63.2]	0.32 [8.1]	1.08 [27.5]
PSL-14ABL	2	1.43 [36.3]	1.23 [31.2]	0.57 [14.5]	0.96 [24.4]	0.27 [6.9]	0.75 [19.1]

						TITLE		
						PSL-14 Series Weatherproof Padlocks		
						CUSTOMER DRAWING		
						ITEM REVISION NAME		
						00220NCS/00		
						DATASET FILE NAME		
						00220NCS_C11716/00A		
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		
						.x ± .25 [6.35] .xxx ± .05 [1.27]		
						.xx ± .15 [3.81] ANGLES ± 5 °		
						THIRD ANGLE PROJECTION		
						DRAWING NUMBER: C11716		
						MATERIAL: Brass, Steel, & Plastic		
00	02/08/2018	AUMA	DJW	JHAC	Initial Release	GAECN05189		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY AUMA	DATE 1/30/18
							CHK JHAC	SCALE 1:1
								SIZE A