


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT
GPKT724Y	9.95 LB/ea 4522.73g/ea

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.
- 288 PAIR CATEGORY 6 TOWER ASSEMBLY IS DESIGNED FOR WALL MOUNT APPLICATIONS, PROVIDES VERTICAL CABLE MANAGEMENT, AND SUPPLIED JUMPER TROUGHS PROVIDE VERTICAL CABLE MANAGEMENT.
- ASSEMBLY COMES WITH FASTENER KIT WHICH INCLUDES THE FOLLOWING: (2) #12 X 1/2" SHEET METAL SCREWS, (2) #12 LOCK WASHERS, (1) 1/4-20 X 3/4 MACHINE SCREW, (1) 1/4-20 HEX NUT, (2) 1/4" LOCK WASHERS.
- ALSO INCLUDED WITH TOWER IS A SCREW KIT USED TO MOUNT THE JUMPER TROUGHS AND BASES.
- 6 LABEL HOLDERS AND 6 LABELS ARE ALSO PROVIDED.
- SEE CHART FOR NUMBER OF CONNECTING BLOCKS INCLUDED FOR EACH PART NUMBER.
- DIMENSIONS IN ( ) ARE IN METRIC.

PART NUMBER		GPKT724Y	
TITLE		GP6 PLUS STANDARD DENSITY 288 PAIR TOWER KIT	
		CUSTOMER DRAWING	
ITEM REVISION NAME		M01537PK/00	
DATASET FILE NAME		M01537PK_DC44/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xxx ± .010 [ .3 ]		SEE NOTES	
.xx ± .03 [ .8 ]		DRAWING NUMBER:	
ANGLES ±		01357-44	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
MDJR	3-08-07	PBD	NONE
REV	DATE	BY	CHK
1	5/30/14	JSP	REFR
R	3-08-97	MDJR	PBD
APR			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5/30/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	01537-44
R	3-08-97	MDJR	PBD	RMD	RELEASED TO PRODUCTION	01537-44

D10100DA/14

2

1

2

1