

Kev Features

# SFP28 Passive Direct Attach Copper (DAC) Cable Assemblies

Low Power, Low Latency 25 Gb/s Server Interconnect Solution for Top of Rack Switching Applications



High bandwidth interconnects are required for next generation data centers. Panduit offers SFP28 Direct Attach Copper Cable Assemblies. These passive cables provide a cost-effective solution for interconnecting high speed 25GbE switches and servers. This high speed data transport capability is ideal as server virtualization becomes more prevalent. With multiple virtual machines, server I/O consolidation topology requires 25 Gb/s interconnects between top of rack switches and servers. By incorporating SFP28 Passive DAC Cable Assemblies into the physical infrastructure, businesses can achieve 25 Gigabit performance port-to-port without additional signal processing or conversion, providing a low power, low latency server interconnect for top of rack switching applications.

100% performance tested	Confidence that each assembly delivers specified performance for ensured network availability  Ensuring 25 Gb/s performance when mated to any SFF-8402 SFP28 compliant host port				
Compliant to SFF-8402, SFF-8432, and SFF-8472					
Robust construction	High speed 22 GHz twin-axial cable, with two shielded parallel pairs, factory terminated to SFP28 25 Gb/s hot pluggable modular connectors; rated to a minimum 250 mating cycles				
Low latency performance	Ideal for high performance computer clustering and other latency sensitive applications				
Passive low power assembly	Provides a low cost short reach interconnect option with no additional power draw				

belly-to-belly high density installations

### Key Applications Include:

• Top of Rack Switching

Small diameter cable design

**Built-in strain relief** 

Variety of lengths

• I/O Consolidation

Low profile

• Fibre Channel Over Ethernet (FCOE)

• 25 Gigabit Ethernet

Robust easy-to-use connector latching feature allows easy installation in

Enables proper cable management and improved air flow

Ensures proper bend radius control for reliable deployment

• 16 Gb/s Fibre Channel

1 to 5 meters (1 meter increments) for design flexibility and optimum airflow

• High Performance Computer Clustering

## SFP28 Passive Direct Attach Copper (DAC) Cable Assemblies


#### Technical Information

Characteristic impedance	100 ± 5 Ω
Temperature range	-25°C to 80°C (-13°F to 176°F)
IEC flame compliance	IEC 60332, 60333, 60324
Bend radius	5 x O.D. single time, 10 x O.D. repeated times
Insertion force to cage	18N (4 lbf.) maximum
Withdrawal force from cage	12.5N (2.8 lbf.) maximum
Retention force	90 – 170N (20 – 38 lbf.)
ROHS status	Compliant

#### Ordering Information

	Length	Length		Nominal Cable O.D.		
Part Number	(m)	(Ft.)	Cable Gauge	mm	ln.	Cable Jacket
PSF2PZA1M**	1	3.3	30 AWG	4.1	0.161	PVC
PSF2PZA1.5M**	1.5	4.9	30 AWG	4.1	0.161	PVC
PSF2PZA2M**	2	6.6	30 AWG	4.1	0.161	PVC
PSF2PZA2.5M**	2.5	8.2	26 AWG	4.1	0.161	PVC
PSF2PZA3M**	3	9.8	30 AWG	4.1	0.161	PVC
PSF2PZC3.5M**	3.5	11.5	26 AWG	4.9	0.193	PVC
PSF2PZC4M**	4	13.1	26 AWG	4.9	0.193	PVC
PSF2PZC5M**	5	16.4	26 AWG	4.9	0.193	PVC

Replace \*\* with cable jacket colors: BL - Black, BU - Blue, RD - Red, WH - White



#### **WORLDWIDE SUBSIDIARIES AND SALES OFFICES**

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

