









THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

2

В

	FRONT AND REAR E-RAIL POSITION RANGE								
WIDTH	DEPTH	FRONT OF FRAME TO FRONT RAIL	FRONT TO REAR RAIL SPAN						
600	1070	64mm (2.5")	154mm TO 915mm / (6.1" TO 36.0")						
600	1200	64mm (2.5")	154mm TO 1065mm / (6.1" TO 42.0")						

В

А

NOTE: MAXIMUM E-RAIL SPAN ONLY POSSIBLE IF NO PDU BRACKETS ARE INSTALLED

PART NO.	DESCRIPTION	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
XGL64212*	FLEXFUSION™ LIMITED CABINET	123 Kg/EACH	136 Kg/EACH
	600mm X 42RU X 1070mm DEEP W∕SIDE PANELS	271 LBS/EACH	300 LBS/EACH
XGL64812*	FLEXFUSION™ LIMITED CABINET	136 Kg/EACH	148 Kg/EACH
	600mm X 48RU X 1070mm DEEP W∕SIDE PANELS	300 LBS/EACH	326 LBS/EACH
XGL64222*	FLEXFUSION™ LIMITED CABINET	131 Kg/EACH	143 Kg/EACH
	600mm X 42RU X 1200mm DEEP W∕SIDE PANELS	289 LBS/EACH	315 LBS/EACH
XGL64822*	FLEXFUSION™ LIMITED CABINET	146 Kg/EACH	158 Kg/EACH
	600mm X 48RU X 1200mm DEEP W∕SIDE PANELS	322 LBS/EACH	348 LBS/EACH

		DENOTES "B" = E "W" = \	BLĀČK	<		LIS	RE CABINET THAT INCLUDES A TE 8: FRAME, E-RAILS, TOP HINGED FRONT DOOR, SPLIT DU BRACKETS, (4) LEVELING L	CAP, SIDE PANELS, HINGED REAR DOOR,			
A								FLEXFUSION [™] XGL 600mm CABINET FAMILY			
								ITEM REVISION NAME 01196EAV/00 DATASET FILE NAME 01196EAV_DC/00A			
NL_AS1ZE	00A	2/1/23	MEX- JAGC	ткw	ELE	DRAWING RELEASE	V09002UV/00	THIRD ANGLE PROJECTION	N/A Drawing number: 01196EAV-DC		
NXGLOBA	REV	DATE	BY	СНК	APR		ECN	DRAWN BY DATE CHK SCALE MEX- JAGC 2/1/23 TKW NONE	SHT 6 OF 6		