ELECTRICAL SOLUTIONS

Write-On Labels on Cards

Material Chart

Material	Print Method	Temperature Range	Features
Vinyl Cloth	Pre-Printed	-50°F to 170°F (-46°C to 77°C)	Indoor/outdoor rated; conformable material with repositionable adhesive allows label to be removed and reused or used in temporary applications; provides durability, high temperature resistance, and dimensional stability for rough or textured surfaces.

			Wi	Width		Height		Std. Pkg.	Std. Ctn.
Part Number	Symbol	Description	ln.	mm	ln.	mm	Per Card		Card(s)
PCWL-BL		BLANK			0.63	15.90	14	25	100
PCWL-ACC	ACCEPTED BY DATE	ACCEPTED						25	100
PCWL-CAL	CALIBRATION BY DATE	CALIBRATION	1.50	00.40				25	100
PCWL-CALD	CALIBRATED BYDATE DUE	CALIBRATED	1.50	38.10				25	100
PCWL-ICAL	CALIBRATION BYDATE DUE GAGE ID	CALIBRATION						25	100
PCWL-REJ	REJECTED DATE REASON BY	REJECTED						25	100

Order number of cards required.

Can be clearly identified with Panduit permanent marking pens.

A. System Overview

B1. Cable Ties

B2. Cable Accessories

> B3. Stainless

C1. Wiring Duct

C2. Surface Raceway

C3. Abrasion Protection

Cable Management

D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems

> E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/ Tagout & Safety Solutions

> F. Index