


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO.	WEIGHT
PZLRB2U	10.42 lbs/EACH 4.73 kgs/EACH

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- MAIN BRACKET
 - 2- RECTANGULAR BRACKETS
 - 2- L-SHAPED ATTACHMENT BRACKETS
 - 6- 3-8/16 HEX SERRATED FLANGE NUTS
 - 6- 3-8/16 CARRIAGE BOLTS
 - 2- #12-24 SCREWS (4 PACK)
5. CABLE MANAGEMENT OPTIONS:
 - BEND RADIUS POSTS (PZBR4)
 - VERTICAL D-RINGS (CMVDR2)
6. STATIC LOAD CAPACITY - 40 lbs

HOLES FOR ATTACHING
CABLE MANAGEMENT PRODUCTS.
(SEE NOTE 5)

A

TITLE		PANZONE OVERHEAD DISTRIBUTION RACK (PZLRB2U)	
CUSTOMER DRAWING			
ITEM REVISION NAME		V10521A0/01	
DATASET FILE NAME		V10521A0_DC/01B	
		THIRD ANGLE PROJECTION	
MATERIAL		N/A	
DRAWING NUMBER		V10521A0-DC	
DRAWN BY	DATE	CHK	SCALE
PM	6-6-11	SRK	1:8
SHEET 1 OF 1		A	

2

1

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01B	11-28-22	JBO	KRKE	BETL	UPDATED DRAWING TITLE BLOCK ADDED NOTE 6, STATIC LOAD CAPACITY	M09000RD

A-SIZE CUSTOMER